

THE FUTURE IS ON®

LEVITON®



Temporary Power Solutions

LINE CARD



TEMPORARY POWER SOLUTIONS

Leviton has a wide range of temporary power solutions to give you the power you need, when and where you need it. Our devices are built to deliver safe and reliable power in hazardous environments, keeping you connected and preventing unplanned downtime.

Rhino-Hide® Single Pole Cam Devices

- Complete line includes 15 (to 150A/600V), 16/18 (to 400A/600V), and 17/22/23 (to 690A-600V) Series devices
- Insulating sleeves are color-coded for phase identification and designed for rugged applications
 - Available in a range of termination styles and cord range options



LEV Series IEC 60309 Pin & Sleeve Devices

- Industrial grade plugs, connectors, receptacles, inlets and mechanical interlocks
- 30 A & 60 A North American Configurations
- IP66, IP67, IP68 and IP69K Rated
- Superior watertight ratings for use in any environment
- Improved safety and productivity with Inform™ Technology



Local and remote monitoring provides 24/7 access to device health. Also available in our Powerswitch® safety disconnect switches.



Industrial Grade Plugs and Connectors

- Black & White® Extra Heavy Duty 15-50 A, 125-600 V
- Wetguard® Watertight 15-30 A, 125-600 V
- Rhino-Hide® Rough Service 15-20 A, 125-250 V
- NEMA and Non-NEMA Configurations
- UL/Fed.Spec./CSA/NOM
- Industry leading limited lifetime warranty



Power Strips

- 15-20 A, 125 V
- Commercial, industrial, hospital and medical grade versions
- Surge protective versions
- Variety of outlet configurations
- Multiple cord lengths
- Medical grade power strips with load monitoring Inform™ Technology



Self-Test Portable GFCIs

- 15 and 20 A, 120 V
- Compact right angle plugs available in NEMA 5-15 and 5-20 configurations
- Rainproof, Outdoor rated GFCI Module
- Complies with NEC and OSHA regulations for construction sites
- Automatic and manual reset versions



Wire Mesh Safety Grips

- Pulling grips: galvanized steel, flexible and rotating eye attachments available
- Strain-relief grips: galvanized steel, stainless steel or nylon wire, liquid-tight and dust-tight versions available
- Support grips: tinned bronze, stainless steel or galvanized steel, wide variety of styles



Industrial Grade Weatherproof Covers

- For use with 15, 20, 30 and 50 A devices
- Standard FS/FD mount for box or panel mounting
- IP64 and NEMA 3R rated
- Provisions for OSHA compliant lockout/tagout
- Pre-mounted gasket and stay open feature simplify installation



Portable Outlet Boxes and Covers

- Single- and two-gang, feed-thru and pendant style boxes
- Many cover configurations; flip-lid versions are rated NEMA Type 3R
- Resistant to heat, harsh chemicals and impacts



Visit our Website at:

leviton.com/temporarypower

email: industrial@leviton.com

Q-741G

011624

Leviton Manufacturing Co., Inc.

201 N Service Rd, Melville, NY 11747

Telephone: 1-800-323-8920 • FAX: 1-800-832-9538

Tech Line: 1-800-824-3005 (M-F 8AM-10PM; Sat 9AM-7PM; Sun 9AM-5PM)

© 2024 Leviton Manufacturing Co., Inc. All rights reserved.