

# JC121371

## RGBW Controllers

RGBW 2.4G RF Remote control, Hand Held



### Features & Benefits

- For use with JCC RGBW strip
- Simple, fast installation
- Easy set up and pairing with controllers
- 2.4GHz RF, does not require line of site to operate
- Battery operated; no wiring required
- Up to 30m transmission distance
- Control up to 3 different zones
- Each zone can have matching scenes or a separate scene
- Each zone can run up to 10 controllers
- Each zone can control up to 100m 17.6W RGBW or 250m 7.2W RGBW \*based on 180W driver-must not exceed the maximum Wattage of the driver
- Up to 30 controllers in total
- Up to 300m 17.6W RGBW or 750m 7.2W RGBW \* based on all 3 zones, 30 controllers -with 180W driver
- Built in memory, saves last set scene when turned off
- Smooth touch control to adjust colour and brightness
- 10 dynamic pre-set modes, including 3 colour change, 7 colour change, strobe, and single colour fade options
- 



### General Information

Trade Name	<b>Led Tape</b>
Environment	<b>Indoor</b>
Product Group	<b>LED Strip - accessory</b>
Color Finish	<b>White</b>
Product Shape	<b>Rectangular</b>
Product Range	<b>RGBW Controllers</b>
Overall Dimensions	<b>106 x 52 x 4</b>
Width (mm)	<b>52</b>
Height (mm)	<b>106</b>
Depth (mm)	<b>4</b>
Product Weight(kg)	<b>0.057</b>
Additional Information	<b>Please note: All LED tape can suffer voltage drop over</b>

	distance, depending on configuration of LED tape, DC cable and driver. Any run over 10m may result in up to 2% loss of output per meter thereafter. Consider adding a new power supply every 10m to ensure you achieve the maximum performance of your tape. All the standard length LED tape products can be cut every 50mm if required. It is the installer's responsibility to ensure if the IP65 tape is cut, they maintain the IP rating of the tape by using heatshrink, silicone end caps with suitable silicone sealant where applicable.
IP Rating	IP20
Origin of manufacturer	China
Warranty	2 year standard warranty (See Website for terms and conditions)
Lighting Product Type 1	Accessory
Customs Tariff code**	8543709035

## Electrical

Voltage Rating	2 x 1.5V AAA
----------------	--------------

## Controls and Sensors


Detection Distance	30m
--------------------	-----

## Packaging

Product carton overall dimensions(cm)	11.4 x 5.9 x 1.6
Product Packaged Weight(kg)	0.076
Quantity Per Outer Carton	200
Outer carton(L)- cm	41.50
Outer carton(W)- cm	31.5
Outer carton Net weight- kg	15.20kg
Outer carton Gross weight- kg	15.90kg
Product Bar Code EAN-13 Number	5052544107245
Outer carton Bar Code ITF-14 Number	15052544107242

## Standards & Approvals

CE Marked	Yes
UKCA Marked	Yes
Date code/Purchase order No.	Yes
WEEE Symbol	Yes
Certificate Of Conformity	Available on request
Accredited Members	LIA, ISO9001-2015, ISO14001-2015



\*\*JCC Lighting Limited makes every effort to ensure that the Customs Tariff information in this document is timely and accurate. However, it's not possible for us to assure the absolute veracity and completeness of that information, as errors may occur. The placement of any inaccurate tariff information is completely unintentional. JCC Lighting Limited reserves the right, in its sole discretion, to correct any errors or omissions to the tariff code and to make any and all changes contained in this document at any time and without notice. It is the sole responsibility of the importer to ensure that the commodity code advised is correct for the products/goods being supplied by JCC Lighting Limited. JCC Lighting Limited does not assume any liabilities, losses, costs, and expenses arising out of or related to the importers use of this commodity code or the information related to the import of any JCC Lighting products.

JCC Lighting LTD, Lux Park, Chichester Business Park, City Fields Way, Tangmere, Chichester, West Sussex, PO20 2FT.  
 Sales: 01243 838999 (8am to 5pm Monday to Friday) Fax: 01243 838998 | [sales@jcc.co.uk](mailto:sales@jcc.co.uk) | [www.jcc.co.uk](http://www.jcc.co.uk)  
 Company Registration Number: 03044848 | VAT Number: 918544112