



4

3

2

1



CATALOG # 2310

V0 MAX SINGLE LOCKING RECEPTACLE
 20 AMP, 125 VOLT, GROUNDING,
 2 POLE, 3 WIRE, NEMA L5-20R

UNLESS OTHERWISE SPECIFIED:
 DO NOT SCALE DRAWING.
 ALL DIMENSIONS ARE IN INCHES.
 ALL ANGLES ARE IN DEGREES.



TOLERANCES	
INCH	METRIC
.XX ± .01	.X ± .2 mm
.XXX ± .005	.XX ± .1 mm

TITLE:
**2310 V0 MAX FR CATALOG
 DRAWING FOR NEMA L5-20**

ANGLES: ± 1/2°

DWG NO.
CATSTD-02310-0XX-D01



THIRD ANGLE PROJECTION	SIZE	SCALE:1:1	SHEET 1 OF 1	REV
	B			1

ALL PRINTED COPIES
 ARE UNCONTROLLED

Copyright 2020. Unpublished. All Rights Reserved.

4

3

2

1

B

B

A

A