



CATALOG # 2415 FLANGED INLET

20A NEMA L14-20 3 POLE, 4 WIRE
 20A 125/250V GROUNDING

UNLESS OTHERWISE SPECIFIED: DO NOT SCALE DRAWING. ALL DIMENSIONS ARE IN INCHES. ALL ANGLES ARE IN DEGREES.		LEVITON		
TOLERANCES		TITLE: CAT #2415 FLANGED INLET 20A NEMA L14-20 4 WIRE		
INCH	METRIC	DWG NO. CATSTD-02415-000-D01		
.XX ± .01	.X ± .2 mm	SIZE	SCALE:1:1	SHEET 1 OF 1
.XXX ± .005	.XX ± .1 mm	B	Copyright 2019. Unpublished. All Rights Reserved.	
ANGLES: ± 1/2°		REV 1		
THIRD ANGLE PROJECTION				
ALL PRINTED COPIES ARE UNCONTROLLED				