



## CATALOG # 2426

20 AMP, 250 VOLT 3-PHASE, GROUNDING  
 FLANGED OUTLET LOCKING RECEPTACLE  
 NEMA L15-20R, 3 POLE, 4 WIRE

UNLESS OTHERWISE SPECIFIED: DO NOT SCALE DRAWING. ALL DIMENSIONS ARE IN INCHES. ALL ANGLES ARE IN DEGREES.		<b>LEVITON</b>										
<table border="1"> <tr> <th colspan="2">TOLERANCES</th> </tr> <tr> <th>INCH</th> <th>METRIC</th> </tr> <tr> <td>.XX ± .01</td> <td>.X ± .2 mm</td> </tr> <tr> <td>.XXX ± .005</td> <td>.XX ± .1 mm</td> </tr> </table>		TOLERANCES		INCH	METRIC	.XX ± .01	.X ± .2 mm	.XXX ± .005	.XX ± .1 mm	TITLE: 2426 20A FLANGED OUTLET NEMA L15-20 CATALOG		
TOLERANCES												
INCH	METRIC											
.XX ± .01	.X ± .2 mm											
.XXX ± .005	.XX ± .1 mm											
<table border="1"> <tr> <td colspan="2">ANGLES: ± 1/2°</td> </tr> <tr> <td colspan="2">THIRD ANGLE PROJECTION</td> </tr> <tr> <td></td> <td></td> </tr> </table>		ANGLES: ± 1/2°		THIRD ANGLE PROJECTION				DWG NO. CATSTD-02426-000-D01				
ANGLES: ± 1/2°												
THIRD ANGLE PROJECTION												
<table border="1"> <tr> <td>ALL PRINTED COPIES ARE UNCONTROLLED</td> <td>SIZE <b>B</b></td> <td>SCALE: 1:1</td> <td>SHEET 1 OF 1</td> <td>REV 1</td> </tr> </table>		ALL PRINTED COPIES ARE UNCONTROLLED	SIZE <b>B</b>	SCALE: 1:1	SHEET 1 OF 1	REV 1	Copyright 2020. Unpublished. All Rights Reserved.					
ALL PRINTED COPIES ARE UNCONTROLLED	SIZE <b>B</b>	SCALE: 1:1	SHEET 1 OF 1	REV 1								