

4



3

2

1

B

B



CATALOG #2620  
 3 WIRE V0 MAX  
 L6-30 FLUSH  
 RECEPTACLE

UPPER VALUES = INCHES  
 LOWER VALUES = MM

A

A

UNLESS OTHERWISE SPECIFIED: DO NOT SCALE DRAWING. ALL DIMENSIONS ARE IN INCHES. ALL ANGLES ARE IN DEGREES.		<b>LEVITON</b> <sup>®</sup>		
TOLERANCES		TITLE: 2620 V0 MAX FR CATALOG DRAWING FOR NEMA L6-30		
<b>INCH</b>	<b>METRIC</b>	DWG NO. CATSTD-02620-000-D01		
.XX ± .01 .XXX ± .005	.X ± .2 mm .XX ± .1 mm			
ANGLES: ± 1/2°		SIZE: <b>B</b> SCALE: 1:1    SHEET 1 OF 1    REV 1		
THIRD ANGLE PROJECTION 				
ALL PRINTED COPIES ARE UNCONTROLLED		Copyright 2019. Unpublished. All Rights Reserved.		

4

3

2

1