



4

3

2

1



CATALOG # 2776

30A 347/600 VOLT 3 PHASE FLANGED OUTLET
NEMA L20-30R, 4 POLE, 4 WIRE, NON-GROUNDING

UNLESS OTHERWISE SPECIFIED:
DO NOT SCALE DRAWING.
ALL DIMENSIONS ARE IN INCHES.
ALL ANGLES ARE IN DEGREES.


LEVITON

TOLERANCES	
INCH	METRIC
.XX ± .01	.X ± .2 mm
.XXX ± .005	.XX ± .1 mm

TITLE:
**FLNG OUTLET, NEMA L20-30R
CATALOG DRAWING**

ANGLES: ± 1/2°
THIRD ANGLE PROJECTION

DWG NO.
CATSTD-02776-000-D01



SIZE B	SCALE: 1:1	SHEET 1 OF 1	REV 1
------------------	------------	--------------	-----------------

ALL PRINTED COPIES
ARE UNCONTROLLED

Copyright 2019. Unpublished. All Rights Reserved.

4

3

2

1

B

B

A

A