



4 3 2 1



CATALOG #5032

SINGLE RECEPTACLE, 3 POLE, 3 WIRE
 20A-125V/250V, NEMA 10-20R
 COMMERCIAL SPEC GRADE
 FLUSH MOUNT

UNLESS OTHERWISE SPECIFIED:
 DO NOT SCALE DRAWING.
 ALL DIMENSIONS ARE IN INCHES.
 ALL ANGLES ARE IN DEGREES.




TOLERANCES	
INCH	METRIC
.XX ± .01	.X ± .2 mm
.XXX ± .005	.XX ± .1 mm

TITLE:
**#5032 SINGLE RECEPTACLE
 CATALOG DWG. NEMA 10-20R**

ANGLES: ± 1/2°

DWG NO.
CATSTD-05032-00X-D01



THIRD ANGLE PROJECTION	SIZE	SCALE: 1:1	SHEET 1 OF 1	REV
ALL PRINTED COPIES ARE UNCONTROLLED	B	Copyright 2019. Unpublished. All Rights Reserved.		1

4 3 2 1

B

B

A

A