



### CATALOG # 5279-C

15 AMP, 125 VOLT, GROUNDING,  
 FLANGED OUTLET RECEPTACLE  
 NEMA 5-15R, 2 POLE, 3 WIRE,  
 STRAIGHT BLADE

UNLESS OTHERWISE SPECIFIED: DO NOT SCALE DRAWING. ALL DIMENSIONS ARE IN INCHES. ALL ANGLES ARE IN DEGREES.		<b>LEVITON</b>		
TOLERANCES		TITLE: 5279-C FLANGED OUTLET 15A NEMA 5-15 CATALOG		
INCH	METRIC	DWG NO. CATSTD-05279-00C-M01		
.XX ± .01 .XXX ± .005	.X ± .2 mm .XX ± .1 mm			
ANGLES: ± 1/2°		SIZE	SCALE: 1:1	SHEET 1 OF 1
THIRD ANGLE PROJECTION		<b>B</b>	Copyright 2020. Unpublished. All Rights Reserved.	REV 1
ALL PRINTED COPIES ARE UNCONTROLLED				