



CATALOG #CR20
 2 POLE, 3 WIRE
 20A-125V NEMA 5-20R
 DUPLEX RECEPTACLE

UPPER VALUES = INCHES
 LOWER VALUES = MM

UNLESS OTHERWISE SPECIFIED: DO NOT SCALE DRAWING. ALL DIMENSIONS ARE IN INCHES. ALL ANGLES ARE IN DEGREES.		LEVITON®		
TOLERANCES		TITLE: 0CR20 DUPLEX RECEPTACLE CATALOG DRAWING		
INCH .XX ± .01 .XXX ± .005	METRIC .X ± .2 mm .XX ± .1 mm	DWG NO. CATSTD-0CR20-000-D01		
ANGLES: ± 1/2°		SIZE	SCALE: 1:1	SHEET 1 OF 1
THIRD ANGLE PROJECTION 		B	Copyright 2019. Unpublished. All Rights Reserved.	
ALL PRINTED COPIES ARE UNCONTROLLED				REV 1