



4

3

2

1



### CATALOG # 16362-HG

DECORA PLUS DUPLEX RECEPTACLE,  
 2 POLE, 3 WIRE, 20AMP, 125 VOLT  
 SELF-GROUNDING, HOSPITAL GRADE,  
 NEMA 5-20R

UNLESS OTHERWISE SPECIFIED:  
 DO NOT SCALE DRAWING.  
 ALL DIMENSIONS ARE IN INCHES.  
 ALL ANGLES ARE IN DEGREES.


# LEVITON®

TOLERANCES	
INCH	METRIC
.XX ± .01	.X ± .2 mm
.XXX ± .005	.XX ± .1 mm

TITLE:  
**HG DECORA RECEPTACLE  
 CATALOG DRAWING**

ANGLES: ± 1/2°  
 THIRD ANGLE PROJECTION

DWG NO.  
**CATSTD-16362-HGX-D01**



SIZE	SCALE:1:1	SHEET 1 OF 1	REV
<b>B</b>	Copyright 2020. Unpublished. All Rights Reserved.		<b>1</b>

ALL PRINTED COPIES  
 ARE UNCONTROLLED

4

3

2

1