



30 AMP, 277/480 VOLT, 3-PHASE Y,  
NEMA L22-30, 4 POLE, 5 WIRE,  
GROUNDING,  
SINGLE LOCKING INLET

30A 5W WETGUARD FLANGED  
INLET COVER FOR CAT. No. 68W82

UNLESS OTHERWISE SPECIFIED: DO NOT SCALE DRAWING. ALL DIMENSIONS ARE IN INCHES. ALL ANGLES ARE IN DEGREES.		<b>LEVITON</b>		
TOLERANCES		TITLE: <b>68W82 WETGUARD FLANGED INLET COVER NEMA L22-30</b>		
<b>INCH</b>	<b>METRIC</b>	DWG NO. <b>CATSTD-68W82-000-D01</b>		
.XX ± .01 .XXX ± .005	.X ± .2 mm .XX ± .1 mm			
<b>ANGLES: ± 1/2°</b>		SIZE <b>B</b>		
THIRD ANGLE PROJECTION 				
<b>ALL PRINTED COPIES ARE UNCONTROLLED</b>		SCALE: 1:1	SHEET 1 OF 1	REV <b>1</b>
		Copyright 2019. Unpublished. All Rights Reserved.		