

**GFNT2-DIN**

DIN RAIL GFCI RECEPTACLE 20A-120V AC  
 MODULE 20A-120V AC FEED THRU  
 WITH GREEN LED POWER INDICATOR LIGHT.  
 DIN-RAIL MOUNTABLE.  
 TERMINAL BLOCK PROVIDED FOR INPUT/OUTPUT  
 (#10-#12 AWG SOLID OR STRANDED)


UNLESS OTHERWISE SPECIFIED:  
 DO NOT SCALE DRAWING.  
 ALL DIMENSIONS ARE IN INCHES.  
 ALL ANGLES ARE IN DEGREES.

**TOLERANCES**

INCH	METRIC
.XX ± .01	.X ± .2 mm
.XXX ± .005	.XX ± .1 mm

**ANGLES:** ± 1/2°

THIRD ANGLE PROJECTION



**ALL PRINTED COPIES  
 ARE UNCONTROLLED**



TITLE:  
**GFNT2-DIN CATALOG  
 DIN-RAIL SELF-TEST GFCI**

DWG NO.  
**CATSTD-GFNT2-DIN-D01**

SIZE <b>B</b>	SCALE: 1:1	SHEET 1 OF 1	REV <b>1</b>
------------------	------------	--------------	-----------------

Copyright 2019. Unpublished. All Rights Reserved.