

4

3

2

1

B




B

A

A

A

A



**NOTES:**

1. UPPER DIMENSIONS ARE IN INCHES. LOWER DIMENSIONS ARE IN MILLIMETERS.
2. USB RECEPTACLE WITH (2) TYPE A PORTS, 5 VDC, 3.6 A (COMBINED TOTAL).
3. USE ONLY WITH CAT. #MSTWL LEV-LOK RECEPTACLE WIRING MODULE.
4. SEE CATSTD-M56AA-HG0-D02 DRAWING FOR RECEPTACLE WITH WIRING MODULE ASSEMBLED.

UNLESS OTHERWISE SPECIFIED:  
DO NOT SCALE DRAWING.  
ALL DIMENSIONS ARE IN INCHES.  
ALL ANGLES ARE IN DEGREES.

TOLERANCES	
INCH	METRIC
.XX ± .01	.X ± .2 mm
.XXX ± .005	.XX ± .1 mm

ANGLES: ± 1/2°  
THIRD ANGLE PROJECTION

ALL PRINTED COPIES ARE UNCONTROLLED

**LEVITON®**

TITLE:  
**LEV-LOK USB RECEPTACLE  
15A-125VAC HOSPITAL GRADE**

DWG NO.  
**CATSTD-M56AA-HG0-D01**

SIZE <b>B</b>	SCALE: 1:1	SHEET 1 OF 1	REV <b>1</b>
------------------	------------	--------------	-----------------

Copyright 2019. Unpublished. All Rights Reserved.

4

3

2

1