

4

3

2

1

B




B

A

A

A

A



**NOTES:**

1. UPPER DIMENSIONS ARE IN INCHES. LOWER DIMENSIONS ARE IN MILLIMETERS.
2. RECEPTACLE RATING: 15A - 125V AC HOSPITAL GRADE.
3. USB RECEPTACLE WITH (2) TYPE A PORTS, 5 VDC, 3.6 A (COMBINED TOTAL).
4. USE ONLY WITH CAT. #MSTWL LEV-LOK RECEPTACLE WIRING MODULE.
5. SEE CATSTD-M56AA-HG0-D01 DRAWING FOR RECEPTACLE LESS WIRING MODULE.

UNLESS OTHERWISE SPECIFIED: DO NOT SCALE DRAWING. ALL DIMENSIONS ARE IN INCHES. ALL ANGLES ARE IN DEGREES.		<b>LEVITON®</b>		
TOLERANCES		TITLE: <b>LEV-LOK USB RECEPTACLE WITH WIRING MODULE</b>		
<b>INCH</b>	<b>METRIC</b>	DWG NO. <b>CATSTD-M56AA-HG0-D02</b>		
.XX ± .01 .XXX ± .005	.X ± .2 mm .XX ± .1 mm			
ANGLES: ± 1/2°		SIZE	SCALE: 1:1	SHEET 1 OF 1
THIRD ANGLE PROJECTION		<b>B</b>	Copyright 2019. Unpublished. All Rights Reserved.	REV <b>1</b>
ALL PRINTED COPIES ARE UNCONTROLLED				

4

3

2

1