

4

3

2

1

B


B

A

A



A

A



STRAP, ZINC PLATED (GALVANIZED)
STEEL WITH REMOVABLE EARS

SELF GROUNDING CLIP,
BRASS



NOTES:

- UPPER DIMENSIONS ARE IN INCHES.
LOWER DIMENSIONS ARE IN MILLIMETERS.
- USB RECEPTACLE WITH (1) TYPE A & (1) TYPE C PORT,
5 VDC, 5.1 A (COMBINED TOTAL).
- USE ONLY WITH CAT. #MSTWL LEV-LOK RECEPTACLE
WIRING MODULE.
- SEE CATSTD-M56AC-000-D02 DRAWING FOR
RECEPTACLE WITH WIRING MODULE ASSEMBLED.


UNLESS OTHERWISE SPECIFIED:
DO NOT SCALE DRAWING.
ALL DIMENSIONS ARE IN INCHES.
ALL ANGLES ARE IN DEGREES.

TOLERANCES

INCH	METRIC
.XX ± .01	.X ± .2 mm
.XXX ± .005	.XX ± .1 mm

ANGLES: ± 1/2°

THIRD ANGLE PROJECTION



ALL PRINTED COPIES
ARE UNCONTROLLED

LEVITON®

TITLE:
**LEV-LOK USB RECEPTACLE
15A-125VAC SPEC GRADE**

DWG NO.
CATSTD-M56AC-000-D01

SIZE B	SCALE: 1:1	SHEET 1 OF 1	REV 1
------------------	------------	--------------	-----------------

Copyright 2019. Unpublished. All Rights Reserved.

4

3

2

1