

4

3

2

1

B




B

A

A

A

A



STRAP, ZINC PLATED (GALVANIZED) STEEL WITH REMOVABLE EARS

SELF GROUNDING CLIP, BRASS

#6-32 MOUNTING SCREW, ZINC PLATED STEEL (2 PL)

CAT. #MSTWL WIRING MODULE

**NOTES:**

1. UPPER DIMENSIONS ARE IN INCHES. LOWER DIMENSIONS ARE IN MILLIMETERS.
2. RECEPTACLE RATING: 15A - 125V AC SPEC GRADE.
3. USB RECEPTACLE WITH (1) TYPE A & (1) TYPE C PORT, 5 VDC, 5.1 A (COMBINED TOTAL).
4. USE ONLY WITH CAT. #MSTWL LEV-LOK RECEPTACLE WIRING MODULE.
5. SEE CATSTD-M56AC-000-D01 DRAWING FOR RECEPTACLE LESS WIRING MODULE.

UNLESS OTHERWISE SPECIFIED:  
DO NOT SCALE DRAWING.  
ALL DIMENSIONS ARE IN INCHES.  
ALL ANGLES ARE IN DEGREES.

TOLERANCES	
<b>INCH</b>	<b>METRIC</b>
.XX ± .01	.X ± .2 mm
.XXX ± .005	.XX ± .1 mm
<b>ANGLES: ± 1/2°</b>	
THIRD ANGLE PROJECTION	
<b>ALL PRINTED COPIES ARE UNCONTROLLED</b>	

**LEVITON®**

TITLE:  
**LEV-LOK USB RECEPTACLE WITH WIRING MODULE**

DWG NO.  
**CATSTD-M56AC-000-D02**

SIZE <b>B</b>	SCALE:1:1	SHEET 1 OF 1	REV <b>1</b>
Copyright 2019. Unpublished. All Rights Reserved.			

4

3

2

1