

4

3

2

1

B


B

A

A


A

A




STRAP, ZINC PLATED (GALVANIZED) STEEL WITH REMOVABLE EARS

SELF GROUNDING CLIP, BRASS



#6-32 MOUNTING SCREW, ZINC PLATED STEEL (2 PL)



CAT. #MSTWL WIRING MODULE

**NOTES:**

- 1. UPPER DIMENSIONS ARE IN INCHES. LOWER DIMENSIONS ARE IN MILLIMETERS.
- 2. RECEPTACLE RATING: 20A - 125V AC SPEC GRADE.
- 3. USB RECEPTACLE WITH (2) TYPE A PORTS, 5 VDC, 3.6 A (COMBINED TOTAL).
- 4. USE ONLY WITH CAT. #MSTWL LEV-LOK RECEPTACLE WIRING MODULE.
- 5. SEE CATSTD-M58AA-000-D01 DRAWING FOR RECEPTACLE LESS WIRING MODULE.

UNLESS OTHERWISE SPECIFIED:  
DO NOT SCALE DRAWING.  
ALL DIMENSIONS ARE IN INCHES.  
ALL ANGLES ARE IN DEGREES.

TOLERANCES	
INCH	METRIC
.XX ± .01	.X ± .2 mm
.XXX ± .005	.XX ± .1 mm

ANGLES: ± 1/2°

THIRD ANGLE PROJECTION



ALL PRINTED COPIES ARE UNCONTROLLED

**LEVITON®**

TITLE:  
**LEV-LOK USB RECEPTACLE WITH WIRING MODULE**

DWG NO.  
**CATSTD-M58AA-000-D02**

SIZE <b>B</b>	SCALE: 1:1	SHEET 1 OF 1	REV <b>1</b>
------------------	------------	--------------	-----------------

Copyright 2019. Unpublished. All Rights Reserved.

4

3

2

1