

4

3

2




1

B

B

A

A

**NOTES:**

- UPPER DIMENSIONS ARE IN INCHES.  
LOWER DIMENSIONS ARE IN MILLIMETERS.
- USB RECEPTACLE WITH (2) TYPE A PORTS, 5 VDC, 3.6 A (COMBINED TOTAL).
- USE ONLY WITH CAT. #MSTWL LEV-LOK RECEPTACLE WIRING MODULE.
- SEE CATSTD-M58AA-HG0-D02 DRAWING FOR RECEPTACLE WITH WIRING MODULE ASSEMBLED.

UNLESS OTHERWISE SPECIFIED: DO NOT SCALE DRAWING. ALL DIMENSIONS ARE IN INCHES. ALL ANGLES ARE IN DEGREES.		<div><div></div><div>LEVITON®</div></div>		
TOLERANCES		TITLE: LEV-LOK USB RECEPTACLE 20A-125VAC SPEC GRADE		
INCH	METRIC	DWG NO. CATSTD-M58AA-HG0-D01		
.XX ± .01 .XXX ± .005	.X ± .2 mm .XX ± .1 mm			
ANGLES: ± 1/2°		REV 1		
THIRD ANGLE PROJECTION				
<div><div><div></div><div></div></div><div><div></div><div></div></div></div>				
ALL PRINTED COPIES ARE UNCONTROLLED		SIZE B	SCALE:1:1	SHEET 1 OF 1
		Copyright 2019. Unpublished. All Rights Reserved.		