

4

3

2

1

B


B

A

A


A

A




STRAP, ZINC PLATED (GALVANIZED) STEEL WITH REMOVABLE EARS

SELF GROUNDING CLIP, BRASS



#6-32 MOUNTING SCREW, ZINC PLATED STEEL (2 PL)



CAT. #MSTWL WIRING MODULE

NOTES:

1. UPPER DIMENSIONS ARE IN INCHES. LOWER DIMENSIONS ARE IN MILLIMETERS.
2. RECEPTACLE RATING: 20A - 125V AC HOSPITAL GRADE.
3. USB RECEPTACLE WITH (2) TYPE A PORTS, 5 VDC, 3.6 A (COMBINED TOTAL).
4. USE ONLY WITH CAT. #MSTWL LEV-LOK RECEPTACLE WIRING MODULE.
5. SEE CATSTD-M58AA-HG0-D01 DRAWING FOR RECEPTACLE LESS WIRING MODULE.

UNLESS OTHERWISE SPECIFIED:
DO NOT SCALE DRAWING.
ALL DIMENSIONS ARE IN INCHES.
ALL ANGLES ARE IN DEGREES.

TOLERANCES	
INCH	METRIC
.XX ± .01	.X ± .2 mm
.XXX ± .005	.XX ± .1 mm
ANGLES: ± 1/2°	
THIRD ANGLE PROJECTION	
ALL PRINTED COPIES ARE UNCONTROLLED	

LEVITON®

TITLE:
LEV-LOK USB RECEPTACLE WITH WIRING MODULE

DWG NO.
CATSTD-M58AA-HG0-D02

SIZE B	SCALE: 1:1	SHEET 1 OF 1	REV 1
------------------	------------	--------------	-----------------

Copyright 2019. Unpublished. All Rights Reserved.

4

3

2

1