

4

3

2

1

B




B

A

A

A

A



STRAP, ZINC PLATED (GALVANIZED) STEEL WITH REMOVABLE EARS

SELF GROUNDING CLIP, BRASS

NOTES:

- UPPER DIMENSIONS ARE IN INCHES. LOWER DIMENSIONS ARE IN MILLIMETERS.
- USB RECEPTACLE WITH (1) TYPE A & (1) TYPE C PORT, 5 VDC, 5.1 A (COMBINED TOTAL).
- USE ONLY WITH CAT. #MSTWL LEV-LOK RECEPTACLE WIRING MODULE.
- SEE CATSTD-M58AC-000-D02 DRAWING FOR RECEPTACLE WITH WIRING MODULE ASSEMBLED.

UNLESS OTHERWISE SPECIFIED:
DO NOT SCALE DRAWING.
ALL DIMENSIONS ARE IN INCHES.
ALL ANGLES ARE IN DEGREES.

TOLERANCES	
INCH	METRIC
.XX ± .01	.X ± .2 mm
.XXX ± .005	.XX ± .1 mm
ANGLES: ± 1/2°	
THIRD ANGLE PROJECTION	
ALL PRINTED COPIES ARE UNCONTROLLED	



TITLE:
**LEV-LOK USB RECEPTACLE
20A-125VAC SPEC GRADE**

DWG NO.
CATSTD-M58AC-000-D01

SIZE B	SCALE:1:1	SHEET 1 OF 1	REV 1
Copyright 2019. Unpublished. All Rights Reserved.			

4

3

2

1