

4

3

2

1

B

B

A

A

A




A

4

3

2

1



CAT. #MSTWL WIRING MODULE

STRAP, ZINC PLATED (GALVANIZED) STEEL WITH REMOVABLE EARS

SELF GROUNDING CLIP, BRASS

#6-32 MOUNTING SCREW, ZINC PLATED STEEL (2 PL)

NOTES:


- 1. UPPER DIMENSIONS ARE IN INCHES. LOWER DIMENSIONS ARE IN MILLIMETERS.
- 2. RECEPTACLE RATING: 20A - 125V AC SPEC GRADE.
- 3. USB RECEPTACLE WITH (1) TYPE A & (1) TYPE C PORT, 5 VDC, 5.1 A (COMBINED TOTAL).
- 4. USE ONLY WITH CAT. #MSTWL LEV-LOK RECEPTACLE WIRING MODULE.
- 5. SEE CATSTD-M58AC-000-D01 DRAWING FOR RECEPTACLE LESS WIRING MODULE.

UNLESS OTHERWISE SPECIFIED:
DO NOT SCALE DRAWING.
ALL DIMENSIONS ARE IN INCHES.
ALL ANGLES ARE IN DEGREES.

TOLERANCES	
INCH	METRIC
.XX ± .01	.X ± .2 mm
.XXX ± .005	.XX ± .1 mm

ANGLES: ± 1/2°

THIRD ANGLE PROJECTION



ALL PRINTED COPIES ARE UNCONTROLLED

LEVITON

TITLE:
LEV-LOK USB RECEPTACLE WITH WIRING MODULE

DWG NO.
CATSTD-M58AC-000-D02

SIZE B	SCALE:1:1	SHEET 1 OF 1	REV 1
------------------	-----------	--------------	-----------------

Copyright 2019. Unpublished. All Rights Reserved.