

4

3

2

1

B




B

A

A

A

A



STRAP, ZINC PLATED (GALVANIZED) STEEL WITH REMOVABLE EARS

SELF GROUNDING CLIP, BRASS

NOTES:

- UPPER DIMENSIONS ARE IN INCHES. LOWER DIMENSIONS ARE IN MILLIMETERS.
- USB RECEPTACLE WITH (1) TYPE A & (1) TYPE C PORT, 5 VDC, 5.1 A (COMBINED TOTAL).
- USE ONLY WITH CAT. #MSTWL LEV-LOK RECEPTACLE WIRING MODULE.
- SEE CATSTD-M58AC-HG0-D02 DRAWING FOR RECEPTACLE WITH WIRING MODULE ASSEMBLED.

UNLESS OTHERWISE SPECIFIED:
DO NOT SCALE DRAWING.
ALL DIMENSIONS ARE IN INCHES.
ALL ANGLES ARE IN DEGREES.

TOLERANCES	
INCH	METRIC
.XX ± .01	.X ± .2 mm
.XXX ± .005	.XX ± .1 mm

ANGLES: ± 1/2°

THIRD ANGLE PROJECTION

ALL PRINTED COPIES ARE UNCONTROLLED



TITLE:
**LEV-LOK USB RECEPTACLE
20A-125VAC HOSPITAL GRADE**

DWG NO.
CATSTD-M58AC-HG0-D01

SIZE B	SCALE:1:1	SHEET 1 OF 1	REV 1
------------------	-----------	--------------	-----------------

Copyright 2019. Unpublished. All Rights Reserved.

4

3

2

1