


CATALOG # T1626-IG

DECORA PLUS DUPLEX RECEPTACLE,
ISOLATED GROUND, 2 POLE, 3 WIRE,
15 AMP, 125 VOLT, SELF-GROUNDING,
SPEC GRADE, TAMPER-RESISTANT,
NEMA 5-15R

UNLESS OTHERWISE SPECIFIED:
DO NOT SCALE DRAWING.
ALL DIMENSIONS ARE IN INCHES.
ALL ANGLES ARE IN DEGREES.

| TOLERANCES | |
|-------------|-------------|
| INCH | METRIC |
| .XX ± .01 | .X ± .2 mm |
| .XXX ± .005 | .XX ± .1 mm |

ANGLES: ± 1/2°
THIRD ANGLE PROJECTION



ALL PRINTED COPIES ARE UNCONTROLLED

LEVITON

TITLE:
**IG DECORA RECEPTACLE
CATALOG DRAWING**

DWG NO.
CATSTD-T1626-IGX-D01

| | | | |
|------------------|-----------|--------------|-----------------|
| SIZE B | SCALE:1:1 | SHEET 1 OF 1 | REV 1 |
|------------------|-----------|--------------|-----------------|

Copyright 2020. Unpublished. All Rights Reserved.