

4

3

2



1

B

B

A

A



### CATALOG # T1636-IG

DECORA PLUS DUPLEX RECEPTACLE,  
 ISOLATED GROUND, 2 POLE, 3 WIRE,  
 20 AMP, 125 VOLT, SELF-GROUNDING,  
 SPEC GRADE, TAMPER-RESISTANT,  
 NEMA 5-20R

UNLESS OTHERWISE SPECIFIED: DO NOT SCALE DRAWING. ALL DIMENSIONS ARE IN INCHES. ALL ANGLES ARE IN DEGREES.		<b>LEVITON</b> TITLE: T1636-IG DECORA RECEPT. CATALOG DRAWING		
TOLERANCES		DWG NO. CATSTD-T1636-IGX-D01		
<b>INCH</b>	<b>METRIC</b>	<b>SIZE</b>	SCALE:1:1	SHEET 1 OF 1
.XX ± .01	.X ± .2 mm	<b>B</b>	Copyright 2020. Unpublished. All Rights Reserved.	
.XXX ± .005	.XX ± .1 mm			REV 1
ANGLES: ± 1/2°				
THIRD ANGLE PROJECTION				
ALL PRINTED COPIES ARE UNCONTROLLED				

4

3

2

1