



4

3

2

1



UPPER VALUES = INCHES  
 LOWER VALUES = MM

**CATALOG #T5020-W**  
 125V, 20A, NEMA 5-20R  
 2P, 3W TAMPER RESISTANT  
 SINGLE RECEPTACLE OUTLET

UNLESS OTHERWISE SPECIFIED: DO NOT SCALE DRAWING. ALL DIMENSIONS ARE IN INCHES. ALL ANGLES ARE IN DEGREES.		<b>LEVITON®</b>		
TOLERANCES		TITLE: <b>SINGLE RECEPTACLE 20A TR CATALOG DRAWING</b>		
<b>INCH</b> .XX ± .01 .XXX ± .005	<b>METRIC</b> .X ± .2 mm .XX ± .1 mm	DWG NO. <b>CATSTD-T5020-00W-D01</b>		
ANGLES: ± 1/2°		SIZE	SCALE:1:1	SHEET 1 OF 1
THIRD ANGLE PROJECTION 		<b>B</b>	Copyright 2019. Unpublished. All Rights Reserved.	REV <b>1</b>
ALL PRINTED COPIES ARE UNCONTROLLED				

4

3

2

1

B

B

A

A