

4

3

2

1

D

D

C


C

B

B


A

A



63A SHOWN

NOTE:
 UPPER VALUE = INCHES
 LOWER VALUE = METRIC
 DIMENSIONS ARE FOR REFERENCE ONLY



125A SHOWN

Catalog Number	VOLTAGE	COLOR	CLOCK (Hr)
0W263-0R6	200 -250V	BLUE	
W2125-0R6			
0W363-0R9	200 -250V	BLUE	
W3125-0R9			
0W463-0R9	208 -250V	BLUE	
W4125-0R9			
0W363-0R6	380 - 415V	RED	
W3125-0R6			
0W363-R11	440 - 460V	RED	
W3125-R11			
0W463-0R6	346 - 415V	RED	
W4125-0R6			
0W463-R11	440 - 460V	RED	
W4125-R11			

INTERNATIONAL PIN & SLEEVE RECEPTACLE
 IEC/EN 60309-1 & 60309-2, INTERNATIONAL
 CONFIGURATION PANEL MOUNTING SOCKET OUTLET,
 IP66/67, Watertight

STATUS: In Work					<p>The information in this document is the exclusive PROPRIETARY property of LEVITON MFG. CO., INC. It is disclosed with the understanding that acceptance or review by the recipient constitutes an undertaking by the recipient: (1) to hold this information in strict confidence. (2) not to disclose, duplicate, copy, or use the information, in whole or in part, for any purpose other than that for which disclosed. Copyright 2010. Unpublished. All Rights Reserved.</p>	UNLESS OTHERWISE SPECIFIED: DO NOT SCALE DRAWING. ALL DIMENSIONS ARE IN INCHES. ALL ANGLES ARE IN DEGREES.		TITLE: FLUSH MTG RECEPTACLE 63A/125A CATALOG ASSEMBLY					
REV.	DATE	ECO NUMBER	CHGD	APVD		TOLERANCES INCH .XX ± .01 .X ± .2 mm .XXX ± .005 .XX ± .1 mm METRIC .X ± .2 mm .XX ± .1 mm		ANGLES: ± 1/2° THIRD ANGLE PROJECTION		DWN BY	PR	02/15/2023	ENGRG
1	-	-	-	-	ALL PRINTED COPIES ARE UNCONTROLLED		DWG NO. ORA7007-D02		CHK BY	-	MFG	-	-
-	-	-	-	-					SIZE	PROJECT NO.	PROJ-02986	REV	1
-	-	-	-	-					C	SCALE:1:1	SHEET 1 OF 1		

4

3

2

1