


Ø0.170 in
Ø[4 mm]
(4 PL)

3.75 in
[95 mm]

3.12 in
[79 mm]

3.12 in
[79 mm]


3.75 in
[95 mm]



UNLESS OTHERWISE SPECIFIED:
DO NOT SCALE DRAWING.
ALL DIMENSIONS ARE IN INCHES.
ALL ANGLES ARE IN DEGREES.

TOLERANCES	
INCH	METRIC
.XX ± .01	.X ± .2 mm
.XXX ± .005	.XX ± .1 mm

ANGLES: ± 1/2°
THIRD ANGLE PROJECTION



ALL PRINTED COPIES
ARE UNCONTROLLED

LEVITON®

TITLE:
20A Receptacle 3 Wire
-

DWG NO.
ORB4707-D02

SIZE B	SCALE:1:2	SHEET 1 OF 1	REV 1
------------------	-----------	--------------	-----------------

Copyright 2019. Unpublished. All Rights Reserved.