



CATALOG #	AMPS	VOLTAGE	DESCRIPTION
DCR15	15A	125V	DECORA DUPLEX RECEPTACLE , NON-TR, 2-POLE, 3-WIRE, GROUNDING, NEMA 5-15R, SIDE WIRE
DBR15	15A	125V	DECORA DUPLEX RECEPTACLE , NON-TR, 2-POLE, 3-WIRE, GROUNDING, NEMA 5-15R, BACK & SIDE WIRE
DCBR1	15A	125V	DECORA DUPLEX RECEPTACLE , NON-TR, 2-POLE, 3-WIRE, GROUNDING, NEMA 5-15R, BACK & SIDE WIRE
DCR20	20A	125V	DECORA DUPLEX RECEPTACLE , NON-TR, 2-POLE, 3-WIRE, GROUNDING, NEMA 5-20R, SIDE WIRED
DBR20	20A	125V	DECORA DUPLEX RECEPTACLE , NON-TR, 2-POLE, 3-WIRE, GROUNDING, NEMA 5-20R, BACK & SIDE WIRED
DCBR2	20A	125V	DECORA DUPLEX RECEPTACLE , NON-TR, 2-POLE, 3-WIRE, GROUNDING, NEMA 5-20R, BACK & SIDE WIRED

CATALOG DCR20 SHOWN

"NON-TR" NON-TAMPER RESISTANT
DECORA DUPLEX RECEPTACLE

DIMENSIONS ARE IN INCHES,
DIMENSIONS IN BRACKET ARE IN MM

UNLESS OTHERWISE SPECIFIED: DO NOT SCALE DRAWING. ALL DIMENSIONS ARE IN INCHES. ALL ANGLES ARE IN DEGREES.		LEVITON	
TOLERANCES		TITLE: DECORA DUPLEX RECEPTACLE NON-TR WEBSITE DRAWING	
INCH .XX ± .01 .XXX ± .005	METRIC .X ± .2 mm .XX ± .1 mm	DWG NO. ORC6949-D01	
ANGLES: ± 1/2°		SIZE: B SCALE: 1:1 SHEET 1 OF 1 REV A	
THIRD ANGLE PROJECTION 		Copyright 2020. Unpublished. All Rights Reserved.	
ALL PRINTED COPIES ARE UNCONTROLLED			