



CATALOG #	AMPS	VOLTAGE	DESCRIPTION
DTB15	15A	125V	DECORA DUPLEX RECEPTACLE, TR, 2-POLE 3-WIRE, GROUNDING, NEMA 5-15R, BACK & SIDE WIRED
TDBR1	15A	125V	DECORA DUPLEX RECEPTACLE, TR, 2-POLE 3-WIRE, GROUNDING, NEMA 5-15R, BACK & SIDE WIRED
DTC15	15A	125V	DECORA DUPLEX RECEPTACLE, TR, 2-POLE 3-WIRE, GROUNDING, NEMA 5-15R, SIDE WIRED
DTB20	20A	125V	DECORA DUPLEX RECEPTACLE, TR, 2-POLE 3-WIRE, GROUNDING, NEMA 5-20R, BACK & SIDE WIRED
TDBR2	20A	125V	DECORA DUPLEX RECEPTACLE, TR, 2-POLE 3-WIRE, GROUNDING, NEMA 5-20R, BACK & SIDE WIRED
DTC20	20A	125V	DECORA DUPLEX RECEPTACLE, TR, 2-POLE 3-WIRE, GROUNDING, NEMA 5-20R, SIDE WIRED

CATALOG DTB20 SHOWN

"TR" TAMPER RESISTANT
DECORA DUPLEX RECEPTACLE

DIMENSIONS ARE IN INCHES,
DIMENSIONS IN BRACKET ARE IN MM

UNLESS OTHERWISE SPECIFIED: DO NOT SCALE DRAWING. ALL DIMENSIONS ARE IN INCHES. ALL ANGLES ARE IN DEGREES.		LEVITON		
TOLERANCES		TITLE: DECORA DUPLEX RECEPTACLE TR WEBSITE DRAWING		
INCH .XX ± .01 .XXX ± .005	METRIC .X ± .2 mm .XX ± .1 mm	DWG NO. ORC6951-D01		
ANGLES: ± 1/2°		SIZE: B SCALE: 1:1 SHEET 1 OF 1 REV A		
THIRD ANGLE PROJECTION 		Copyright 2020. Unpublished. All Rights Reserved.		
ALL PRINTED COPIES ARE UNCONTROLLED				