Power Pedestals for Marine

CUSTOMIZABLE & PRE-CONFIGURED UNITS TO MEET YOUR UNIQUE NEEDS

DS1 DOCKSIDER

DH1 DOCKHEAD

- Withstands corrosive environments with plastic resin housing for extended lifespan
- Efficient design turnaround and lead times
- Two piece system allows disassembly of pedestal in anticipation of harsh weather

For questions, please contact your local Leviton sales rep, or email industrial@leviton.com

DOCKSIDER

DS1 Large Power Pedestals

(Wiring devices will vary from those shown)



DOCKSIDER POWER PEDESTALS FOR MARINE:

- Preassembled with distribution block, wiring devices with weather-resistant covers, and LED base lights
- Allows up to 6 wiring devices
- Includes pedestal base with cord management hooks

CONSTRUCTION:

- Polycarbonate housing with two piece system to allow disassembly of pedestal in harsh weather conditions
- Base extension available to raise bus bar connection by 6 inches

STANDARDS:

- NEMA 3R, UL-231, CSA 22.2 No. 29, NFPA 303, NFPA 70

WARRANTY:

- Housing: 5 years
- Wiring Devices: 1 year

DS1 ADDITIONAL INFORMATION

PRODUCT DETAIL PAGE

CONFIGURATION FORM

leviton.com/products/ds1-docksider-power-pedestal

For more information, please contact your local Leviton sales representative or email us at industrial@leviton.com

DOCKHEAD

DH1 Small Power Outlet Boxes & DH2 Large Power Outlet Boxes

(Wiring devices will vary from those shown)

- Available in 2 sizes, with or without mounting pedestal:
  - DH1 is 8" x 10"
  - DH2 is 10" x 12"
- Durable glass reinforced fiberglass material
- Analog water and kW meter available
- EPD or standard breakers available
- Weatherproof covers in up to 6 colors
- Water hook-up options (with pedestal)
- Allows from 2 (DH1) to 4 (DH2) receptacles (breakers are side mounted)
- Daylight sensing LED lighting in amber or white
- NEMA 3R rated

DH1

Optional 4" x 6" aluminum stands are available to elevate DH2 units 23" above the surface and feature two fixed hangers for hoses, ropes or cords. ***Ordering details appear at bottom of next page.***

DH2

8" X 10" POWER OUTLET BOX FOR MARINE:

- Preassembled with mini straight distribution block, wiring devices with weather-resistant covers, and front and bottom LED lights
- Allows up to 2 wiring devices

10" X 12" POWER OUTLET BOX FOR MARINE:

- Preassembled with distribution block, wiring devices with weather-resistant covers, and front and bottom LED lights
- Allows up to 4 wiring devices
- Can be ordered with or without stand/pedestal

CONSTRUCTION (BOTH):

- Polycarbonate housing

WARRANTY (BOTH):

- Housing: 5 years
- Wiring Devices: 1 year

STANDARDS (BOTH):

- NEMA 3R, UL-231, CSA 22.2 No. 29, NFPA 303, NFPA 70

DH1 ADDITIONAL INFORMATION

PRODUCT DETAIL PAGE

CONFIGURATION FORM

leviton.com/products/dh1-dockhead-power-pedestal

DH2 ADDITIONAL INFORMATION

PRODUCT DETAIL PAGE

CONFIGURATION FORM

leviton.com/products/dh2-dockhead-power-pedestal

For more information, please contact your local Leviton sales representative or email us at **industrial@leviton.com**

PRE-CONFIGURED UNITS

Ordering Information

Pre-configured pedestals and boxes can be ordered using our ordering chart. Additionally, we offer fully customizable units to meet your specific needs. For more information, please contact your local Leviton sales representative or email us at industrial@leviton.com.

Catalog Number	Description
DOCKSIDER PEDESTALS	
D3232	Includes Two 30 A (125 V) Receptacles with Standard Breakers, Two 20 A GFCI Receptacles with Standard Breakers, White LED with Photocell, and White Receptacle Covers. Includes Single Phase Loop Distribution Block, Two 3/4" Quarter-Turn Water Valves. *(No Meter or Spare Breaker.)*
D5352	Includes Two 50 A (125/250 V) Receptacles with Standard Breakers, 30 A (125V) Receptacle with Standard Breaker, 20 A GFCI Receptacles with Standard Breaker, White LED with Photocell, and White Receptacle Covers. Includes Single Phase Loop Distribution Block, Two 3/4" Quarter-Turn Water Valves. *(No Meter or Spare Breaker.)*
D532S	Includes 50 A (125/250 V) Receptacle with Standard Breaker, 30 A (125 V) Receptacle with Standard Breaker, 20 A GFCI Receptacles with Standard Breaker, White LED with Photocell, and White Receptacle Covers. Includes Single Phase Loop Distribution Block, 3/4" Quarter-Turn Water Valve. *(No Meter or Spare Breaker.)*
D332D	Includes Four 30 A (125 V) Receptacles with Standard Breakers, Two 20 A GFCI Receptacles with Standard Breakers, White LED with Photocell, and White Receptacle Covers. Includes Single Phase Loop Distribution Block, Two 3/4" Quarter-Turn Water Valves. *(No Meter or Spare Breaker.)*
D532D	Includes Two 50 A (125/250 V) Receptacles with Standard Breakers, Two 30 A (125 V) Receptacles with Standard Breakers, Two 20 A GFCI Receptacles with Standard Breakers, White LED with Photocell, and White Receptacle Covers. Includes Single Phase Loop Distribution Block, Two 3/4" Quarter-Turn Water Valves. *(No Meter or Spare Breaker.)*
D532E	Includes 50 A (125/250 V) Receptacle with 30 mA EPD Breaker, 30 A (125 V) Receptacle with 30 mA EPD Breaker, 20 A GFCI Receptacle with Standard Breaker, White LED with Photocell, and White Receptacle Covers. Includes Single Phase Loop Distribution Block, 3/4" Quarter-Turn Water Valve. *(No Meter or Spare Breaker.)*
D532W	Includes Two 50 A (125/250 V) Receptacles with 30 mA EPD Breakers, Two 30 A (125 V) Receptacles with 30 mA EPD Breakers, Two 20 A GFCI Receptacles with Standard Breakers, White LED with Photocell, and White Receptacle Covers. Includes Single Phase Loop Distribution Block, Two 3/4" Quarter-Turn Water Valves. *(No Meter or Spare Breaker.)*
DOCKHEAD POWER BOXES	
HL323	10"x12" Base Includes Two 30 A (125 V) Receptacles with Standard Breakers, 20 A GFCI Receptacle with Standard Breaker, White LED with Photocell, and White Receptacle Covers. Includes Single Phase Loop Distribution Block. *(No Water, Meter or Spare Breaker.)*
HL533	10"x12" Base Includes 50 A (125/250 V) Receptacle with Standard Breaker, Two 30 A (125 V) Receptacles with Standard Breakers, White LED with Photocell, and White Receptacle Covers. Includes Single Phase Loop Distribution Block. *(No Water, Meter or Spare Breaker.)*
HS320	8" x 10" Base Includes 30 A (125 V) Receptacle with Standard Breaker, 20 A GFCI Receptacle with Standard Breaker, White LED with Photocell, and White Receptacle Covers. *(No Water, Meter or Spare Breaker.)*
DOCKHEAD STANDS *Designed for use with custom DH2 or the HL323 or HL533 power boxes listed above, these optional 4" x 6" aluminum stands elevate units 23" above the surface and feature two fixed hangers for hoses, ropes or cords.*	
RVST	No Water Hookup
RVST1	Two 1/2" Quarter-Turn Water Valves
RVST2	Two 3/4" Quarter-Turn Water Valves

Visit our Website at:
www.leviton.com/powerpedestals
email: industrial@leviton.com

Q-1475B 052125

Leviton Manufacturing Co., Inc.
201 N Service Rd, Melville, NY 11747
Telephone: 1-800-323-8920 • FAX: 1-800-832-9538
Tech Line: 1-800-824-3005 (M-F 8AM-10PM; Sat 9AM-7PM; Sun 9AM-5PM)

© 2025 Leviton Manufacturing Co., Inc. All rights reserved.