



NOTES:

- 1) DIM IN/MM
- 2) CSA

STATUS: In Work					 <p>The information in this document is the exclusive PROPRIETARY property of LEVITON MFG. CO., INC. It is disclosed with the understanding that acceptance or review by the recipient constitutes an undertaking by the recipient:</p> <p>(1) to hold this information in strict confidence.</p> <p>(2) not to disclose, duplicate, copy, or use the information, in whole or in part, for any purpose other than that for which disclosed.</p> <p>Copyright 2016. Unpublished. All Rights Reserved.</p>	UNLESS OTHERWISE SPECIFIED: DO NOT SCALE DRAWING. ALL DIMENSIONS ARE IN INCHES. ALL ANGLES ARE IN DEGREES.		TITLE: TOGGLE SWITCH 20A-347V DOUBLE POLE					
						TOLERANCES							
REV.	DATE	ECO NUMBER	CHGD	APVD	INCH .XX ± .01 .XXX ± .005	METRIC .X ± .2 mm .XX ± .1 mm	DWN BY	ML	09/29/2017	ENGRG	-	-	
1	-	-	-	-			CHK BY	-	-	MFG	-	-	
-	-	-	-	-	ANGLES: ± 1/2°		DWG NO. CATSTD-18222-00X-D01						
-	-	-	-	-	THIRD ANGLE PROJECTION		SIZE		PROJECT NO. LEGACY-CI			REV	
-	-	-	-	-			A		SCALE:1:1		SHEET 1 OF 1		1
					ALL PRINTED COPIES ARE UNCONTROLLED								