

4

3

2

1

D

D

C

C



B

B

A

A

STYLE 7



Basic Dash	Rating	Type
TCR15-IGx	15A-125V	Duplex – SW, FF, STS
TCR20-IGx	20A-125V	Duplex – SW, FF, STS
T5262-IGx	15A-125V	Duplex – B/SW, FF, BTS
T5362-IGx	20A-125V	Duplex – B/SW, FF, BTS
WT562-IGx	15A-125V	Duplex – B/SW, FF, BTS
WT563-IGx	20A-125V	Duplex – B/SW, FF, BTS
T8200-xxx	15A-125V	Duplex – B/SW, FF, BTS
T8300-xxx	20A-125V	Duplex – B/SW, FF, BTS
WT820-xxx	15A-125V	Duplex – B/SW, FF, BTS
WT830-xxx	20A-125V	Duplex – B/SW, FF, BTS
T8200-IGx	15A-125V	Duplex – B/SW, FF, BTS
T8300-IGx	20A-125V	Duplex – B/SW, FF, BTS
WT820-IGx	15A-125V	Duplex – B/SW, FF, BTS
WT830-IGx	20A-125V	Duplex – B/SW, FF, BTS

B/SW- Back and Side Wire
 SW - Side wire only
 FF - Flat Face
 BTS-Brass terminal screw
 STS-Steel terminal screw

REV.	DATE	ECO NUMBER	CHGD	APVD
1	-	-	-	-
-	-	-	-	-
-	-	-	-	-
-	-	-	-	-
-	-	-	-	-

LEVITON
 The information in this document is the exclusive **PROPRIETARY** property of **LEVITON MFG. CO., INC.** It is disclosed with the understanding that acceptance or review by the recipient constitutes an undertaking by the recipient: (1) to hold this information in strict confidence. (2) not to disclose, duplicate, copy, or use the information, in whole or in part, for any purpose other than that for which disclosed.
 Copyright 2016. Unpublished. All Rights Reserved.

UNLESS OTHERWISE SPECIFIED: DO NOT SCALE DRAWING. ALL DIMENSIONS ARE IN INCHES. ALL ANGLES ARE IN DEGREES.
TOLERANCES
 INCH .XX ± .01 .X ± .005
 METRIC .X ± .2 mm .XX ± .1 mm
ANGLES: ± 1/2°
THIRD ANGLE PROJECTION
ALL PRINTED COPIES ARE UNCONTROLLED

TITLE: TAMPER RESISTANT DUPLEX RECEPTACLE		DWN BY		09/22/2016		ENGRG		-		-	
CHK BY		-		-		MFG		-		-	
DWG NO.		ORA4993-D02									
SIZE C		PROJECT NO. PROJ-02715				SCALE:1:2		SHEET 12 OF 13		REV 1	

4

3

2

1