

WARNINGS AND CAUTIONS:

- TO BE INSTALLED AND/OR USED IN ACCORDANCE WITH APPROPRIATE ELECTRICAL CODES AND REGULATIONS.
- IF YOU ARE NOT SURE ABOUT ANY PART OF THESE INSTRUCTIONS, CONSULT AN ELECTRICIAN.

DESCRIPTION:

The Handheld Self-Powered Wireless Remote is a battery-free wireless transmitter that communicates with a wide variety of receivers. Every time one of the buttons are pressed a small micro-generator produces a small electrical current that powers a built-in transmitter. This transmitter sends wireless signals that command the receiver to turn a device off or on. With an appropriate receiver, the button can even be used to control the dimming of lights.

COMPATIBLE DEVICES:


EnOcean wireless receivers.

PROGRAMMING AND ACTIVATION:

1. **Make sure the remote is within 5 meters of the desired receiver when programming.** Receivers have reduced range during programming.
2. **Programming:** To associate a wireless remote with a receiver, simply press the button of the wireless remote while the receiver is in the desired Program Mode (see receiver installation guide for information on how to program the receiver). Repeat this process for the second, third and fourth buttons.
3. **Activation:** Once a wireless rocker has been associated with a receiver, simply press the button on the wireless remote to control the load.

| SPECIFICATIONS | |
|----------------------------|--|
| | WSS0S-R9W |
| Range | 50-150 feet |
| Frequency | 902 MHz |
| Power Supply | Self-generated when button is pressed |
| Channels | 4 buttons (2 rockers) |
| Dimensions | 1.85 x 3.15 x 0.7 inches |
| Radio Certification | FCC (United States) SZV-PTM210U IC (Canada) 5731A-PTM210U |
| Addressing | Factory set unique ID (1 of 4 billion) |

NETWORK DIAGRAM



FCC COMPLIANCE STATEMENT:

Contains FCC ID: SZV-PTM210U, Contains IC: 5731A-PTM210U
The enclosed device complies with Part 15 of the FCC Rules.
Operation is subject to the following two conditions:
(i.) This device may not cause harmful interference
(ii.) This device must accept any interference received, including interference that may cause undesired operation.

Leviton is a registered trademark of Leviton Mfg. Co. in the United States, Canada, Mexico, and other countries. Other trademarks herein are the property of their respective owners.

LIMITED 2 YEAR WARRANTY AND EXCLUSIONS

Leviton warrants to the original consumer purchaser and not for the benefit of anyone else that this product at the time of its sale by Leviton is free of defects in materials and workmanship under normal and proper use for two years from the purchase date. Leviton's only obligation is to correct such defects by repair or replacement, at its option, if within such two year period the product is returned prepaid, with proof of purchase date, and a description of the problem to **Leviton Manufacturing Co., Inc., Att: Quality Assurance Department, 201 North Service Road, Melville, New York 11747**. This warranty excludes and there is disclaimed liability for labor for removal of this product or reinstallation. This warranty is void if this product is installed improperly or in an improper environment, overloaded, misused, opened, abused, or altered in any manner, or is not used under normal operating conditions or not in accordance with any labels or instructions. **There are no other or implied warranties of any kind, including merchantability and fitness for a particular purpose**, but if any implied warranty is required by the applicable jurisdiction, the duration of any such implied warranty, including merchantability and fitness for a particular purpose, is limited to two years. **Leviton is not liable for incidental, indirect, special, or consequential damages, including without limitation, damage to, or loss of use of, any equipment, lost sales or profits or delay or failure to perform this warranty obligation.** The remedies provided herein are the exclusive remedies under this warranty, whether based on contract, tort or otherwise.