

Berk-Tek Power Injection Devices

1U Mounting Bracket

Part Number: 81000463

With options to power one device or many, the OneReach PI seamlessly becomes a part of the network infrastructure, with 2U or 4U Injector Chassis and a 1U Mounting Bracket (for 1-port modules) installing in a standard 19" rack.

DESCRIPTION

The OneReach System begins in the local closet with the PI. The PI provides both the power to run the system and the technology to transmit the data signals to previously unreachable distances. Composed of a specially designed PoE Media Module or 19" rack mountable powered injector chassis, and PoE Power Supply modules, these devices deliver big benefits in a small footprint.

This approach to IP-based security enables the consolidation of device management through the existing network infrastructure. The existing IT team is able to monitor device traffic and operations without having to travel to remote locations.

By locating the power for remote devices in a single local closet, users are able to consolidate UPS devices and streamline and simplify management. Unlike traditional installations, with OneReach there is no need to provide for redundant power at a variety of remote and possibly environmentally hostile locations. Now, in the event of a power outage, one centrally located UPS can keep your cameras, access control devices or wireless access points fully operational.

Benefits

- Simplifies device management
- Enables UPS consolidation
- Uses simple screw terminal connections
- Supports PoE

CHARACTERISTICS

Construction characteristics

Material	Steel
Colour	Black

Dimensional characteristics

Height/unit	1 U
Approximate net weight	0.7 kg
Approximate net weight	1.5 lb

Usage characteristics

Recommended operating temperature range	0 .. 40 °C
---	------------



STANDARDS


International EN 50173;
ISO/IEC 11801

PRODUCT DETAILS

14 gauge steel, accomodating two 1-port PoE Media Modules.

Includes screws and washers for mouting two Media Modules, and the bracket.

1U MOUNTING BRACKET - DIMENSIONS (INCHES)



MANUFACTURING RELEASE

IMPORTANT NOTICE: This product specification is provided for informational purposes only in order to illustrate typical product constructions, applications and/or methods of installation. Because conditions of actual installation and use are unique and will vary, Berk-Tek makes no representation or warranty as to the reliability, accuracy or completeness of this data, even if Berk-Tek is aware of the product's intended use or purpose. Furthermore, this data does not constitute, nor should it be regarded or relied upon, as professional engineering advice. Installation of product should only be done by qualified personnel and in conformance with all safety, electrical and other applicable codes, standards, rules or regulations. Appropriate and correct product selection, installation and use, and compliance with all such codes, standards, rules and regulations, is a customer/end-user responsibility. Product specifications, standards, programs or services are subject to improvement or changes without notice. Berk-Tek accepts no liability for typographical errors, technical inaccuracies, omissions or misuse of the information contained herein. Changes will be periodically made to address any such issues.