


Half RU Universal Flat Patch Panel

APPLICATION

Leviton's Half RU Universal Flat Patch Panels provide high density patching where rack space is a premium. This makes them ideal for use in many applications including health care, manufacturing, datacenters and other environments where rack space is limited. Universal Flat QUICKPORT[™] Patch Panels are available in 24 ports and designed to provide a high-density option with a low profile.



SPECIFICATION

Patch panels shall be available in a 24-port configuration and shield data from electromagnetic and radio frequency interference. Panels shall accept both shielded and unshielded QUICKPORT[™] jacks and connectors. Panels shall have a black powder coat finish with white silk screening. Panels shall meet or exceed ANSI/ TIA-568.0-E, and IEC 60603-7.

FEATURES & BENEFITS

- Panels allow mix-and-match of shielded and unshielded QUICKPORT™ jacks and connectors
- Panel includes hardware to accept standards-compliant grounding connectors
- · Shielding provides EMI/RFI protection and data security
- Included Rear Cable Manager supports incoming copper cables
- · Mounts on standard 19-inch racks and cabinets

DESIGN CONSIDERATIONS

• Verify rack is grounded according to commercial building grounding and bonding requirements for telecommunications

STANDARDS & REGULATIONS

- ANSI/TIA 568.0-E
- IEC 60603-7

MECHANICAL SPECIFICATIONS

Dimensions:See page twoMaterials:18-gauge steel, black powder coatTemp. (Storage):-40 °C to +70 °C (-40 °F to +158 °F)Temp. (Installation):Refer to cable installation temperatureTemp. (Operating):-10 °C to +60 °C (+14 °F to +140 °F)Humidity (Max.):95% relative humidity, non-condensing

COUNTRY OF ORIGIN


China

WARRANTY INFORMATION


For Leviton product warranties, go to Leviton.com/NS/Warranty

PRODUCT SPECIFICATIONS 4S255-4BH





<u> </u>	480.1 mm [18.90"]
	<u> </u>



PART NUMBER	
Description	Part No.
Universal Flat Patch Panel, 24 ports, Half RU with cable management tray	4S255-4BH

For further support information, visit Leviton.com/NS/Support

Page 2 of 2

USA Network Solutions Headquarters +1 (800) 722 2082 infoUSA@leviton.com

Asia Pacific Canada +1 (800) 461 2002

Europe

Latin America MX: +52 (55) 2128 6286 LATAM: +52 (55) 2333 5963 Middle East & Africa

Leviton Cable (formerly Berk-Tek) +1 (800) 237 5835 | infoUSA@leviton.com

+852 3620 2602 infoAPAC@leviton.com NETWORK SOLUTIONS PRODUCTS ARE AVAILABLE WORLDWIDE IN OVER 100 COUNTRIES. VISIT US ONLINE AT LEVITON.COM/NS TO LEARN MORE.

infoCanada@leviton.com

+44 (0) 1592 772124 infoEurope@leviton.com infoLATAM@leviton.com

+971 (4) 247 9800 infoMEA@leviton.com

Copyright © 2024 Leviton Manufacturing Co., Inc. All rights reserved. Leviton reserves the right to modify product specifications without notice.