

## Angled Single-Gang QuickPort® Wallplates with ID Windows

### APPLICATION

Angled single-gang wallplates accept QuickPort snap-in modules to support multimedia applications with either 1, 2, or 4 ports. Use where designation windows in an economical single-gang flush-mount housing are desired. Available in four colors: white, ivory, light almond, and black (4-port only).



42081-1xS

42081-2xS

42081-4WS

### SPECIFICATION

The wallplate housing shall be a one-piece, single-gang flush-mount style that fits standard NEMA openings. It shall provide 1, 2, or 4 ports and feature a 45-degree angled design to facilitate optimal cable management. The wallplate shall accept all Leviton QuickPort UTP, fiber, or AV modules. Wallplate shall be made of high-impact, fire-retardant plastic rated UL 94V-0, and be cULus Listed and compliant with ANSI/TIA-568-C.0 specifications. Colors, port counts, and configurations to be specified per schedule on plan.

### FEATURES

- 45-degree angled ports facilitate optimal cable management, ensuring proper bend radius compliance in front and back of connector
- Includes ID designation windows for each wallplate
- Fits within minimum rectangular NEMA openings
- Compatible with all individual QuickPort UTP, fiber, and AV modules
- Individual port configurability allows specification flexibility
- Narrow module width allows high port density in a small area
- Ideal for Cat 6A and fiber optic applications at the workstation
- Slotted mounting holes allow installers to level the plate if back box is crooked
- Recessed ports protect jack and patch cord plug

### DESIGN CONSIDERATIONS

- Fits standard NEMA single-gang back boxes
- For future expansion, install blanks (41084-BxB) in unused ports
- Specify port identification method (colored modules, designation labels, and custom silk-screening available)
- Identify ports using different colored connectors for each application (full selection of ANSI/TIA-606 compatible colors) or Leviton pre-printed Port Designation Labels (41080-LEB)

### STANDARDS COMPLIANCE

- cULus Listed (UL 1863 & CAN/CSA-C22.2 No. 182.4)
- ANSI/TIA-568-C.0

### PHYSICAL SPECIFICATIONS

Dimensions: See page two  
Capacity: Available in 1-, 2-, or 4-port versions  
Materials: High-impact, fire-retardant plastic rated UL 94V-0

### COUNTRY OF ORIGIN

Taiwan

### WARRANTY INFORMATION

For a copy of Leviton product warranties, visit [www.leviton.com/warranty](http://www.leviton.com/warranty).

42081-xxS

#### Leviton Network Solutions

2222 - 222nd St. SE  
Bothell, WA 98021-4416

tel 1-800-824-3005  
tel +1-425-486-2222  
appeng@leviton.com  
[www.leviton.com](http://www.leviton.com)

**Asia / Pacific**  
T +1.631.812.6228  
E infoasean@leviton.com

**Europe**  
T +44.0.1592.772124  
E customerserviceeu@leviton.com

**Canada**  
T +1.514.954.1840  
E pcservice@leviton.com

**Mexico**  
T +52.55.5082.1040  
E lsamarketing@leviton.com

**Caribbean**  
T +1.954.593.1896  
E infocaribbean@leviton.com

**Middle East & Africa**  
T +971.4.247.9800  
E lmeinfo@leviton.com

**China**  
T +852.2774.9876  
E infochina@leviton.com

**South Korea**  
T +82.2.3273.9963  
E infokorea@leviton.com


**Colombia**  
T +57.1.743.6045  
E infocolombia@leviton.com

**ELECTRONIC FILES**


For CAD files, typical specs, or technical drawings (.DXF, .DWG), visit [www.leviton.com](http://www.leviton.com).

**42081-xxS**


42081-1xS



42081-4xS



42081-2xS



**PART NUMBERS**

Description	WHITE	LT. ALMOND	IVORY	BLACK
Angled Single-Gang QuickPort® Wallplate with ID Windows, 1 Port	42081-1WS	42081-1TS	42081-1IS	—
Angled Single-Gang QuickPort Wallplate with ID Windows, 2 Ports	42081-2WS	42081-2TS	42081-2IS	—
Angled Single-Gang QuickPort Wallplate with ID Windows, 4 Ports	42081-4WS	42081-4TS	42081-4IS	42081-4ES

**Leviton Network Solutions**

2222 - 222nd St. SE  
Bothell, WA 98021-4416

**Asia / Pacific**  
T +1.631.812.6228  
E [infoasean@leviton.com](mailto:infoasean@leviton.com)

**Canada**  
T +1.514.954.1840  
E [pcservice@leviton.com](mailto:pcservice@leviton.com)

**Caribbean**  
T +1.954.593.1896  
E [infocaribbean@leviton.com](mailto:infocaribbean@leviton.com)

**China**  
T +852.2774.9876  
E [infochina@leviton.com](mailto:infochina@leviton.com)

**Colombia**  
T +57.1.743.6045  
E [infocolombia@leviton.com](mailto:infocolombia@leviton.com)

tel 1-800-824-3005  
tel +1-425-486-2222  
[appeng@leviton.com](mailto:appeng@leviton.com)  
[www.leviton.com](http://www.leviton.com)

**Europe**  
T +44.0.1592.772124  
E [customerserviceeu@leviton.com](mailto:customerserviceeu@leviton.com)

**Mexico**  
T +52.55.5082.1040  
E [lsamarketing@leviton.com](mailto:lsamarketing@leviton.com)

**Middle East & Africa**  
T +971.4.247.9800  
E [lmeinfo@leviton.com](mailto:lmeinfo@leviton.com)

**South Korea**  
T +82.2.3273.9963  
E [infokorea@leviton.com](mailto:infokorea@leviton.com)