

## Opt-X<sup>®</sup> Fiber Cleaver

### APPLICATION

The Opt-X Fiber Cleaver provides high precision at a low cost. This compact and easy to use cleaver is perfect for all cleaving applications, from fusion splicing to mechanical splicing, and is ideal for working with Leviton FastCAM<sup>®</sup> connectors. For a self-contained workspace, mount the cleaver to the optional work tray and use the optional gooseneck LED for task lighting.

The Opt-X Fiber Cleaver can be purchased individually or as part of the FastCAM Tool Kit, which includes the cleaver, lint free dry wipes, alcohol pads, and a jacket stripper.



### SPECIFICATION

Cleaver shall work with both 250 μm coated and 900 μm buffered fibers. It shall guarantee a cleave angle of 90° +/- 0.5°, and the 16-position blade shall have a blade life of approximately 48,000 cleaves.

### COUNTRY OF ORIGIN

Korea

### WARRANTY INFORMATION

For a copy of Leviton product warranties, visit [www.leviton.com/warranty](http://www.leviton.com/warranty).

Page 1 of 1

D14 4875

#### Leviton Network Solutions

2222 - 222nd St. SE  
 Bothell, WA 98021-4416

tel 1-800-824-3005  
 tel +1-425-486-2222  
 appeng@leviton.com  
[www.leviton.com](http://www.leviton.com)

#### Asia / Pacific

T +1.631.812.6228  
 E infoasean@leviton.com

#### Europe

T +33.6.8869.1380  
 E infoeurope@leviton.com

#### Canada

T +1.514.954.1840  
 E pcservice@leviton.com

#### India / SAARC

T +91.80.4322.5678  
 E infoindia@leviton.com

#### Caribbean

T +1.954.593.1896  
 E infocaribbean@leviton.com

#### Mexico

T +52.55.5082.1040  
 E lsamarketing@leviton.com

#### China

T +852.2774.9876  
 E infochina@leviton.com

#### Middle East & Africa

T +971.4.886.4722  
 E lmeinfo@leviton.com

#### Colombia

T +57.1.743.6045  
 E infocolombia@leviton.com

#### South Korea

T +82.2.3273.9963  
 E infokorea@leviton.com

### FEATURES

- High precision cleaves
- 250 μm coated or 900 μm buffer fiber
- Single-mode or multimode use
- 16-position rotatable and replaceable blade
- 3-action operation

### DESIGN CONSIDERATIONS

- Compact, ergonomic design
- Optional work tray and gooseneck LED for task lighting available

### SPECIFICATIONS

Fiber Diameter	125 μm
Coating Diameter	250 μm ~ 900 μm
Cleave Angle	90° ± 0.5°
Cleave Length	5 ~ 20 mm
Blade Lifetime	48,000 cleaves (3,000 per blade position)
Cleaver Dimensions	58 x 55 x 48 mm
Weight	360 g

### PART NUMBERS

Description	Part No.
FastCAM <sup>®</sup> Tool Kit with Opt-X Fiber Cleaver, Stripper, and Consumables	49800-MSK
FastCAM <sup>®</sup> Tool Kit with Opt-X Fiber Cleaver, Stripper, Work Tray, Gooseneck LED, and Consumables	49800-LAK
Opt-X Cleaver	49886-LNX
Gooseneck LED	49886-LGN
Work Tray	49886-LNT

49886-Lxx, 49800-MSK, 49800-LAK