

Cat 5e Unshielded Patch Cords

APPLICATION

Leviton Cat 5e Unshielded Patch Cords enable optimum system performance. These factory-made and tested patch cords offer you guaranteed quality and ensure that your system avoids the performance degradation that inferior alternatives will give you at high data rates.



SPECIFICATION

The patch cords shall provide Cat 5e performance for cross connecting Cat 5e equipment and/or backbone cables to high-performance Cat 5e horizontal cable systems. The patch cords shall be stranded conductor cable with a standard 8-position modular plug and colored boot on each end. The cords shall be available in lengths of 1, 1.5, 2, 3, and 5 meters. The cords must meet performance and assembly requirements per ISO 11801-1 and ANSI/TIA-568.2. Patch cord plug shall have industry-standard, ANSI/TIA-1096-A compliant 50 micro inches of gold plating.

WARRANTY INFORMATION

For Leviton product warranties, go to Leviton.com/warranty

FEATURES & BENEFITS

- Compliant with Category 5e standards
- Low Smoke Halogen Free (LSHF) materials as standard
- Available in a variety of lengths and colors
- Low profile boots for higher density blade connectivity
- Flexible and robust construction
- Performance assessed through rigorous quality control in compliance with industry standards

DESIGN CONSIDERATIONS

Suitable for connection in:

- Wall and multi-user outlets
- Patch panels and consolidation points
- Servers, blade servers, hubs, and switches

STANDARDS & REGULATIONS

- ISO/IEC 11801-1
- EN50173-1
- ANSI/TIA 568.2
- EN61935-2
- EN60303-7 Series
- Fire Safety Rating to IEC 60332-1-2
- Acid Gas Emissions to IEC 60754-2
- Smoke Index to IEC 61034
- Supports IEEE 802.3 PoE Type 1, 2, 3 (60 watts max)
- Fully supports the safe delivery of power over LAN cabling described by IEEE 802.3 (Type 3) and complies with the unrating under electrical load requirements prescribed by IEC 60512-99-001

MECHANICAL SPECIFICATIONS

Dimensions:	Stranded UTP - 5.4mm
Length Tolerance (bracketed length):	+/- 1%
Materials:	PC UL94 V0 rated plastics throughout body Plated Phosphor Bronze Screen
Voltage Rating:	300V
Temp. (Storage):	-20 °C to +70 °C (-4 °F to +158 °F)
Temp. (Installation):	-20 °C to +70 °C (-4 °F to +158 °F)
Temp. (Operating):	0 °C to +50 °C (+32 °F to +122 °F)
Humidity (Max):	93% relative humidity, non-condensing

PRODUCT SPECIFICATIONS
GPCPCU*-xxxHB**



GPCPCU***-xxxHB

ORDER INFO

Part Number	Item Description	Weight per Item (nom)	Qty per Pack
GPCPCU010-xxxHB	Cat 5e U/UTP Patch Cord – 1.0m	50g	10
GPCPCU015-xxxHB	Cat 5e U/UTP Patch Cord – 1.5m	75g	10
GPCPCU020-xxxHB	Cat 5e U/UTP Patch Cord – 2.0m	100g	10
GPCPCU030-xxxHB	Cat 5e U/UTP Patch Cord – 3.0m	150g	10
GPCPCU050-xxxHB	Cat 5e U/UTP Patch Cord – 5.0m	200g	10

x = Note: xxx = Cable and boot color, see options below.

GPCPCabb-cdefff CAT 5E PATCH CORDS PART NUMBER CONFIGURATOR

GPCPC	a (Cord Type)	bbb (Length, Standard)	c (Cable Colors)	d (Boot Color)	e (Boot Color)	fff (Specialty Tag)
	<ul style="list-style-type: none"> U = Unshielded 	<ul style="list-style-type: none"> 010 = 1.0m 015 = 1.5m 020 = 2.0m 030 = 3.0m 050 = 5.0m <p>Other lengths available upon request</p>	<ul style="list-style-type: none"> 1 = Red 2 = Black (Non-STD) 3 = White (Non-STD) 4 = Blue 5 = Green 6 = Yellow 7 = Violet (Non-STD) 8 = Gray 	<ul style="list-style-type: none"> 1 = Red 2 = Black (Non-STD) 3 = White (Non-STD) 4 = Blue 5 = Green 6 = Yellow 7 = Violet (Non-STD) 8 = Gray 	<ul style="list-style-type: none"> 1 = Red 2 = Black (Non-STD) 3 = White (Non-STD) 4 = Blue 5 = Green 6 = Yellow 7 = Violet (Non-STD) 8 = Gray 	<ul style="list-style-type: none"> B = Blade H = Halogen Free S = Solid C = Crossover <p>Cords are halogen-free with stranded copper conductors unless otherwise stated.</p>



For further support information, visit Leviton.com/ns/support

USA
 Network Solutions Headquarters
 +1 (800) 722 2082
infoUSA@leviton.com
 BERK-TEK™ Cable
 +1 (800) 237 5835 | infoUSA@leviton.com

Asia Pacific
 +852 3620 2602
infoAPAC@leviton.com

Canada
 +1 (800) 461 2002
infoCanada@leviton.com

Europe
 +44 (0) 1592 772124
infoEurope@leviton.com

Latin America
 MX: +52 (55) 2128 6286
 LATAM: +52 (55) 2333 5963
infoLATAM@leviton.com

Middle East & Africa
 +971 (4) 247 9800
infoMEA@leviton.com

NETWORK SOLUTIONS PRODUCTS ARE AVAILABLE WORLDWIDE IN OVER 100 COUNTRIES. VISIT US ONLINE AT LEVITON.COM/NS TO LEARN MORE.