


Dimmer Compatibility

Ensure your customers have an exceptional lighting experience.



DIMMERS:

SureSlide: 6674N

Decora Digital: DDM06

Decora Slide: DSL06, DSE06


Trimatron Rotary: RDL06, RNL06

Toggle Slide: TSL06

Decora Smart: D26HD, D2MSD, DN6HD, DWVAA, ZW6HD



Certifications



- Can be used to comply with Title 24 Part 6 JA8 High Efficacy LED Light Source Requirements
- Complies with IECC for high-efficacy LED lighting
- Compliant with ASTM E283 (Air Leakage Rate 2.0 CFM or Less)
- Suitable for use in clothes closets when installed in accordance with NEC® 410.16 (A)(1) (C)(3) spacing requirements



Scan to learn more
Downlights and Dimmers

Visit us at www.leviton.com



Leviton Manufacturing Co., Inc.

Tech Line: 1-800-824-3005

Mon-Fri 8am-10pm EST, Saturday 9am-7pm EST, Sunday 9am – 5pm EST
For 24/7 product support visit www.leviton.com/support

© 2024 Leviton Manufacturing Co., Inc. All rights reserved.



GR-100424-tp

Slim Downlight Fixtures

Easy to use, flexible applications, premium performance



Ease of Use


- Designed for new and remodel construction; direct mount design eliminates the need for a recessed housing or junction box
- Remote Driver Enclosure has two (2) conduit knockouts and includes poke-in connectors for easy installation
- Ideal for all shallow plenum applications

Flexibility

- Select from five (5) different color temperatures with a switch on the remote driver enclosure
- Suitable for use in wet locations, insulated ceilings, and where air-tight installation is required
- Dimmable down to 10% with forward- or reverse-phase dimmers

Performance


- The color rendering of the room surfaces and materials is enhanced by 90+ CRI LEDs
- Long-life LEDs are rated for 70% of the original light level after 50,000 hours of use
- 5-Year warranty after date of purchase



ROUND

Applications: High/low ceilings, shallow plenum applications, general lighting

CAT NO.	DBR40-S1W	DBR60-S1W	DBR80-S1W
SIZE	4-Inch	6-Inch	8-Inch
LUMEN OUTPUT	900Lm	1200Lm	1400Lm
INPUT POWER	12W	15W	18W



SQUARE

Applications: High/low ceilings, shallow plenum applications, general lighting

CAT NO.	DBS40-S1W	DBS60-S1W
SIZE	4-Inch	6-Inch
LUMEN OUTPUT	850Lm	1100Lm
INPUT POWER	12W	15W



ADJUSTABLE

Applications: Sloped ceilings, wall accents, Highlight areas of interest

CAT NO.	DAR40-S1W	DAR60-S1W
SIZE	4-Inch	6-Inch
LUMEN OUTPUT	800Lm	1100Lm
INPUT POWER	12W	15W