

Leviton LED Dimmers & LED Bulb Compatibility Test Results

As of July 2016





Testing and Compatibility

Leviton has an ongoing program testing LED bulbs for compatibility with our universal dimmers. The test program includes measurement of dimming range and testing for any abnormal flickering or fluttering.

Bulbs are tested in differing quantities of up to eight as the performance can vary based on the number of bulbs being dimmed. The ratings shown are based on an average of readings obtained and represent a reasonable expectation of performance.

In order to obtain consistence performance, it is recommended that when using multiple bulbs, they should be of the same model and wattage. Using combinations of different bulbs can result in varied dimming levels, color variation and potentially other undesired effects. Updated listings can be viewed at www.leviton.com/universal.

Understanding the Test Results

This compatibility list has been designed to help you determine which dimmable LED bulbs that have been tested and approved as compatible with the Leviton's Universal and Electronic Low Voltage Dimmers.

Minimum Brightness Level

The lower this percentage, the better the dimming range

Performance

This is how the dimmer performs with the bulb listed.

Better: Bulbs will dim, flickering may be present but not significant and diminishes with manual adjustment of slide

Best: Starts at low end, dimming range similar to incandescent, no observable flickering

If a rating for a particular bulb/dimmer combination is not provided, it could indicate inconsistent results or test results not available at this time. As additional test results for newer bulbs and dimmers are obtained, the compatibility chart will be updated.

INDEX

Click on the dimmer you are interested in for the compatibility information for that specific dimmer.

- I. Decora® Digital with Bluetooth® Technology – DDMX1, DDL06-BL
- II. Decora® Digital Dimmer (No Bluetooth) – DDL06-1L
- III. Decora® Rocker Slide – DSL06, DSM10, DSE06
- IV. IllumaTech® - IPL06
- V. SureSlide® - 6674, 6672
- VI. Renu® - REL06
- VII. Vizia RF +® - VRMX1
- VIII. Dimming Sensor – IPSD6, IPVD6

LED Bulb Compatibility
Decora® Digital Dimmer
with Bluetooth® Technology DDMX1



Manufacturer	Type	Model #	Wattage	Color (K)	Lumens	Minimum Brightness (% of full Brightness)	Performance
Buckingham	Fixed Track	1001573381	21	2700	1100	11%	Better
	Under Cabinet	205663883	9	3000	450	1%	Better
	Under Cabinet	1001217457	17	3000	790	0%	Better
	Under Cabinet	1001217466	6	3000	280	1%	Better
Bulbrite	A19	774101 LED11A19/827/D	11	2700	800	19%	Better
	A19	774103 LED15/A21/827/D	15.5	2700	1600	13%	Better
	A21	774102 LED13A21/827/D	13	2700	1100	28%	Better
	BR30	772810 LED16BR30/C/927/D	16.5	2700	975	31%	Better
	BR30	772840 LED12BR30/827/D/2	12.5	2700	1050	10%	Better
	BR30	773355 LED11BR30/827/D/2	11	2700	750	18%	Better
	BR40	772850 LED20BR40/827/D/2	20	2700	1750	10%	Better
	G5	771172 LED6MR16GU/30K/D-SN	6	3000	300	4%	Better
	MR16	771200 LEDMR16SW/D/E26	6	3000	300	4%	Better
	PAR30	772631 LED13PAR30L/FL40/930/WD	13	3000	820	7%	Better
	PAR30	772734 LED13PAR30L/FL40/830/WD	13	3000	1000	7%	Better
	PAR30S	772621 LED13/PAR30S/FL40/930/WD	13	3000	820	8%	Better
	PAR30S	772724 led13par30s/fl40/830/wd	13	3000	1000	9%	Better
	PAR38	772641 LED18PAR38/FL40/930/WD	18	3000	1150	7%	Better
	PAR38	772744 LED15PAR38/FL40/830/WD	15	3000	1200	7%	Better
R20	773255 LED8R20/827/D/2	8	2700	535	20%	Better	
Commercial Electric	Recessed-Kit	CE-JB6-650L-27K-E26	12.5	2700	670	36%	Better
Cree	A19	BA19-04527OMB-12DE26-3_1	6	2700	460	24%	Better
	A19	BA19-08027OMB-12DE26-3_1	10	2700	815	31%	Better
	A19	BA19-11027OMF-12DE26-1U100	13.5	2700	1100	32%	Better
	A21	BA21-16027OMF-12DE26-1U110	18	2700	1600	28%	Better
	BR30	BBR30-06527FLF-12DE26-4U100	9	2700	655	13%	Better
	PAR30	BPAR30L-0803040C-12DE26-1C_00	10.5	3000	850	12%	Better
	PAR30	BPAR30S-0803025C-12DE26-1C_00	11	3000	850	5%	Better
	PAR38	BPAR38-1503027T-12DE26-2U_00	18	3000	1500	10%	Better
Recessed-Kit	DRDL4-05727009-12DE26-1C100	11.5	2700	575	11%	Better	
Ecosmart	A15	1001684222 ECS A15 60WE W27 E12 12C	6	2700	500	12%	Better
	BR30	ECSBR3065WEWW120DG	9.5	3000	650	23%	Better
	BR30	LSBR30CECWWCRI90E26	13.2	3000		4%	Better
	BR40	ECSBR4075WEW27120G1BL	13	2700	940	12%	Better
	G25	ECS2525WEW27120DG	3.8	2700	300	18%	Better
	G25	ECS2540WEW27120DG	5.5	2700	400	19%	Better
	Recessed-Kit	ECS DN6 W27 E26 120	9.5	2700	650	11%	Better
Recessed-Kit	LSGLP6W27120WHS1BX	13	2700		2%	Better	
Feit-Utilitech Pro	A19	BPAGOM800/5K/LED	9.5	5000	810	28%	Better
	A19	BPAGOM800/LED	9.5	3000	800	30%	Better
GE	A19	13791	10.5	2700	800	17%	Better
	A19	14203	10.5	2700	800	17%	Better
	A19	83570	10.5	2700	800	17%	Better
	A19	89943	10.5	5000	850	17%	Better
	A19	95927	10.5	5000	850	17%	Better
	BR30	21907	10	2700	700	22%	Better
	BR30	68160	10	2700	700	22%	Better
	BR30	68161	10	3000	700	22%	Better
	BR30	89936	10	2700	700	22%	Better
	BR30	89942	10	5000	700	22%	Better
	PAR30	42131	12	3000	1050	21%	Better
	PAR30	42133	12	2700	1050	21%	Better
	PAR30	42134	12	2700	1000	21%	Better
PAR30	73583	12	2700	1000	21%	Better	

GE	PAR30	84379	12	3000	860	21%	Better
	PAR30	84380	12	3000	900	21%	Better
	PAR30	84384	12	3000	850	21%	Better
	PAR30	84392	12	2700	900	21%	Better
	PAR30	84395	12	2700	850	21%	Better
	PAR30	84399	12	3000	900	21%	Better
	PAR30	84400	12	3000	900	21%	Better
	PAR30	84407	12	2700	850	21%	Better
	PAR30L	42136	12	3000	1050	21%	Better
	PAR30L	42137	12	3000	1050	21%	Better
	PAR30L	42144	12	3000	1000	21%	Better
	PAR38	65727	18	3000	1550	17%	Better
	PAR38	65730	18	5000	1700	17%	Better
	PAR38	65731	18	5000	1700	17%	Better
	PAR38	70962	18	2700	1300	17%	Better
	PAR38	91286	18	2700	1300	17%	Better
	PAR38	92923	18	2700	1250	17%	Better
	PAR38	92926	18	2700	1250	17%	Better
	PAR38	92927	18	2700	1350	17%	Better
	PAR38	92933	18	3000	1350	17%	Better
	PAR38	92934	18	3000	1350	17%	Better
	PAR38	92944	18	3000	1550	17%	Better
	PAR38	92950	18	2700	1550	17%	Better
	PAR38	92958	18	2700	1550	17%	Better
	PAR38	92961	18	3000	1750	17%	Better
	PAR38	92963	18	3000	1550	17%	Better
	PAR38	92967	18	3000	1550	17%	Better
	PAR38	92969	12	2700	1050	17%	Better
	PAR38	92971	12	2700	1050	17%	Better
	PAR38	92972	12	3000	1050	17%	Better
PAR38	92973	12	3000	1050	17%	Better	
PAR38	93171	18	4000	1700	17%	Better	
PAR38	93172	18	4000	1700	17%	Better	
Halco	A19	80842	7	3000	500	21%	Better
	A19	80864	10.5	3000	820	10%	Better
	BR30	80181	10	4000	750	2%	Better
	PAR20	82006	7	2700	460	20%	Better
	PAR30	82016	10	4000	820	15%	Better
	PAR30S	82029	10	4000	820	30%	Better
	PAR38	82040	15	4000	1020	26%	Better
PAR38	82050	17	4000	1220	8%	Better	
Kobi	A19	LED-ASD-15W1100-27	15	2700	1000	4%	Better
Lighting Science	A19	LSGP19W2740WEFR120	6	2700	480	21%	Better
	B11	LSB11CAW2740WECLE12120	4.5	2700	350	29%	Better
	B11	LSB11CAW2740WECLE26120	4.5	2700	350	29%	Better
	G25	DFN2560WEW27120	8.5	2700	650	22%	Better
	PAR30	LS3075WEWWFL120	14	3000	900	7%	Better
	PAR30	LS3075WEWWGBFL120	10.5	3000	750	16%	Better
	PAR30-Short-Neck	LS30SN75WEWWFL120	14.5	3000	950	7%	Better
	PAR38	G3TP120-16/PAR38-DIM-3000K-25°	16	3000		1%	Better
PAR38	LED21WPAR383000K40°DIM	21	3000		1%	Better	
Philips	A19	9290002268	11	2700	830	2%	Better
	A19	9290011176	6.5	2700	450	7%	Better
	A19	9290011345	9.5	2200-2700	800	6%	Better
	A19	12E26A60-1	12.5	2700	800	5%	Better
	A21	9290002290	22	2700	1780	1%	Better
	A21	9290011120	13	2700	1100	26%	Better
	A21	17E26A21D	17	2700	1100	6%	Better
	BR30	9290002197	13	2700	730	5%	Better
	BR30	9290011117	9.5	2700	730	9%	Better
	BR40	9290002199	14.5	2700	800	6%	Better
	BR40	9290002580	12	2700	800	2%	Better
	GU10	929001156504	5	2700	400	5%	Better

Philips	PAR20	9290002333	8	2700	450	2%	Better
	PAR30L	9290002235	13	3000	750	7%	Better
	PAR38	9290002252	19.5	2700	1100	5%	Better
Satco	A19	S9037	10.5	2700	810	6%	Better
	A19	S9107	7	2700	450	13%	Better
	A19	S9252	6.5	2700	800	28%	Better
	A19	S9612	10.5	2700	800	12%	Better
	B11-Bent-Candle	S9265	4.5	2700	450	36%	Better
	BR30	S9025	12.8	750	750	16%	Better
	BR30	S9133	10	2700	750	2%	Better
	BR40	S9144	12	2700	900	13%	Better
	R20	S9073	7.8	2200-2700	460	23%	Better
	R20	S9140	7	525	525	7%	Better
	R40	S9101	16	2200-2700	1000	22%	Better
Vintage	S9270	2.5	2300	220	34%	Better	
Sylvania	PAR30LN	LED13PAR30LN/DIM/850/NFL25/G3	13	5000	850	9%	Better
	PAR38	LED16PAR38/DIM/830/FL40/G3	16	3000	1050	7%	Better
	PAR38	LED17PAR38/DIM/840/NFL25/P3	17	4000	1300	21%	Better
	PAR38	LED17PAR38/DIM/850/NFL25/GL1	17	5000	1300	14%	Better
	Recessed-Kit	LED/1100/LD/850/RP	13	5000	1100	9%	Better
	Recessed-Kit	LED/700/LD/830/FL120	10	3000	700	8%	Better
	Recessed-Kit	LED/RT/5/6/900/830/FL80 2/CS 1/SKU	13	3000	900	9%	Better
	Recessed-Kit	LED/RT/5/6/G/900/827/FL80/RP	13	2700	900	9%	Better
	Recessed-Kit	LED/RT/5/6/G/900/830	13	3000	900	9%	Better
	Recessed-Kit	LED/RT/5/6/HO/700/827	8	2700	700	3%	Better
	Recessed-Kit	LED/RT/5/6/HO/700/830	8	3000	700	3%	Better
	Recessed-Kit	LED/RT/5/6/HO/700/835	8	3500	700	3%	Better
	Recessed-Kit	LED/RT4/600/827/1PK	9	2700	600	10%	Better
	Recessed-Kit	LED/RT4/600/827/FL80	9	2700	600	10%	Better
	Recessed-Kit	LED/RT4/600/830/FL80	9	3000	600	10%	Better
	Recessed-Kit	LED/RT4/600/830/FL80/RP	9	3000	600	10%	Better
	Recessed-Kit	LED/RT4/600/840/FL80	9	4000	600	10%	Better
	Recessed-Kit	LED/RT4/600/850/FL80	9	5000	600	10%	Better
	Recessed-Kit	LED/RT5/6/700/840/FL80	10	4000	700	12%	Better
	Recessed-Kit	LED/RT5/6/900/827/FL80	13	2700	900	9%	Better
	Recessed-Kit	LED/RT5/6/G/900/830/FL80/RP	13	3000	900	9%	Better
	Recessed-Kit	LED/RT5/6/HO/700/840	8	4000	700	3%	Better
	Recessed-Kit	LEDRT/5/6/700/850/FL80 2/CS 1/SKU	10	5000	700	12%	Better
Recessed-Kit	LEDRT56700827FL80 2/CS 1/SKU	10	2700	700	12%	Better	
Recessed-Kit	LEDRT56700830FL80 2/CS 1/SKU	10	3000	700	12%	Better	
Recessed-Kit	LEDRT56900830RP	13	3000	900	9%	Better	
TCP	A19	ES95A1940SWD4	7	2700	450	15%	Better
	A19	ES95A1960SWD4	11	2700	800	12%	Better
	A19	ES95A19GU60SWD	11	2700	800	11%	Better
	BR30	ES95BR3065SWD6	9	2700	650	10%	Better
	GU10	ES95GU1050BWD3	7	3000	500	15%	Better
	P20	ES95P2050BWD2	8	3000	500	14%	Better
	P30	ES95P3075BWD2	10	3000	750	10%	Better
	P38	ES95P3890BWD2	13	3000	850	13%	Better

LED Bulb Compatibility
Decora® Digital Dimmer
with Bluetooth® Technology DDL06-BL



Manufacturer	Type	Model #	Wattage	Color (K)	Lumens	Minimum Brightness (% of full Brightness)	Performance
Buckingham	Fixed Track	1001573381	21	2700	1100	7%	Better
	Track Lighting (x3)	1001279379	27	2700	1150	5%	Better
	Track Lighting (x3)	1001279386	50	2700	2600	1%	Better
Bulbrite	A19	774101 LED11A19/827/D	11	2700	800	29%	Better
	A19	774103 LED15/A21/827/D	15.5	2700	1600	10%	Better
	A21	774102 LED13A21/827/D	13	2700	1100	11%	Better
	BR30	772810 LED16BR30/C/927/D	16.5	2700	975	24%	Better
	BR30	772840 LED12BR30/827/D/2	12.5	2700	1050	6%	Better
	BR30	773355 LED11BR30/827/D/2	11	2700	750	13%	Better
	G5	771172 LED6MR16GU/30K/D-SN	6	3000	300	6%	Better
	MR16	771200 LEDMR16SW/D/E26	6	3000	300	7%	Better
	PAR20	772714 LED7PAR20/NF25/830/WD	7	3000	525	13%	Better
	PAR30	772631 LED13PAR30L/FL40/930/WD	13	3000	820	5%	Better
	PAR30	772734 LED13PAR30L/FL40/830/WD	13	3000	1000	18%	Better
	PAR30S	772621 LED13/PAR30S/FL40/930/WD	13	3000	820	6%	Better
	PAR30S	772724 led13par30s/fl40/830/wd	13	3000	1000	6%	Better
	PAR38	772641 LED18PAR38/FL40/930/WD	18	3000	1150	5%	Better
	PAR38	772744 LED15PAR38/FL40/830/WD	15	3000	1200	5%	Better
R20	773255 LED8R20/827/D/2	8	2700	535	19%	Better	
Commercial Electric	Recessed-Kit	CE-JB6-650L-27K-E26	12.5	2700	670	7%	Better
Cree	A19	BA19-04527OMB-12DE26-3_1	6	2700	460	10%	Better
	A19	BA19-08027OMB-12DE26-3_1	10	2700	815	6%	Better
	A19	BA19-11027OMF-12DE26-1U100	13.5	2700	1100	22%	Better
	A21	BA21-16027OMF-12DE26-1U110	18	2700	1600	6%	Better
	BR30	BBR30-06527FLF-12DE26-4U100	9	2700	655	4%	Better
	PAR30	BPAR30L-0803040C-12DE26-1C_00	10.5	3000	850	4%	Better
	PAR30	BPAR30S-0803025C-12DE26-1C_00	11	3000	850	6%	Better
	PAR38	BPAR38-1503027T-12DE26-2U_00	18	3000	1500	14%	Better
Ecosmart	A15	1001653696 ECS A15 60WE W27 120 G	6	2700	500	15%	Better
	A15	1001653702 ECS A15 40WE W27 120 G	4	2700	330	21%	Better
	A15	1001684222 ECS A15 60WE W27 E12 1	6	2700	500	9%	Better
	B11	1001604600 ECS B11 CA 40WE W27 LP	4	2700	350	18%	Better
	B11	1001604604 ECS B11 CA 25WE W27 LP	3	2700	500	20%	Better
	B11	1001659350 ECS B11 60WE W27 E12 1	6	2700	500	9%	Better
	BR40	ECSBR4075WEW27120G1BL	13	2700	940	8%	Better
	G16.5	1001653709 ECS G16.5 60WE CW LP C	6.5	5000	500	28%	Better
	G16.5	1001654224 ECS G16.5 60WE W27 LP C	6.5	2700	500	11%	Better
	G25	1001659342 ECS 25 40WE W27 LP FR 1	4.5	2700	500	23%	Better
G25	1001696048 ECS 25 60WE W27 LP FR 1	6	2700	200	23%	Better	
GE	A19	13791	10.5	2700	800	14%	Better
	A19	14203	10.5	2700	800	14%	Better
	A19	83570	10.5	2700	800	14%	Better
	A19	89943	10.5	5000	850	14%	Better
	A19	95927	10.5	5000	850	14%	Better
	BR30	21907	10	2700	700	9%	Better
	BR30	68160	10	2700	700	9%	Better
	BR30	68161	10	3000	700	9%	Better
	BR30	89936	10	2700	700	9%	Better
	BR30	89942	10	5000	700	9%	Better
	PAR30	42131	12	3000	1050	19%	Better
	PAR30	42133	12	2700	1050	19%	Better
	PAR30	42134	12	2700	1000	19%	Better
	PAR30	73583	12	2700	1000	19%	Better

GE	PAR30	84379	12	3000	860	19%	Better
	PAR30	84380	12	3000	900	19%	Better
	PAR30	84384	12	3000	850	19%	Better
	PAR30	84392	12	2700	900	19%	Better
	PAR30	84395	12	2700	850	19%	Better
	PAR30	84399	12	3000	900	19%	Better
	PAR30	84400	12	3000	900	19%	Better
	PAR30	84407	12	2700	850	19%	Better
	PAR30L	42136	12	3000	1050	19%	Better
	PAR30L	42137	12	3000	1050	19%	Better
	PAR30L	42144	12	3000	1000	19%	Better
	PAR38	65727	18	3000	1550	16%	Better
	PAR38	65730	18	5000	1700	16%	Better
	PAR38	65731	18	5000	1700	16%	Better
	PAR38	70962	18	2700	1300	16%	Better
	PAR38	91286	18	2700	1300	16%	Better
	PAR38	92923	18	2700	1250	16%	Better
	PAR38	92926	18	2700	1250	16%	Better
	PAR38	92927	18	2700	1350	16%	Better
	PAR38	92933	18	3000	1350	16%	Better
	PAR38	92934	18	3000	1350	16%	Better
	PAR38	92944	18	3000	1550	16%	Better
	PAR38	92950	18	2700	1550	16%	Better
	PAR38	92958	18	2700	1550	16%	Better
	PAR38	92961	18	3000	1750	16%	Better
	PAR38	92963	18	3000	1550	16%	Better
	PAR38	92967	18	3000	1550	16%	Better
	PAR38	92969	12	2700	1050	16%	Better
	PAR38	92971	12	2700	1050	16%	Better
	PAR38	92972	12	3000	1050	16%	Better
PAR38	92973	12	3000	1050	16%	Better	
PAR38	93171	18	4000	1700	16%	Better	
PAR38	93172	18	4000	1700	16%	Better	
Halco	A19	80842	7	3000	500	18%	Better
	BR30	80181	10	4000	750	4%	Better
	PAR20	82006	7	2700	460	24%	Better
	PAR30	82016	10	4000	820	27%	Better
	PAR30S	82029	10	4000	820	21%	Better
	PAR38	82040	15	4000	1020	6%	Better
	PAR38	82050	17	4000	1220	5%	Better
Kobi	A19	LED-ASD-15W1100-27	15	2700	1000	15%	Better
	R30	LED-R30-11W700-27	11	2700	700	13%	Better
Satco	A19	S9037	10.5	2700	810	3%	Better
	A19	S9107	7	2700	450	9%	Better
	A19	S9252	6.5	2700	800	27%	Better
	A19	S9612	10.5	2700	800	31%	Better
	B11-Bent-Candle	S9265	4.5	2700	450	33%	Better
	BR30	S9133	10	2700	750	0%	Better
	BR40	S9144	12	2700	900	9%	Better
	R20	S9140	7	525	525	4%	Better
Vintage	S9270	2.5	2300	220	9%	Better	
Sylvania	PAR30LN	LED13PAR30LN/DIM/850/NFL25/G3	13	5000	850	27%	Better
	PAR38	LED16PAR38/DIM/830/FL40/G3	16	3000	1050	5%	Better
	PAR38	LED17PAR38/DIM/840/NFL25/P3	17	4000	1300	19%	Better
	PAR38	LED17PAR38/DIM/850/NFL25/GL1	17	5000	1300	17%	Better
	Recessed-Kit	LED/1100/LD/850/RP	13	5000	1100	6%	Better
	Recessed-Kit	LED/900/LD/830/FL120	13	3000	900	7%	Better
	Recessed-Kit	LED/900/LD/830/FL120/RP	13	3000	900	7%	Better
	Recessed-Kit	LED/RT/5/6/900/830/FL80 2/CS 1/SKU	13	3000	900	6%	Better
	Recessed-Kit	LED/RT/5/6/G/900/827/FL80/RP	13	2700	900	5%	Better
	Recessed-Kit	LED/RT/5/6/G/900/830	13	3000	900	5%	Better
	Recessed-Kit	LED/RT/5/6/HO/700/827	8	2700	700	0%	Better
Recessed-Kit	LED/RT/5/6/HO/700/830	8	3000	700	0%	Better	

Sylvania	Recessed-Kit	LED/RT/5/6/HO/700/835	8	3500	700	0%	Better
	Recessed-Kit	LED/RT4/600/827/1PK	9	2700	600	7%	Better
	Recessed-Kit	LED/RT4/600/827/FL80	9	2700	600	7%	Better
	Recessed-Kit	LED/RT4/600/830/FL80	9	3000	600	7%	Better
	Recessed-Kit	LED/RT4/600/830/FL80/RP	9	3000	600	7%	Better
	Recessed-Kit	LED/RT4/600/840/FL80	9	4000	600	7%	Better
	Recessed-Kit	LED/RT4/600/850/FL80	9	5000	600	7%	Better
	Recessed-Kit	LED/RT5/6/900/827/FL80	13	2700	900	6%	Better
	Recessed-Kit	LED/RT5/6/G/900/830/FL80/RP	13	3000	900	5%	Better
	Recessed-Kit	LED/RT5/6/HO/700/840	8	4000	700	0%	Better
	Recessed-Kit	LEDRT56900830RP	13	3000	900	6%	Better
TCP	A19	ES95A1940SWD4	7	2700	450	11%	Better
	A19	ES95A1960SWD4	11	2700	800	8%	Better
	A19	ES95A19GU60SWD	11	2700	800	7%	Better
	A21	ES95A2175SWD2	15	2700	1100	5%	Better
	BR30	ES95BR3065SWD6	9	2700	650	6%	Better
	P20	ES95P2050BWD2	8	3000	500	10%	Better
	P30	ES95P3075BWD2	10	3000	750	6%	Better
	P38	ES95P3890BWD2	13	3000	850	9%	Better
	R20	ES95R2050SWD3	7	2700	500	16%	Better

LED Bulb Compatibility
Decora® Digital Dimmer DDL06-1L



Manufacturer	Type	Model #	Wattage	Color (K)	Lumens	Minimum Brightness (% of full Brightness)	Performance
Buckingham	Fixed Track	1001573381	21	2700	1100	7%	Better
	Track Lighting (x3)	1001279379	27	2700	1150	5%	Better
	Track Lighting (x3)	1001279386	50	2700	2600	1%	Better
Bulbrite	A19	774101 LED11A19/827/D	11	2700	800	12%	Better
	A19	774103 LED15/A21/827/D	15.5	2700	1600	9%	Better
	A21	774102 LED13A21/827/D	13	2700	1100	11%	Better
	BR30	772810 LED16BR30/C/927/D	16.5	2700	975	10%	Better
	BR30	772840 LED12BR30/827/D/2	12.5	2700	1050	5%	Better
	BR30	773355 LED11BR30/827/D/2	11	2700	750	13%	Better
	BR40	772850 LED20BR40/827/D/2	20	2700	1750	5%	Better
	G5	771172 LED6MR16GU/30K/D-SN	6	3000	300	6%	Better
	MR16	771200 LEDMR16SW/D/E26	6	3000	300	4%	Better
	PAR20	772714 LED7PAR20/NF25/830/WD	7	3000	525	10%	Better
	PAR30	772631 LED13PAR30L/FL40/930/WD	13	3000	820	5%	Better
	PAR30	772734 LED13PAR30L/FL40/830/WD	13	3000	1000	5%	Better
PAR38	772641 LED18PAR38/FL40/930/WD	18	3000	1150	4%	Better	
R20	773255 LED8R20/827/D/2	8	2700	535	11%	Better	
Commercial Electric	Recessed-Kit	CE-JB6-650L-27K-E26	12.5	2700	670	13%	Better
Cree	A19	BA19-04527OMB-12DE26-3_1	6	2700	460	3%	Better
	A21	BA21-16027OMF-12DE26-1U110	18	2700	1600	6%	Better
	BR30	BBR30-06527FLF-12DE26-4U100	9	2700	655	4%	Better
	PAR30	BPAR30L-0803040C-12DE26-1C_0C	10.5	3000	850	3%	Better
	PAR30	BPAR30S-0803025C-12DE26-1C_0C	11	3000	850	3%	Better
	PAR38	BPAR38-1503027T-12DE26-2U_0C	18	3000	1500	6%	Better
Ecosmart	A15	1001653696 ECS A15 60WE W27 120 G1	6	2700	500	14%	Better
	A15	1001684222 ECS A15 60WE W27 E12 12C	6	2700	500	8%	Better
	B11	1001604594 ECS B11 CA 25WE W27 LP E12 12C	3	2700	200	12%	Better
	BR40	ECSBR4075WEW27120G1BL	13	2700	940	7%	Better
	G16.5	1001653709 ECS G16.5 60WE CW LP CL E12 12C	6.5	5000	500	9%	Better
	G25	1001659342 ECS 25 40WE W27 LP FR 12C	4.5	2700	500	9%	Better
	G25	1001696048 ECS 25 60WE W27 LP FR 12C	6	2700	200	11%	Better
GE	A19	13791	10.5	2700	800	12%	Better
	A19	14203	10.5	2700	800	12%	Better
	A19	83570	10.5	2700	800	12%	Better
	A19	89943	10.5	5000	850	12%	Better
	A19	95927	10.5	5000	850	12%	Better
	BR30	21907	10	2700	700	8%	Better
	BR30	68160	10	2700	700	8%	Better
	BR30	68161	10	3000	700	8%	Better
	BR30	89936	10	2700	700	8%	Better
	BR30	89942	10	5000	700	8%	Better
	PAR38	65727	18	3000	1550	7%	Better
	PAR38	65730	18	5000	1700	7%	Better
	PAR38	65731	18	5000	1700	7%	Better
	PAR38	70962	18	2700	1300	7%	Better
	PAR38	91286	18	2700	1300	7%	Better
	PAR38	92923	18	2700	1250	7%	Better
	PAR38	92926	18	2700	1250	7%	Better
	PAR38	92927	18	2700	1350	7%	Better
PAR38	92933	18	3000	1350	7%	Better	
PAR38	92934	18	3000	1350	7%	Better	

GE	PAR38	92944	18	3000	1550	7%	Better
	PAR38	92950	18	2700	1550	7%	Better
	PAR38	92958	18	2700	1550	7%	Better
	PAR38	92961	18	3000	1750	7%	Better
	PAR38	92963	18	3000	1550	7%	Better
	PAR38	92967	18	3000	1550	7%	Better
	PAR38	92969	12	2700	1050	7%	Better
	PAR38	92971	12	2700	1050	7%	Better
	PAR38	92972	12	3000	1050	7%	Better
	PAR38	92973	12	3000	1050	7%	Better
	PAR38	93171	18	4000	1700	7%	Better
	PAR38	93172	18	4000	1700	7%	Better
Halco	A19	80842	7	3000	500	19%	Better
	BR30	80181	10	4000	750	2%	Better
	PAR20	82006	7	2700	460	15%	Better
	PAR30	82016	10	4000	820	8%	Better
	PAR30S	82029	10	4000	820	10%	Better
	PAR38	82040	15	4000	1020	5%	Better
	PAR38	82050	17	4000	1220	4%	Better
Kobi	A19	LED-ASD-15W1100-27	15	2700	1000	2%	Better
	R30	LED-R30-11W700-27	11	2700	700	12%	Better
Satco	A19	S9037	10.5	2700	810	3%	Better
	A19	S9107	7	2700	450	8%	Better
	A19	S9252	6.5	2700	800	10%	Better
	A19	S9612	10.5	2700	800	8%	Better
	B11-Bent-Candle	S9265	4.5	2700	450	11%	Better
	BR30	S9133	10	2700	750	3%	Better
	BR40	S9144	12	2700	900	8%	Better
	R20	S9140	7	525	525	3%	Better
Vintage	S9270	2.5	2300	220	9%	Better	
Sylvania	PAR30LN	LED13PAR30LN/DIM/850/NFL25/G3	13	5000	850	5%	Better
	PAR38	LED16PAR38/DIM/830/FL40/G3	16	3000	1050	4%	Better
	PAR38	LED17PAR38/DIM/840/NFL25/P3	17	4000	1300	9%	Better
	PAR38	LED17PAR38/DIM/850/NFL25/GL1	17	5000	1300	6%	Better
	Recessed-Kit	LED/1100/LD/850/RP	13	5000	1100	5%	Better
	Recessed-Kit	LED/900/LD/830/FL120	13	3000	900	6%	Better
	Recessed-Kit	LED/900/LD/830/FL120/RP	13	3000	900	6%	Better
	Recessed-Kit	LED/RT/5/6/900/830/FL80 2/CS 1/SKU	13	3000	900	5%	Better
	Recessed-Kit	LED/RT/5/6/G/900/827/FL80/RP	13	2700	900	5%	Better
	Recessed-Kit	LED/RT/5/6/G/900/830	13	3000	900	5%	Better
	Recessed-Kit	LED/RT/5/6/HO/700/827	8	2700	700	2%	Better
	Recessed-Kit	LED/RT/5/6/HO/700/830	8	3000	700	2%	Better
	Recessed-Kit	LED/RT/5/6/HO/700/835	8	3500	700	2%	Better
	Recessed-Kit	LED/RT4/600/827/1PK	9	2700	600	6%	Better
	Recessed-Kit	LED/RT4/600/827/FL80	9	2700	600	6%	Better
	Recessed-Kit	LED/RT4/600/830/FL80	9	3000	600	6%	Better
	Recessed-Kit	LED/RT4/600/830/FL80/RP	9	3000	600	6%	Better
	Recessed-Kit	LED/RT4/600/840/FL80	9	4000	600	6%	Better
	Recessed-Kit	LED/RT4/600/850/FL80	9	5000	600	6%	Better
	Recessed-Kit	LED/RT5/6/900/827/FL80	13	2700	900	5%	Better
Recessed-Kit	LED/RT5/6/G/900/830/FL80/RP	13	3000	900	5%	Better	
Recessed-Kit	LED/RT5/6/HO/700/840	8	4000	700	2%	Better	
Recessed-Kit	LEDRT56900830RP	13	3000	900	5%	Better	
TCP	A19	ES95A19GU60SWD	11	2700	800	6%	Better
	P20	ES95P2050BWD2	8	3000	500	8%	Better
	P38	ES95P3890BWD2	13	3000	850	7%	Better

LED Bulb Compatibility
Decora Rocker Slide DSL06



Manufacturer	Type	Model #	Wattage	Color (K)	Lumens	Minimum Brightness (% of full Brightness)	Performance
Buckingham	Fixed Track Lighting	1001573381	21W	2700	1100	6%	Better
	Track Lighting (x3)	939044	17.5	2700	420	2%	Better
	Track Lighting (x3)	1001279379	27	2700	1150	9%	Better
	Track Lighting (x3)	1001279383	14	2700	820	6%	Better
	Track Lighting (x3)	1001279386	50	2700	2600	1%	Better
	Under Cabinet	205663883	9	3000	450	3%	Better
	Under Cabinet	1001217444	15	3000	690	1%	Better
	Under Cabinet	1001217457	17	3000	790	6%	Better
Under Cabinet	1001217466	6	3000	280	3%	Better	
Commercial Electric	Recessed-Kit	CE-JB6-650L-27K-E26	12.5	2700	670	14%	Better
Cree	PAR30	BPAR30L-0803040C-12DE26-1C_00	10.5	3000	850	4%	Better
	PAR30	BPAR30S-0803025C-12DE26-1C_00	11	3000	850	12%	Better
	PAR38	BPAR38-1503027T-12DE26-2U_00	18	3000	1500	22%	Better
EcoSmart	A15	1001653702 ECS A15 40WE W27 120 G1	4	2700	330	23%	Better
	B11	1001604604 ECS B11 CA 25WE W27 LP E26 120	3	2700	500	16%	Better
	BR20	ECSBR2050WECW120DG	7.5	5000	600	11%	Better
	BR30	ECSBR3065WEWW120DG	9.5	3000	650	21%	Better
	BR30	LSBR30CECWWCRI90E26	13.2	3000	-	11%	Better
	BR40	ECSBR4075WEW27120G1BL	13	2700	940	1%	Better
	BR40	ECSBR4090WEW27120DG	12.7	2700	-	8%	Better
	G25	ECS2540WEW27120DG	5.5	2700	400	12%	Better
	G25	ECS2560WEW27120DG	7	2700	-	14%	Better
	Recessed-Kit	ECS DN6 W27 E26 120	9.5	2700	650	17%	Better
Recessed-Kit	LSGLP6W27120WHS1BX	13	2700	-	15%	Better	
Feit-Utilitech Pro	A19	BPAGOM800/5K/LED	9.5	5000	810	10%	Better
GE	A19	13791	10.5	2700	800	15%	Better
	A19	14203	10.5	2700	800	15%	Better
	A19	83570	10.5	2700	800	15%	Better
	A19	89943	10.5	5000	850	15%	Better
	A19	95927	10.5	5000	850	15%	Better
	BR30	21907	10	2700	700	12%	Better
	BR30	68160	10	2700	700	12%	Better
	BR30	68161	10	3000	700	12%	Better
	BR30	89936	10	2700	700	12%	Better
	BR30	89942	10	5000	700	12%	Better
	PAR30	42131	12	3000	1050	13%	Better
	PAR30	42133	12	2700	1050	13%	Better
	PAR30	42134	12	2700	1000	13%	Better
	PAR30	73583	12	2700	1000	13%	Better
	PAR30	84379	12	3000	860	13%	Better
	PAR30	84380	12	3000	900	13%	Better
	PAR30	84384	12	3000	850	13%	Better
	PAR30	84392	12	2700	900	13%	Better
	PAR30	84395	12	2700	850	13%	Better
	PAR30	84399	12	3000	900	13%	Better
	PAR30	84400	12	3000	900	13%	Better
	PAR30	84407	12	2700	850	13%	Better
	PAR30L	42136	12	3000	1050	13%	Better
PAR30L	42137	12	3000	1050	13%	Better	
PAR30L	42144	12	3000	1000	13%	Better	
Halco	A19	80842	7	3000	500	25%	Better
	A19	80864	10.5	3000	820	11%	Better
	BR30	80181	10	4000	750	4%	Better
	PAR20	82006	7	2700	460	23%	Better
	PAR30S	82029	10	4000	820	24%	Better
	PAR38	82040	15	4000	1020	27%	Better
	PAR38	82050	17	4000	1220	3%	Better
Juno	4" Recessed Kit	4RLD-927-6-WWH	11.2	2700	572	24%	Better
	6" Recessed Kit	6RLD-927-6-WWH	11.2	2700	619	3%	Better
Kobi	R30	LED-R30-11W700-27	11	2700	700	16%	Better
Lighting Science	A19	LSGP19W2740WFEFR120	6	2700	480	1%	Better
	BR30	LSPRO BR30 65WE W27 120 FS1 BX	10	2700	650	0%	Better
	BR30	LSPRO BR30 75WE W27 120 FS1 BX	15	2700	940	0%	Better
	BR40	LSPRO BR40 75WE W27 120 FS1 BX	15	2700	940	1%	Better
	BR40	LSPRO BR40 90WE W27 120 FS1 BX	20	2700	1260	3%	Better

Lighting Science	GU10	LSPro 16 35WE W27 FL GU10 BX	6	2700	350	22%	Better
	GU10	LSPro 16 50WE W27 FL GU10 BX	8	2700	480	4%	Better
	PAR20	LS2050WEWWFL120	8	3000	525	2%	Better
	PAR20	LSPro 50WE W27 FL 120 BX	9	2700	420	21%	Better
	PAR30	LS3075WEWWFL120	14	3000	900	0%	Better
	PAR30	LS3075WEWWGBFL120	10.5	3000	750	22%	Better
	PAR30	LSPro 30 75WE W27 FL 120 BX	14	2700	680	4%	Better
	PAR30 Short Neck	LS30SN75WEWWFL120	14.5	3000	950	2%	Better
	PAR38	G3TP120-16/PAR38-DIM-3000K-25°	16	3000	-	21%	Better
	PAR38	LED21WPAR383000K40°DIM	21	3000	-	4%	Better
	PAR38	LSPro 38 120WE W27 NFL 120 BX	19	2700	1350	8%	Better
	PAR38	LSPro 38 90WE W27 FL 120 BX	17	2700	840	9%	Better
R20	LSPro R20 50WE W27 120 FS1 BX	8	2700	525	3%	Better	
Philips	A19	9290011176	6.5	2700	450	7%	Better
	A19	9290011345	9.5	2200-2700	800	6%	Better
	A19 Edison	9290002268	11	2700	830	2%	Better
	A19 Edison	12E26A60-1	12.5	2700	800	2%	Better
	A21	9290011120	13	2700	1100	9%	Better
	A21 Edison	17E26A21D	17	2700	1100	2%	Better
	B13	9290011121	6.5	2700	520	2%	Better
	BR30	9290011117	9.5	2700	730	9%	Better
	BR30 Edison	9290002197	13	2700	730	3%	Better
	BR40 Edison	9290002199	14.5	2700	800	4%	Better
	GU10	929001156504	5	2700	400	1%	Better
	PAR30L Edison	9290002235	13	3000	750	4%	Better
	PAR38 Edison	9290002252	19.5	2700	1100	3%	Better
Satco	A19	S9107	7	2700	450	1%	Better
	A19	S9244	12	5000	1230	4%	Better
	A19	S9608	9	4000	830	4%	Better
	A19	S9312	10.5	2700	800	12%	Better
	A21	S92871	16	5000	1800	3%	Better
	BR30	S9133	10	2700	750	5%	Better
	BR40	S9144	12	2700	900	1%	Better
	PAR20	S9409	7	5000	525	6%	Better
	PAR30	S9424	13	5000	1000	6%	Better
	PAR38	S9454	15	5000	1200	5%	Better
	PAR38	S9456	18	4000	1400	5%	Better
	R20	S9140	7	525	525	1%	Better
R40	S9101	16	2200-2700	1000	1%	Better	
Sylvania	PAR16	LED7PAR16/DIM/830/FL36	7	3000	350	8%	Better
	PAR30LN	LED13PAR30LN/DIM/850/NFL25/G3	13	5000	850	3%	Better
	PAR38	LED16PAR38/DIM/830/FL40/G3	16	3000	1050	2%	Better
	PAR38	LED17PAR38/DIM/840/NFL25/P3	17	4000	1300	12%	Better
	PAR38	LED17PAR38/DIM/850/NFL25/GL1	17	5000	1300	15%	Better
	Recessed-Kit	LED/1100/LD/850/RP	13	5000	1100	18%	Better
	Recessed-Kit	LED/700/LD/830/FL120	10	3000	700	22%	Better
	Recessed-Kit	LED/900/LD/830/FL120	13	3000	900	17%	Better
	Recessed-Kit	LED/900/LD/830/FL120/RP	13	3000	900	17%	Better
	Recessed-Kit	LED/RT/5/6/G/900/830/FL80 2/CS 1/SKU	13	3000	900	24%	Better
	Recessed-Kit	LED/RT/5/6/G/900/827/FL80/RP	13	2700	900	24%	Better
	Recessed-Kit	LED/RT/5/6/G/900/830	13	3000	900	24%	Better
	Recessed-Kit	LED/RT/5/6/HO/700/827	8	2700	700	3%	Better
	Recessed-Kit	LED/RT/5/6/HO/700/830	8	3000	700	3%	Better
	Recessed-Kit	LED/RT/5/6/HO/700/835	8	3500	700	3%	Better
	Recessed-Kit	LED/RT4/600/827/1PK	9	2700	600	19%	Better
	Recessed-Kit	LED/RT4/600/827/FL80	9	2700	600	19%	Better
	Recessed-Kit	LED/RT4/600/830/FL80	9	3000	600	19%	Better
	Recessed-Kit	LED/RT4/600/830/FL80/RP	9	3000	600	19%	Better
	Recessed-Kit	LED/RT4/600/840/FL80	9	4000	600	19%	Better
	Recessed-Kit	LED/RT4/600/850/FL80	9	5000	600	19%	Better
	Recessed-Kit	LED/RT4/G/600/827	9	2700	600	21%	Better
	Recessed-Kit	LED/RT4/G/600/830	7	3000	600	21%	Better
	Recessed-Kit	LED/RT5/6/700/840/FL80	10	4000	700	20%	Better
	Recessed-Kit	LED/RT5/6/900/827/FL80	13	2700	900	24%	Better
	Recessed-Kit	LED/RT5/6/G/900/830/FL80/RP	13	3000	900	24%	Better
	Recessed-Kit	LED/RT5/6/HO/700/840	8	4000	700	3%	Better
	Recessed-Kit	LEDRT5/6/700/850/FL80 2/CS 1/SKU	10	5000	700	20%	Better
Recessed-Kit	LEDRT56700827FL80 2/CS 1/SKU	10	2700	700	20%	Better	
Recessed-Kit	LEDRT56700830FL80 2/CS 1/SKU	10	3000	700	20%	Better	
Recessed-Kit	LEDRT56900830RP	13	3000	900	24%	Better	
TCP	A19	L10A19DODLC2	10	2700	800	6%	Better
	BR30	BR30004	10	2700	700	6%	Better

LED Bulb Compatibility
Decora Rocker Slide DSM10



Manufacturer	Type	Model #	Wattage	Color (K)	Lumens	Minimum Brightness (% of full Brightness)	Performance
Buckingham	Fixed Track Lighting	1001573381	21	2700	1100	9%	Better
	Track Lighting (x3)	939044	17.5	2700	420	4%	Better
	Track Lighting (x3)	1001279379	27	2700	1150	9%	Better
	Track Lighting (x3)	1001279386	50	2700	2600	4%	Better
	Under Cabinet	57005N-WH	5.8	3000	300	7%	Better
	Under Cabinet	205663883	9	3000	450	2%	Better
	Under Cabinet	1001217444	15	3000	690	7%	Better
	Under Cabinet	1001217457	17	3000	790	4%	Better
	Under Cabinet	1001217466	6	3000	280	2%	Better
Bulbrite	A19	774101 LED11A19/827/D	11	2700	800	18%	Better
	A19	774103 LED15/A21/827/D	15.5	2700	1600	17%	Better
	A21	774102 LED13A21/827/D	13	2700	1100	15%	Better
	BR30	772810 LED16BR30/C/927/D	16.5	2700	975	32%	Better
	BR30	772840 LED12BR30/827/D/2	12.5	2700	1050	8%	Better
	BR30	773355 LED11BR30/827/D/2	11	2700	750	18%	Better
	BR40	772850 LED20BR40/827/D/2	20	2700	1750	8%	Better
	G5	771172 LED6MR16GU/30K/D-SN	6	3000	300	17%	Better
	MR16	771200 LEDMR16SW/D/E26	6	3000	300	26%	Better
	PAR20	772714 LED7PAR20/NF25/830/WD	7	3000	525	6%	Better
	PAR30	772631 LED13PAR30L/FL40/930/WD	13	3000	820	6%	Better
	PAR30	772734 LED13PAR30L/FL40/830/WD	13	3000	1000	16%	Better
	PAR30S	772621 LED13/PAR30S/FL40/930/WD	13	3000	820	8%	Better
	PAR30S	772724 led13par30s/fl40/830/wd	13	3000	1000	8%	Better
	PAR38	772641 LED18PAR38/FL40/930/WD	18	3000	1150	13%	Better
	PAR38	772744 LED15PAR38/FL40/830/WD	15	3000	1200	6%	Better
R20	773255 LED8R20/827/D/2	8	2700	535	35%	Better	
Commercial Electric	Recessed-Kit	CE-JB6-650L-27K-E26	12.5	2700	670	15%	Better
Cree	PAR30	BPAR30L-0803040C-12DE26-1C_00	10.5	3000	850	17%	Better
	PAR30	BPAR30S-0803025C-12DE26-1C_00	11	3000	850	5%	Better
	PAR38	BPAR38-1503027T-12DE26-2U_00	18	3000	1500	28%	Better
	Recessed-Kit	DRDL4-05727009-12DE26-1C100	11.5	2700	575	19%	Better
Ecosmart	BR40	ECSBR4075WEW27120G1BL	13	2700	940	4%	Better
	Recessed-Kit	ECS DN6 W27 E26 120	9.5	2700	650	20%	Better
GE	A19	13791	10.5	2700	800	16%	Better
	A19	14203	10.5	2700	800	16%	Better
	A19	83570	10.5	2700	800	16%	Better
	A19	89943	10.5	5000	850	16%	Better
	A19	95927	10.5	5000	850	16%	Better
	PAR30	42131	12	3000	1050	14%	Better
	PAR30	42133	12	2700	1050	14%	Better
	PAR30	42134	12	2700	1000	14%	Better
	PAR30	73583	12	2700	1000	14%	Better
	PAR30	84379	12	3000	860	14%	Better
	PAR30	84380	12	3000	900	14%	Better
	PAR30	84384	12	3000	850	14%	Better
	PAR30	84392	12	2700	900	14%	Better
	PAR30	84395	12	2700	850	14%	Better
	PAR30	84399	12	3000	900	14%	Better
	PAR30	84400	12	3000	900	14%	Better

GE	PAR30	84407	12	2700	850	14%	Better
	PAR30L	42136	12	3000	1050	14%	Better
	PAR30L	42137	12	3000	1050	14%	Better
	PAR30L	42144	12	3000	1000	14%	Better
Halco	A19	80842	7	3000	500	26%	Better
	BR30	80181	10	4000	750	2%	Better
	PAR38	82040	15	4000	1020	3%	Better
	PAR38	82050	17	4000	1220	1%	Better
Juno	Recessed-Kit	4RLD-927-6-WWH	11.2	2700	572	1%	Better
	Recessed-Kit	6RLD-927-6-WWH	11.2	2700	619	24%	Better
Lighting Science	BR30	LSPRO BR30 65WE W27 120 FS1 BX	10	2700	650	0%	Better
	BR30	LSPRO BR30 75WE W27 120 FS1 BX	15	2700	940	0%	Better
	BR40	LSPRO BR40 75WE W27 120 FS1 BX	15	2700	940	1%	Better
	BR40	LSPRO BR40 90WE W27 120 FS1 BX	20	2700	1260	3%	Better
	MR16	LSPRO 16 35WE W27 FL BX	6	2700	300	22%	Best
	MR16	LSPRO 16 50WE W27 FL BX	8	2700	450	21%	Better
	PAR20	LSPRO 50WE W27 FL 120 BX	9	2700	420	6%	Better
	PAR38	LSPRO 38 120WE W27 NFL 120 BX	19	2700	1350	2%	Better
	PAR38	LSPRO 38 90WE W27 FL 120 BX	17	2700	840	3%	Better
Philips	R20	LSPRO R20 50WE W27 120 FS1 BX	8	2700	525	4%	Better
	A19	9290011176	6.5	2700	450	8%	Better
	A19	9290011345	9.5	2200-2700	800	6%	Better
Satco	BR30	9290011117	9.5	2700	730	10%	Better
	A19	S9037	10.5	2700	810	1%	Better
	A19	S9612	10.5	2700	800	13%	Better
	A21	S92871	16	5000	1800	4%	Better
	BR30	S9133	10	2700	750	5%	Better
	BR40	S9144	12	2700	900	0%	Better
	PAR30	S9424	13	5000	1000	6%	Better
	PAR38	S9454	15	5000	1200	6%	Better
Sylvania	R40	S9101	16	2200-2700	1000	0%	Better
	PAR30LN	LED13PAR30LN/DIM/850/NFL25/G3	13	5000	850	4%	Better
	PAR38	LED16PAR38/DIM/830/FL40/G3	16	3000	1050	3%	Better
	PAR38	LED17PAR38/DIM/840/NFL25/P3	17	4000	1300	13%	Better
	PAR38	LED17PAR38/DIM/850/NFL25/GL1	17	5000	1300	9%	Better
	Recessed-Kit	LED/1100/LD/850/RP	13	5000	1100	19%	Better
	Recessed-Kit	LED/700/LD/830/FL120	10	3000	700	24%	Better
	Recessed-Kit	LED/900/LD/830/FL120	13	3000	900	18%	Better
	Recessed-Kit	LED/900/LD/830/FL120/RP	13	3000	900	18%	Better
	Recessed-Kit	LED/RT/5/6/900/830/FL80 2/CS 1/SKU	13	3000	900	23%	Better
	Recessed-Kit	LED/RT/5/6/G/900/827/FL80/RP	13	2700	900	23%	Better
	Recessed-Kit	LED/RT/5/6/G/900/830	13	3000	900	23%	Better
	Recessed-Kit	LED/RT/5/6/HO/700/827	8	2700	700	3%	Better
	Recessed-Kit	LED/RT/5/6/HO/700/830	8	3000	700	3%	Better
	Recessed-Kit	LED/RT/5/6/HO/700/835	8	3500	700	3%	Better
	Recessed-Kit	LED/RT4/G/600/827	9	2700	600	22%	Better
	Recessed-Kit	LED/RT4/G/600/830	7	3000	600	22%	Better
	Recessed-Kit	LED/RT5/6/700/840/FL80	10	4000	700	21%	Better
	Recessed-Kit	LED/RT5/6/900/827/FL80	13	2700	900	23%	Better
	TCP	Recessed-Kit	LED/RT5/6/G/900/830/FL80/RP	13	3000	900	23%
Recessed-Kit		LED/RT5/6/HO/700/840	8	4000	700	3%	Better
Recessed-Kit		LEDRT/5/6/700/850/FL80 2/CS 1/SKU	10	5000	700	21%	Better
Recessed-Kit		LEDRT56700827FL80 2/CS 1/SKU	10	2700	700	21%	Better
Recessed-Kit		LEDRT56700830FL80 2/CS 1/SKU	10	3000	700	21%	Better
Recessed-Kit		LEDRT56900830RP	13	3000	900	23%	Better
A19		L10A19DODLC2	10	2700	800	0%	Better
P38		ES95P3890BWD2	13	3000	850	5%	Better

LED Bulb Compatibility
Decora Rocker Slide DSE06



Manufacturer	Type	Model #	Wattage	Color (K)	Lumens	Minimum Brightness (% of full Brightness)	Performance
Buckingham	Fixed Track Lighting	1001573381	21	2700	1100	4%	Better
	Puck (x5)	21325KIT	3.4	3000	865	1%	Better
	Track Lighting (x3)	939044	17.5	2700	420	1%	Better
	Track Lighting (x3)	1001279379	27	2700	1150	13%	Better
	Track Lighting (x3)	1001279383	14	2700	820	7%	Better
	Track Lighting (x3)	1001279386	50	2700	2600	4%	Better
	Under Cabinet	57005N-WH	5.8	3000	300	1%	Better
	Under Cabinet	205663883	9	3000	450	9%	Better
	Under Cabinet	1001217444	15	3000	690	7%	Better
Under Cabinet	1001217457	17	3000	790	3%	Better	
Under Cabinet	1001217466	6	3000	280	2%	Better	
Bulbrite	A19	776572 LED5A19/27K/FIL/2	5	2700	480	5%	Better
	A19	776602 LED5A19/22K/FIL-NOS/2	5	2200	400	5%	Better
	B11	776555 LED2B11/27K/FIL/E12	2	2700	200	1%	Best
	B11	776556 LED4B11/27K/FIL/E12	4	2700	350	1%	Best
	B11	776557 LED4B11/27K/FIL	4	2700	350	1%	Best
	B11	776568 LED2B11/27K/FIL/E12/F	2	2700	170	1%	Best
	B11	776569 LED4B11/27K/FIL/E12/F	4	2700	300	1%	Best
	CA10	776503 LED2CA10/22K/FIL-NOS	2	2200	180	1%	Best
	CA10	776558 LED2CA10/27K/FIL/E12	2	2700	190	1%	Best
	CA10	776559 LED4CA10/27K/FIL/E12	4	2700	320	1%	Best
	CA10	776560 LED4CA10/27K/FIL	4	2700	320	1%	Best
	CA10	776566 LED2CA10/27K/FIL/E12/F	2	2700	170	1%	Best
	CA10	776567 LED4CA10/27K/FIL/E12/F	4	2700	300	1%	Best
	G16	776506 LED2G16/22K/FIL-NOS	2	2200	180	1%	Best
	G16	776573 LED2G16/27K/FIL/E12	2	2700	170	1%	Best
	G25	776600 LED5G25/22K/FIL-NOS/2	5	2200	450	5%	Better
	ST18	776601 LED5ST18/22K/FIL-NOS/2	5	2200	450	5%	Better
	T14	776605 LED4T14/22K/FIL-NOS/2	4	2200	315	5%	Better
	T6	776504 LED2T6/22K/FIL-NOS	2	2200	180	1%	Best
	T9	776607 LED4T9L/22K/FIL-NOS/2	4	2200	350	5%	Better
	T9	776608 LED2T9/22K/FIL-NOS/2	2	2200	250	5%	Better
	T9	776653 LED2T9/27K/FIL/2	2	2700	300	5%	Better
	T9	776665 LED4T9L/27K/FIL/2	4	2700	450	5%	Better
Commercial Electric	Recessed-Kit	CE-JB6-650L-27K-E26	12.5	2700	670	7%	Better
Cree	PAR30	BPAR30L-0803040C-12DE26-1C_00	10.5	3000	850	4%	Best
	PAR30	BPAR30S-0803025C-12DE26-1C_00	11	3000	850	4%	Better
	PAR38	BPAR38-1503027T-12DE26-2U_00	18	3000	1500	5%	Better
	Recessed-Kit	DRDL4-05727009-12DE26-1C100	11.5	2700	575	32%	Better
Ecosmart	A15	1001653696 ECS A15 60WE W27 120 G1	6	2700	500	15%	Better
	A15	1001653702 ECS A15 40WE W27 120 G1	4	2700	330	21%	Better
	A15	1001684222 ECS A15 60WE W27 E12 120	6	2700	500	9%	Better
	B11	1001604600 ECS B11 CA 40WE W27 LP E12 120	4	2700	350	10%	Better
	B11	1001659350 ECS B11 60WE W27 E12 120	6	2700	500	10%	Better
	BR20	ECSBR2050WECW120DG	7.5	5000	600	11%	Best
	BR30	ECSBR3065WEWW120DG	9.5	3000	650	4%	Better
	BR40	ECSBR4075WEW27120G1BL	13	2700	940	6%	Better
	G16.5	1001653709 ECS G16.5 60WE CW LP CL E12 120	6.5	5000	500	10%	Better
	G16.5	1001654224 ECS G16.5 60WE W27 LP CL 120	6.5	2700	500	11%	Better
	G25	1001659342 ECS 25 40WE W27 LP FR 120	4.5	2700	500	11%	Better
	G25	1001696048 ECS 25 60WE W27 LP FR 120	6	2700	200	13%	Better
	G25	ECS2540WEW27120DG	5.5	2700	400	6%	Best
	G25	ECS2560WEW27120DG	7	2700	-	3%	Best
Recessed-Kit	ECS DN6 W27 E26 120	9.5	2700	650	6%	Better	
ETI	Retrofit	53166161	14	2700	650	1%	Better
	Retrofit	53170162	10	2700	600	2%	Better
Feit-Utilitech Pro	A19	BPAGOM800/5K/LED	9.5	5000	810	26%	Better
	A19	BPAGOM800/LED	9.5	3000	800	9%	Best
GE	A19	13791	10.5	2700	800	11%	Best
	A19	14203	10.5	2700	800	11%	Best
	A19	83570	10.5	2700	800	11%	Best

GE	A19	89943	10.5	5000	850	11%	Best
	A19	95927	10.5	5000	850	11%	Best
	BR30	21907	10	2700	700	9%	Best
	BR30	68160	10	2700	700	9%	Best
	BR30	68161	10	3000	700	9%	Best
	BR30	89936	10	2700	700	9%	Best
	BR30	89942	10	5000	700	9%	Best
	PAR30	42131	12	3000	1050	10%	Better
	PAR30	42133	12	2700	1050	10%	Better
	PAR30	42134	12	2700	1000	10%	Better
	PAR30	73583	12	2700	1000	10%	Better
	PAR30	84379	12	3000	860	10%	Better
	PAR30	84380	12	3000	900	10%	Better
	PAR30	84384	12	3000	850	10%	Better
	PAR30	84392	12	2700	900	10%	Better
	PAR30	84395	12	2700	850	10%	Better
	PAR30	84399	12	3000	900	10%	Better
	PAR30	84400	12	3000	900	10%	Better
	PAR30	84407	12	2700	850	10%	Better
	PAR30L	42136	12	3000	1050	10%	Better
	PAR30L	42137	12	3000	1050	10%	Better
	PAR30L	42144	12	3000	1000	10%	Better
	PAR38	65727	18	3000	1550	6%	Better
	PAR38	65730	18	5000	1700	6%	Better
	PAR38	65731	18	5000	1700	6%	Better
	PAR38	70962	18	2700	1300	6%	Better
	PAR38	91286	18	2700	1300	6%	Better
	PAR38	92923	18	2700	1250	6%	Better
	PAR38	92926	18	2700	1250	6%	Better
	PAR38	92927	18	2700	1350	6%	Better
	PAR38	92933	18	3000	1350	6%	Better
	PAR38	92934	18	3000	1350	6%	Better
	PAR38	92944	18	3000	1550	6%	Better
	PAR38	92950	18	2700	1550	6%	Better
	PAR38	92958	18	2700	1550	6%	Better
	PAR38	92961	18	3000	1750	6%	Better
PAR38	92963	18	3000	1550	6%	Better	
PAR38	92967	18	3000	1550	6%	Better	
PAR38	92969	12	2700	1050	6%	Better	
PAR38	92971	12	2700	1050	6%	Better	
PAR38	92972	12	3000	1050	6%	Better	
PAR38	92973	12	3000	1050	6%	Better	
PAR38	93171	18	4000	1700	6%	Better	
PAR38	93172	18	4000	1700	6%	Better	
Halco	A19	80842	7	3000	500	8%	Best
	A19	80864	10.5	3000	820	13%	Best
	BR30	80181	10	4000	750	3%	Better
	PAR20	82006	7	2700	460	27%	Better
	PAR30	82016	10	4000	820	25%	Better
	PAR30S	82029	10	4000	820	21%	Best
	PAR38	82040	15	4000	1020	4%	Best
PAR38	82050	17	4000	1220	3%	Best	
Juno	Recessed-Kit	4RLD-927-6-WWH	11.2	2700	572	23%	Better
	Recessed-Kit	6RLD-927-6-WWH	11.2	2700	619	18%	Better
Kobi	R30	LED-R30-11W700-27	11	2700	700	12%	Better
Lighting Science	A19	LSGP19W2740WEFR120	6	2700	480	7%	Better
	A19	LSP15W2740WEFR120	5	2700	300	8%	Better
	B11	LSB11CAW2740WECL12120	4.5	2700	350	12%	Better
	B11	LSB11CAW2740WECL26120	4.5	2700	350	37%	Better
	BR30	LSPro BR30 65WE W27 120 FS1 BX	10	2700	650	3%	Better
	BR30	LSPro BR30 75WE W27 120 FS1 BX	15	2700	940	2%	Better
	BR40	LSPro BR40 75WE W27 120 FS1 BX	15	2700	940	7%	Better
	BR40	LSPro BR40 90WE W27 120 FS1 BX	20	2700	1260	3%	Better
	GU10	LSPro 16 35WE W27 FL GU10 BX	6	2700	350	26%	Better
	GU10	LSPro 16 50WE W27 FL GU10 BX	8	2700	480	8%	Best
	PAR20	LS2050WEWWFL120	8	3000	525	5%	Better
	PAR20	LSPro 50WE W27 FL 120 BX	9	2700	420	17%	Best
	PAR30	LSPro 30 75WE W27 FL 120 BX	14	2700	680	6%	Better
	PAR30-Short-Neck	LS30SN75WEWWFL120	14.5	3000	950	2%	Better
	PAR38	G3TP120-16/PAR38-DIM-3000K-25°	16	3000		0%	Better
	PAR38	LED21WPAR383000K40°DIM	21	3000		15%	Better

Lighting Science	PAR38	LSPRO 38 120WE W27 NFL 120 BX	19	2700	1350	10%	Better
	PAR38	LSPRO 38 90WE W27 FL 120 BX	17	2700	840	3%	Best
	R20	LSPRO R20 50WE W27 120 FS1 BX	8	2700	525	7%	Better
Philips	A19	9290002267	8	2700	470	2%	Better
	A19	9290002268	11	2700	830	2%	Better
	A19	9290011176	6.5	2700	450	5%	Best
	A19	9290011345	9.5	2200-2700	800	4%	Best
	A19	12E26A60-1	12.5	2700	800	4%	Best
	A21	9290002290	22	2700	1780	1%	Better
	A21	9290011120	13	2700	1100	8%	Better
	A21	17E26A21D	17	2700	1100	4%	Best
	B13	9290011121	6.5	2700	520	0%	Better
	BR30	9290002197	13	2700	730	4%	Best
	BR30	9290011117	9.5	2700	730	14%	Better
	BR40	9290002199	14.5	2700	800	4%	Best
	GU10	9.29001E+11	5	2700	400	0%	Best
	PAR20	9290002333	8	2700	450	2%	Better
	PAR30L	9290002235	13	3000	750	5%	Best
	PAR38	9290002252	19.5	2700	1100	4%	Best
Satco	A19	S9037	10.5	2700	810	12%	Better
	A19	S9244	12	5000	1230	6%	Best
	A19	S9252	6.5	2700	800	7%	Better
	A19	S9561	4.5	2700	450	8%	Best
	A19	S9562	6.5	2700	810	9%	Best
	A19	S9604	5.5	5000	510	9%	Best
	A19	S9608	9	4000	830	7%	Best
	A19	S9612	10.5	2700	800	9%	Best
	A21	S92871	16	5000	1800	5%	Better
	B11-Bent-Candle	S9265	4.5	2700	450	17%	Best
	BR30	S9025	12.8	750	750	0%	Better
	BR30	S9133	10	2700	750	9%	Better
	PAR20	S9409	7	5000	525	26%	Better
	PAR30	S9424	13	5000	1000	6%	Best
	PAR38	S9454	15	5000	1200	6%	Best
	PAR38	S9456	18	4000	1400	5%	Best
	R20	S9140	7	525	525	4%	Better
	R40	S9101	16	2200-2700	1000	23%	Better
	Torpedo	S9567	2.5	2700	250	8%	Best
Vintage	S9270	2.5	2300	220	32%	Better	
Sylvania	BR30	LED12BR30/DIM/HO/827	12	2700	850	1%	Better
	PAR16	LED7PAR16/DIM/830/FL36	7	3000	350	4%	Best
	PAR30LN	LED13PAR30LN/DIM/850/NFL25/G3	13	5000	850	4%	Better
	PAR38	LED16PAR38/DIM/830/FL40/G3	16	3000	1050	3%	Better
	PAR38	LED17PAR38/DIM/840/NFL25/P3	17	4000	1300	11%	Better
	PAR38	LED17PAR38/DIM/850/NFL25/GL1	17	5000	1300	7%	Better
	Recessed-Kit	LED/1100/LD/850/RP	13	5000	1100	17%	Best
	Recessed-Kit	LED/700/LD/830/FL120	10	3000	700	5%	Better
	Recessed-Kit	LED/900/LD/830/FL120	13	3000	900	19%	Best
	Recessed-Kit	LED/900/LD/830/FL120/RP	13	3000	900	19%	Best
	Recessed-Kit	LED/RT/5/6/900/830/FL80 2/CS 1/SKU	13	3000	900	6%	Best
	Recessed-Kit	LED/RT/5/6/G/900/827/FL80/RP	13	2700	900	19%	Best
	Recessed-Kit	LED/RT/5/6/G/900/830	13	3000	900	19%	Best
	Recessed-Kit	LED/RT/5/6/HO/700/827	8	2700	700	0%	Best
	Recessed-Kit	LED/RT/5/6/HO/700/830	8	3000	700	0%	Best
	Recessed-Kit	LED/RT/5/6/HO/700/835	8	3500	700	0%	Best
	Recessed-Kit	LED/RT4/600/827/1PK	9	2700	600	7%	Better
	Recessed-Kit	LED/RT4/600/827/FL80	9	2700	600	7%	Better
	Recessed-Kit	LED/RT4/600/830/FL80	9	3000	600	7%	Better
	Recessed-Kit	LED/RT4/600/830/FL80/RP	9	3000	600	7%	Better
	Recessed-Kit	LED/RT4/600/840/FL80	9	4000	600	7%	Better
	Recessed-Kit	LED/RT4/600/850/FL80	9	5000	600	7%	Better
	Recessed-Kit	LED/RT4/G/600/827	9	2700	600	11%	Best
	Recessed-Kit	LED/RT4/G/600/830	7	3000	600	11%	Best
	Recessed-Kit	LED/RT5/6/700/840/FL80	10	4000	700	12%	Better
	Recessed-Kit	LED/RT5/6/900/827/FL80	13	2700	900	6%	Best
	Recessed-Kit	LED/RT5/6/G/900/830/FL80/RP	13	3000	900	19%	Best
	Recessed-Kit	LED/RT5/6/HO/700/840	8	4000	700	10%	Best
	Recessed-Kit	LEDRT/5/6/700/850/FL80 2/CS 1/SKU	10	5000	700	12%	Better
	Recessed-Kit	LEDRT56700827FL80 2/CS 1/SKU	10	2700	700	12%	Better
	Recessed-Kit	LEDRT56700830FL80 2/CS 1/SKU	10	3000	700	12%	Better
	Recessed-Kit	LEDRT56900830RP	13	3000	900	6%	Best

TCP	A19	ES95A1940SWD4	7	2700	450	30%	Better
	A19	ES95A1960SWD4	11	2700	800	7%	Better
	A19	L10A19DODLC2	10	2700	800	7%	Better
	A21	ES95A2175SWD2	15	2700	1100	4%	Better
	BR30	BR30004	10	2700	700	6%	Better
	BR30	ES95BR3065SWD6	9	2700	650	6%	Better
	GU10	ES95GU1050BWD3	7	3000	500	12%	Better
	P20	ES95P2050BWD2	8	3000	500	11%	Better
	P38	ES95P3890BWD2	13	3000	850	8%	Better
	R20	ES95R2050SWD3	7	2700	500	9%	Better

LED Bulb Compatibility
SureSlide 6674
IllumaTech IPL06



Manufacturer	Type	Model #	Wattage	Color (K)	Lumens	Minimum Brightness (% of full Brightness)	Performance
Buckingham	Fixed Track Light	1001573381	21	2700	1100	3	Better
	Puck (x5)	21325KIT	3.4	3000	865	0	Better
	Track Lighting (x3)	939044	17.5	2700	420	3	Better
	Track Lighting (x3)	1001279379	27	2700	1150	14	Better
	Track Lighting (x3)	1001279383	14	2700	820	8	Better
	Track Lighting (x3)	1001279386	50	2700	2600	2	Better
	Under Cabinet	57005N-WH	5.8	3000	300	2	Better
	Under Cabinet	205663883	9	3000	450	3	Better
	Under Cabinet	1001217444	15	3000	690	4	Better
	Under Cabinet	1001217457	17	3000	790	5	Better
Under Cabinet	1001217466	6	3000	280	7	Better	
Commercial Electric	Recessed-Kit	CE-JB6-650L-27K-E26	12.5	2700	670	15%	Better
Cree	A19	BA19-04527OMB-12DE26-3_1	6	2700	460	7%	Better
	A19	BA19-11027OMF-12DE26-1U100	13.5	2700	1100	12%	Better
	A21	BA21-16027OMF-12DE26-1U110	18	2700	1600	29%	Better
	BR30	BBR30-06527FLF-12DE26-4U100	9	2700	655	5%	Better
	Recessed-Kit	DRDL4-05727009-12DE26-1C100	11.5	2700	575	17%	Better
Ecosmart	A15	1001653702 ECS A15 40WE W27 120 G1	4	2700	330	25%	Better
	B11	1001654308 ECS B11 60WE W27 120	6	2700	500	14%	Better
	BR40	ECSBR4075WEW27120G1BL	13	2700	940	11%	Better
	Recessed-Kit	ECS DN6 W27 E26 120	9.5	2700	650	18%	Better
Feit-Utillitech Pro	A19	BPAGOM800/5K/LED	9.5	5000	810	11%	Better
GE	BR30	21907	10	2700	700	13%	Better
	BR30	68160	10	2700	700	13%	Better
	BR30	68161	10	3000	700	13%	Better
	BR30	89936	10	2700	700	13%	Better
	BR30	89942	10	5000	700	13%	Better
Halco	A19	80842	7	3000	500	21%	Better
	BR30	80181	10	4000	750	2%	Better
	PAR30	82016	10	4000	820	6%	Better
	PAR38	82040	15	4000	1020	3%	Better
	PAR38	82050	17	4000	1220	1%	Better
Juno	4" Recessed Kit	4RLD-927-6-WWH	11.2	2700	572	23%	Better
	6" Recessed Kit	6RLD-927-6-WWH	11.2	2700	619	23%	Better
Kobi	A19	LED-ASD-15W1100-27	15	2700	1000	4%	Better
Lighting Science	BR30	LSPro BR30 65WE W27 120 FS1 BX	10	2700	650	0%	Better
	BR30	LSPro BR30 75WE W27 120 FS1 BX	15	2700	940	1%	Better
	BR40	LSPro BR40 75WE W27 120 FS1 BX	15	2700	940	1%	Better
	GU10	LSPro 16 50WE W27 FL GU10 BX	8	2700	480	4%	Better
	PAR20	LSPro 50WE W27 FL 120 BX	9	2700	420	7%	Better
	PAR38	LSPro 38 120WE W27 NFL 120 BX	19	2700	1350	2%	Better
	PAR38	LSPro 38 90WE W27 FL 120 BX	17	2700	840	3%	Better
	R20	LSPro R20 50WE W27 120 FS1 BX	8	2700	525	4%	Better
Philips	A19	9290011176	6.5	2700	450	8%	Better
	A19	9290011345	9.5	2200-2700	800	6%	Better
	A21	9290011120	13	2700	1100	17%	Better
	BR30	9290011117	9.5	2700	730	13%	Better
	GU10	929001156504	5	2700	400	6%	Better
Satco	A19	S9244	12	5000	1230	5%	Better
	A19	S9561	4.5	2700	450	15%	Better
	A19	S9562	6.5	2700	810	15%	Better
	A19	S9604	5.5	5000	510	6%	Better
	A19	S9608	9	4000	830	5%	Better
	A19	S9612	10.5	2700	800	13%	Better
	A21	S92871	16	5000	1800	4%	Better
	BR30	S9025	12.8	750	750	4%	Better
	BR30	S9133	10	2700	750	3%	Better
	BR40	S9144	12	2700	900	29%	Better
	PAR30	S9424	13	5000	1000	6%	Better
	PAR38	S9456	18	4000	1400	6%	Better

Satco	R20	S9140	7	525	525	1%	Better
	R40	S9101	16	2200-2700	1000	4%	Better
Sylvania	PAR30LN	LED13PAR30LN/DIM/850/NFL25/G3	13	5000	850	4%	Better
	PAR38	LED16PAR38/DIM/830/FL40/G3	16	3000	1050	3%	Better
	PAR38	LED17PAR38/DIM/840/NFL25/P3	17	4000	1300	22%	Better
	PAR38	LED17PAR38/DIM/850/NFL25/GL1	17	5000	1300	9%	Better
	Recessed-Kit	LED/1100/LD/850/RP	13	5000	1100	22%	Better
	Recessed-Kit	LED/700/LD/830/FL120	10	3000	700	25%	Better
	Recessed-Kit	LED/900/LD/830/FL120	13	3000	900	19%	Better
	Recessed-Kit	LED/900/LD/830/FL120/RP	13	3000	900	19%	Better
	Recessed-Kit	LED/RT/5/6/900/830/FL80 2/CS 1/SKU	13	3000	900	18%	Better
	Recessed-Kit	LED/RT/5/6/G/900/827/FL80/RP	13	2700	900	20%	Better
	Recessed-Kit	LED/RT/5/6/G/900/830	13	3000	900	20%	Better
	Recessed-Kit	LED/RT/5/6/HO/700/827	8	2700	700	4%	Better
	Recessed-Kit	LED/RT/5/6/HO/700/830	8	3000	700	4%	Better
	Recessed-Kit	LED/RT/5/6/HO/700/835	8	3500	700	4%	Better
	Recessed-Kit	LED/RT4/600/827/1PK	9	2700	600	20%	Better
	Recessed-Kit	LED/RT4/600/827/FL80	9	2700	600	20%	Better
	Recessed-Kit	LED/RT4/600/830/FL80	9	3000	600	20%	Better
	Recessed-Kit	LED/RT4/600/830/FL80/RP	9	3000	600	20%	Better
	Recessed-Kit	LED/RT4/600/840/FL80	9	4000	600	20%	Better
	Recessed-Kit	LED/RT4/600/850/FL80	9	5000	600	20%	Better
	Recessed-Kit	LED/RT4/G/600/827	9	2700	600	23%	Better
	Recessed-Kit	LED/RT4/G/600/830	7	3000	600	23%	Better
	Recessed-Kit	LED/RT5/6/700/840/FL80	10	4000	700	21%	Better
	Recessed-Kit	LED/RT5/6/900/827/FL80	13	2700	900	18%	Better
	Recessed-Kit	LED/RT5/6/G/900/830/FL80/RP	13	3000	900	20%	Better
	Recessed-Kit	LED/RT5/6/HO/700/840	8	4000	700	4%	Better
Recessed-Kit	LEDRT/5/6/700/850/FL80 2/CS 1/SKU	10	5000	700	21%	Better	
Recessed-Kit	LEDRT56700827FL80 2/CS 1/SKU	10	2700	700	21%	Better	
Recessed-Kit	LEDRT56700830FL80 2/CS 1/SKU	10	3000	700	21%	Better	
Recessed-Kit	LEDRT56900830RP	13	3000	900	18%	Better	
TCP	A19	ES95A1940SWD4	7	2700	450	8%	Better
	A19	ES95A1960SWD4	11	2700	800	5%	Better
	A19	L10A19DODLC2	10	2700	800	4%	Better
	BR30	BR30004	10	2700	700	3%	Better
	GU10	ES95GU1050BWD3	7	3000	500	9%	Better
	P20	ES95P2050BWD2	8	3000	500	8%	Better

LED Bulb Compatibility
SureSlide 6672



Manufacturer	Type	Model #	Wattage	Color (K)	Lumens	Minimum Brightness (% of full Brightness)	Performance
Buckingham	Fixed Track Light	1001573381	21	2700	1100	21%	Better
	Puck (x5)	21325KIT	3.4	3000	865	0%	Better
	Track Lighting (x3)	939044	17.5	2700	420	2%	Better
	Track Lighting (x3)	1001279379	27	2700	1150	20%	Better
	Track Lighting (x3)	1001279383	14	2700	820	8%	Better
	Track Lighting (x3)	1001279386	50	2700	2600	5%	Better
	Under Cabinet	205663883	9	3000	450	5%	Better
	Under Cabinet	57005N-WH	5.8	3000	300	3%	Best
	Under Cabinet	1001217444	15	3000	690	12%	Better
Under Cabinet	1001217457	17	3000	790	22%	Better	
Under Cabinet	1001217466	6	3000	280	9%	Better	
Commercial Electric	Recessed-Kit	CE-JB6-650L-27K-E26	12.5	2700	670	22%	Better
Cree	A19	BA19-04527OMB-12DE26-3_1	6	2700	460	19%	Better
	A19	BA19-08027OMB-12DE26-3_1	10	2700	815	13%	Better
	A19	BA19-11027OMF-12DE26-1U100	13.5	2700	1100	25%	Better
	BR30	BBR30-06527FLF-12DE26-4U100	9	2700	655	17%	Better
	PAR30	BPAR30L-0803040C-12DE26-1C_00	10.5	3000	850	14%	Better
	PAR30	BPAR30S-0803025C-12DE26-1C_00	11	3000	850	16%	Better
PAR38	BPAR38-1503027T-12DE26-2U_00	18	3000	1500	32%	Better	
Ecosmart	A15	1001653696 ECS A15 60WE W27 120 G1	6	2700	500	2%	Better
	A15	1001653702 ECS A15 40WE W27 120 G1	4	2700	330	1%	Better
	A15	1001684222 ECS A15 60WE W27 E12 12	6	2700	500	11%	Better
	B11	1001604600 ECS B11 CA 40WE W27 LP F	4	2700	350	12%	Better
	B11	1001604604 ECS B11 CA 25WE W27 LP F	3	2700	500	18%	Better
	B11	1001654308 ECS B11 60WE W27 120	6	2700	500	13%	Better
	BR40	ECSBR4075WEW27120G1BL	13	2700	940	11%	Better
	G16.5	1001653709 ECS G16.5 60WE CW LP CL	6.5	5000	500	14%	Better
	G16.5	1001654224 ECS G16.5 60WE W27 LP CL	6.5	2700	500	16%	Better
G25	1001659342 ECS 25 40WE W27 LP FR 12	4.5	2700	500	13%	Better	
Feit-Utilitech Pro	A19	BPAGOM800/5K/LED	9.5	5000	810	17%	Better
	A19	BPAGOM800/LED	9.5	3000	800	11%	Better
GE	A19	13791	10.5	2700	800	18%	Better
	A19	14203	10.5	2700	800	18%	Better
	A19	83570	10.5	2700	800	18%	Better
	A19	89943	10.5	5000	850	18%	Better
	A19	95927	10.5	5000	850	18%	Better
Halco	A19	80842	7	3000	500	25%	Better
	A19	80864	10.5	3000	820	11%	Better
	BR30	80181	10	4000	750	4%	Better
	PAR20	82006	7	2700	460	23%	Better
	PAR30S	82029	10	4000	820	24%	Better
	PAR38	82040	15	4000	1020	27%	Better
	PAR38	82050	17	4000	1220	3%	Better
Kobi	A19	LED-ASD-15W1100-27	15	2700	1000	5%	Better
Lighting Science	BR30	LSPRO BR30 75WE W27 120 FS1 BX	15	2700	940	2%	Better
	BR40	LSPRO BR40 75WE W27 120 FS1 BX	15	2700	940	4%	Better
	BR40	LSPRO BR40 90WE W27 120 FS1 BX	20	2700	1260	0%	Better
	PAR20	LSPRO 50WE W27 FL 120 BX	9	2700	420	24%	Better
	PAR38	LSPRO 38 90WE W27 FL 120 BX	17	2700	840	9%	Better
	R20	LSPRO R20 50WE W27 120 FS1 BX	8	2700	525	13%	Better
Philips	A19	9290011176	6.5	2700	450	7%	Better
	A19	9290011345	9.5	2200-2700	800	5%	Better
	BR30	9290011117	9.5	2700	730	14%	Better
	GU10	9.29001E+11	5	2700	400	0%	Better
Satco	A19	S9244	12	5000	1230	14%	Better
	A19	S9252	6.5	2700	800	29%	Better
	A19	S9561	4.5	2700	450	15%	Better
	A19	S9562	6.5	2700	810	17%	Better

Satco	A19	S9604	5.5	5000	510	0%	Better
	A19	S9612	10.5	2700	800	13%	Better
	A21	S92871	16	5000	1800	0%	Better
	PAR30	S9424	13	5000	1000	22%	Better
	PAR38	S9454	15	5000	1200	25%	Better
	PAR38	S9456	18	4000	1400	22%	Better
	Torpedo	S9567	2.5	2700	250	32%	Better
	Vintage	S9270	2.5	2300	220	32%	Better
Sylvania	PAR30LN	LED13PAR30LN/DIM/850/NFL25/G3	13	5000	850	8%	Better
	PAR38	LED16PAR38/DIM/830/FL40/G3	16	3000	1050	15%	Better
	PAR38	LED17PAR38/DIM/840/NFL25/P3	17	4000	1300	16%	Better
	PAR38	LED17PAR38/DIM/850/NFL25/GL1	17	5000	1300	19%	Better
	Recessed-Kit	LED/1100/LD/850/RP	13	5000	1100	25%	Better
	Recessed-Kit	LED/700/LD/830/FL120	10	3000	700	33%	Better
	Recessed-Kit	LED/900/LD/830/FL120	13	3000	900	26%	Better
	Recessed-Kit	LED/900/LD/830/FL120/RP	13	3000	900	26%	Better
	Recessed-Kit	LED/RT/5/6/900/830/FL80 2/CS 1/SKU	13	3000	900	21%	Better
	Recessed-Kit	LED/RT/5/6/G/900/827/FL80/RP	13	2700	900	25%	Better
	Recessed-Kit	LED/RT/5/6/G/900/830	13	3000	900	25%	Better
	Recessed-Kit	LED/RT/5/6/HO/700/827	8	2700	700	2%	Better
	Recessed-Kit	LED/RT/5/6/HO/700/830	8	3000	700	2%	Better
	Recessed-Kit	LED/RT/5/6/HO/700/835	8	3500	700	2%	Better
	Recessed-Kit	LED/RT4/600/827/1PK	9	2700	600	25%	Better
	Recessed-Kit	LED/RT4/600/830/FL80	9	3000	600	25%	Better
	Recessed-Kit	LED/RT4/600/830/FL80/RP	9	3000	600	25%	Better
	Recessed-Kit	LED/RT4/600/840/FL80	9	4000	600	25%	Better
	Recessed-Kit	LED/RT4/600/850/FL80	9	5000	600	25%	Better
	Recessed-Kit	LED/RT4/G/600/827	9	2700	600	30%	Better
	Recessed-Kit	LED/RT4/G/600/830	7	3000	600	30%	Better
	Recessed-Kit	LED/RT5/6/700/840/FL80	10	4000	700	28%	Better
	Recessed-Kit	LED/RT5/6/900/827/FL80	13	2700	900	21%	Better
	Recessed-Kit	LED/RT5/6/G/900/830/FL80/RP	13	3000	900	25%	Better
	Recessed-Kit	LED/RT5/6/HO/700/840	8	4000	700	2%	Better
	Recessed-Kit	LEDRT/5/6/700/850/FL80 2/CS 1/SKU	10	5000	700	28%	Better
Recessed-Kit	LEDRT56700827FL80 2/CS 1/SKU	10	2700	700	28%	Better	
Recessed-Kit	LEDRT56700830FL80 2/CS 1/SKU	10	3000	700	28%	Better	
Recessed-Kit	LEDRT56900830RP	13	3000	900	21%	Better	
TCP	A19	ES95A1940SWD4	7	2700	450	1%	Better
	A19	ES95A1960SWD4	11	2700	800	0%	Better
	A19	ES95A19GU60SWD	11	2700	800	0%	Better
	A21	ES95A2175SWD2	15	2700	1100	0%	Better
	GU10	ES95GU1050BWD3	7	3000	500	0%	Better
	P30	ES95P3075BWD2	10	3000	750	0%	Better
	P38	ES95P3890BWD2	13	3000	850	0%	Better
	R20	ES95R2050SWD3	7	2700	500	0%	Better
	Recessed-Kit	LED/RT4/600/827/FL80	9	2700	600	25%	Better

LED Bulb Compatibility
Renu REL06



Manufacturer	Type	Model #	Wattage	Color (K)	Lumens	Minimum Brightness (% of full Brightness)	Performance
Buckingham	Puck (x5)	21325KIT	3.4	3000	865	2%	Better
	Track Lighting (x3)	939044	17.5	2700	420	2%	Better
	Track Lighting (x3)	1001279386	50	2700	2600	6%	Better
	Under Cabinet	57005N-WH	5.8	3000	300	4%	Better
	Under Cabinet	1001217444	15	3000	690	4%	Better
	Under Cabinet	1001217457	17	3000	790	5%	Better
Commercial Electric	Recessed-Kit	CE-JB6-650L-27K-E26	12.5	2700	670	21%	Better
Cree	A19	BA19-04527OMB-12DE26-3_1	6	2700	460	27%	Better
	A19	BA19-08027OMB-12DE26-3_1	10	2700	815	24%	Better
	A19	BA19-11027OMF-12DE26-1U100	13.5	2700	1100	32%	Better
	A21	BA21-16027OMF-12DE26-1U110	18	2700	1600	31%	Better
	BR30	BBR30-06527FLF-12DE26-4U100	9	2700	655	8%	Better
	PAR30	BPAR30L-0803040C-12DE26-1C_00	10.5	3000	850	7%	Better
	PAR30	BPAR30S-0803025C-12DE26-1C_00	11	3000	850	11%	Better
	PAR38	BPAR38-1503027T-12DE26-2U_00	18	3000	1500	29%	Better
EcoSmart	A15	1001653696 ECS A15 60WE W27 120 G1	6	2700	500	26%	Better
	A15	1001653702 ECS A15 40WE W27 120 G1	4	2700	330	31%	Better
	A15	1001684222 ECS A15 60WE W27 E12 12C	6	2700	500	19%	Better
	B11	1001604594 ECS B11 CA 25WE W27 LP E12 12C	3	2700	200	25%	Better
	B11	1001604600 ECS B11 CA 40WE W27 LP E12 12C	4	2700	350	17%	Better
	B11	1001604604 ECS B11 CA 25WE W27 LP E26 12C	3	2700	500	25%	Better
	B11	1001654308 ECS B11 60WE W27 120	6	2700	500	20%	Better
	B11	1001659350 ECS B11 60WE W27 E12 120	6	2700	500	20%	Better
	BR30	ECSBR3065WEWW120DG	9.5	3000	650	27%	Better
	BR40	ECSBR4075WEW27120G1BL	13	2700	940	18%	Better
	G16.5	1001653709 ECS G16.5 60WE CW LP CL E12 12C	6.5	5000	500	21%	Better
	G25	1001659342 ECS 25 40WE W27 LP FR 120	4.5	2700	500	20%	Better
	G25	1001696048 ECS 25 60WE W27 LP FR 120	6	2700	200	23%	Better
	G25	ECS2525WEW27120DG	3.8	2700	300	26%	Better
	G25	ECS2540WEW27120DG	5.5	2700	400	20%	Better
	Recessed-Kit	LSGLP6W27120WHS1BX	13	2700		12%	Better
	GE	A19	13791	10.5	2700	800	22%
A19		14203	10.5	2700	800	22%	Better
A19		83570	10.5	2700	800	22%	Better
A19		89943	10.5	5000	850	22%	Better
A19		95927	10.5	5000	850	22%	Better
BR30		21907	10	2700	700	25%	Better
BR30		68160	10	2700	700	25%	Better
BR30		68161	10	3000	700	25%	Better
BR30		89936	10	2700	700	25%	Better
BR30		89942	10	5000	700	25%	Better
PAR30		42131	12	3000	1050	27%	Better
PAR30		42133	12	2700	1050	27%	Better
PAR30		42134	12	2700	1000	27%	Better
PAR30		73583	12	2700	1000	27%	Better
PAR30		84379	12	3000	860	27%	Better
PAR30		84380	12	3000	900	27%	Better
PAR30		84384	12	3000	850	27%	Better
PAR30		84392	12	2700	900	27%	Better
PAR30		84395	12	2700	850	27%	Better
PAR30		84399	12	3000	900	27%	Better
PAR30		84400	12	3000	900	27%	Better
PAR30		84407	12	2700	850	27%	Better
PAR30L		42136	12	3000	1050	27%	Better
PAR30L		42137	12	3000	1050	27%	Better
PAR30L		42144	12	3000	1000	27%	Better
PAR38		65727	18	3000	1550	20%	Better
PAR38		65730	18	5000	1700	20%	Better
PAR38		65731	18	5000	1700	20%	Better
PAR38		70962	18	2700	1300	20%	Better
PAR38		91286	18	2700	1300	20%	Better
PAR38		92923	18	2700	1250	20%	Better
PAR38		92926	18	2700	1250	20%	Better
PAR38	92927	18	2700	1350	20%	Better	

GE	PAR38	92933	18	3000	1350	20%	Better
	PAR38	92934	18	3000	1350	20%	Better
	PAR38	92944	18	3000	1550	20%	Better
	PAR38	92950	18	2700	1550	20%	Better
	PAR38	92958	18	2700	1550	20%	Better
	PAR38	92961	18	3000	1750	20%	Better
	PAR38	92963	18	3000	1550	20%	Better
	PAR38	92967	18	3000	1550	20%	Better
	PAR38	92969	12	2700	1050	20%	Better
	PAR38	92971	12	2700	1050	20%	Better
	PAR38	92972	12	3000	1050	20%	Better
	PAR38	92973	12	3000	1050	20%	Better
	PAR38	93171	18	4000	1700	20%	Better
PAR38	93172	18	4000	1700	20%	Better	
Halco	A19	80842	7	3000	500	25%	Better
	A19	80864	10.5	3000	820	11%	Better
	BR30	80181	10	4000	750	4%	Better
	PAR20	82006	7	2700	460	23%	Better
	PAR30S	82029	10	4000	820	24%	Better
	PAR38	82040	15	4000	1020	27%	Better
PAR38	82050	17	4000	1220	3%	Better	
Kobi	A19	LED-ASD-15W1100-27	15	2700	1000	7%	Better
	R30	LED-R30-11W700-27	11	2700	700	21%	Better
Lighting Science	A19	LSGP19W2740WEFR120	6	2700	480	21%	Better
	A19	LSP15W2740WEFR120	5	2700	300	24%	Better
	B11	LSB11CAW2740WECLE12120	4.5	2700	350	27%	Better
	B11	LSB11CAW2740WECLE26120	4.5	2700	350	38%	Better
	G25	DFN2560WEW27120	8.5	2700	650	13%	Better
	MR16	LSPro 16 35WE W27 FL BX	6	2700	300	33%	Better
	MR16	LSPro 16 50WE W27 FL BX	8	2700	450	46%	Better
	PAR20	LSPro 50WE W27 FL 120 BX	9	2700	420	20%	Better
PAR30	LS3075WEWWGBFL120	10.5	3000	750	14%	Better	
Philips	A19	9290011176	6.5	2700	450	13%	Better
	A19	9290011345	9.5	2200-2700	800	8%	Better
	A19 Edison	12E26A60-1	12.5	2700	800	9%	Better
	A21 Edison	17E26A21D	17	2700	1100	8%	Better
	BR30	9290011117	9.5	2700	730	9%	Better
	BR30 Edison	9290002197	13	2700	730	10%	Better
	BR40 Edison	9290002199	14.5	2700	800	10%	Best
	GU10	929001156504	5	2700	400	6%	Better
	PAR20 Edison	9290002333	8	2700	450	2%	Better
	PAR30L Edison	9290002235	13	3000	750	15%	Best
PAR38 Edison	9290002252	19.5	2700	1100	9%	Better	
Satco	A19	S9107	7	2700	450	23%	Better
	A19	S9244	12	5000	1230	20%	Better
	A19	S9561	4.5	2700	450	21%	Better
	A19	S9562	6.5	2700	810	33%	Better
	A19	S9604	5.5	5000	510	29%	Better
	A19	S9608	9	4000	830	25%	Better
	A19	S9612	10.5	2700	800	17%	Better
	B11-Bent-Candle	S9265	4.5	2700	450	22%	Better
	BR30	S9025	12.8	750	750	11%	Better
	BR30	S9133	10	2700	750	3%	Better
	BR40	S9144	12	2700	900	20%	Better
	PAR30	S9424	13	5000	1000	22%	Better
	PAR38	S9454	15	5000	1200	22%	Better
	R20	S9073	7.8	2200-2700	460	12%	Better
	R20	S9140	7	525	525	16%	Better
	R40	S9101	16	2200-2700	1000	11%	Better
Torpedo	S9567	2.5	2700	250	21%	Better	
Vintage	S9270	2.5	2300	220	20%	Better	
Sylvania	PAR30LN	LED13PAR30LN/DIM/850/NFL25/G3	13	5000	850	20%	Better
	PAR38	LED16PAR38/DIM/830/FL40/G3	16	3000	1050	11%	Better
	PAR38	LED17PAR38/DIM/840/NFL25/P3	17	4000	1300	22%	Better
	PAR38	LED17PAR38/DIM/850/NFL25/GL1	17	5000	1300	12%	Better
	Recessed-Kit	LED/1100/LD/850/RP	13	5000	1100	14%	Better
	Recessed-Kit	LED/900/LD/830/FL120	13	3000	900	15%	Better
	Recessed-Kit	LED/900/LD/830/FL120/RP	13	3000	900	15%	Better
	Recessed-Kit	LED/RT/5/6/900/830/FL80 2/CS 1/SKU	13	3000	900	14%	Better
	Recessed-Kit	LED/RT/5/6/G/900/827/FL80/RP	13	2700	900	14%	Better
	Recessed-Kit	LED/RT/5/6/G/900/830	13	3000	900	14%	Better
	Recessed-Kit	LED/RT/5/6/HO/700/827	8	2700	700	8%	Better
	Recessed-Kit	LED/RT/5/6/HO/700/830	8	3000	700	8%	Better
Recessed-Kit	LED/RT/5/6/HO/700/835	8	3500	700	8%	Better	

Sylvania	Recessed-Kit	LED/RT4/600/827/1PK	9	2700	600	16%	Better
	Recessed-Kit	LED/RT4/600/827/FL80	9	2700	600	16%	Better
	Recessed-Kit	LED/RT4/600/830/FL80	9	3000	600	16%	Better
	Recessed-Kit	LED/RT4/600/830/FL80/RP	9	3000	600	16%	Better
	Recessed-Kit	LED/RT4/600/840/FL80	9	4000	600	16%	Better
	Recessed-Kit	LED/RT4/600/850/FL80	9	5000	600	16%	Better
	Recessed-Kit	LED/RT5/6/900/827/FL80	13	2700	900	14%	Better
	Recessed-Kit	LED/RT5/6/G/900/830/FL80/RP	13	3000	900	14%	Better
	Recessed-Kit	LED/RT5/6/HO/700/840	8	4000	700	8%	Better
Recessed-Kit	LEDRT56900830RP	13	3000	900	14%	Better	
TCP	A19	ES95A1940SWD4	7	2700	450	23%	Better
	A19	ES95A1960SWD4	11	2700	800	22%	Better
	A19	ES95A19GU60SWD	11	2700	800	20%	Better
	A21	ES95A2175SWD2	15	2700	1100	18%	Better
	BR30	ES95BR3065SWD6	9	2700	650	19%	Better
	P30	ES95P3075BWD2	10	3000	750	18%	Better
	P38	ES95P3890BWD2	13	3000	850	23%	Better

LED Bulb Compatibility
Vizia RF + VRMX1



Manufacturer	Type	Model #	Wattage	Color (K)	Lumens	Minimum Brightness (% of full Brightness)	Performance
EcoSmart	BR30	ECSBR3065WEWW120DG	9.5	3000	650	8%	Better
	Edison Recessed Kit	LSGLP6W27120WHS1BX	13	2700	-	15%	Better
	G25	ECS2525WEW27120DG	3.8	2700	300	15%	Better
	G26	ECS2540WEW27120DG	5.5	2700	400	7%	Better
Lighting Science	A19	LSGP19W2740WEFR120	6	2700	480	26%	Better
	A19	LSP15W2740WEFR120	5	2700	300	31%	Better
	G25	DFN2560WEW27120	8.5	2700	650	6%	Better
	PAR30	LS3075WEWWFL120	14	3000	900	7%	Better
	PAR30	LS3075WEWWGBFL120	10.5	3000	750	23%	Better
	PAR30 Short Neck	LS30SN75WEWWFL120	14.5	3000	950	5%	Better
	PAR38	G3TP120-16/PAR38-DIM-3000K-25°	16	3000	-	10%	Better
Philips	A19 Edison	9290002268	11	2700	830	2%	Better
	A19 Edison	12E26A60-1	12.5	2700	800	4%	Better
	A21 Edison	9290002290	22	2700	1780	1%	Better
	A21 Edison	17E26A21D	17	2700	1100	4%	Better
	BR30 Edison	9290002197	13	2700	730	4%	Better
	BR40 Edison	9290002199	14.5	2700	800	5%	Better
	PAR20 Edison	9290002333	8	2700	450	2%	Better
	PAR30L Edison	9290002235	13	3000	750	6%	Better
	PAR38 Edison	9290002252	19.5	2700	1100	5%	Better
Satco	A19	S9037	10.5	2700	810	4%	Better
	A19	S9107	7	2700	450	11%	Better
	BR30	S9025	12.8	750	750	4%	Better
	BR30	S9133	10	2700	750	3%	Better
	BR40	S9144	12	2700	900	11%	Better
	R20	S9073	7.8	2200-2700	460	5%	Better
	R20	S9140	7	525	525	5%	Better
	R40	S9101	16	2200-2700	1000	4%	Better

LED Bulb Compatibility
Dimming Sensor IPSD6/IPVD6



Manufacturer	Type	Model #	Wattage	Color (K)	Lumens	Minimum Brightness (% of full Brightness)	Performance
Ecosmart	BR40	ECSBR4075WEW27120G1BL	13	2700	940	11%	Better
Halco	A19	80842	7	3000	500	25%	Better
	A19	80864	10.5	3000	820	11%	Better
	BR30	80181	10	4000	750	4%	Better
	PAR20	82006	7	2700	460	23%	Better
	PAR30S	82029	10	4000	820	24%	Better
	PAR38	82040	15	4000	1020	27%	Better
	PAR38	82050	17	4000	1220	3%	Better
Satco	A19	S9612	10.5	2700	800	11%	Better
Sylvania	Recessed-Kit	LED/700/LD/830/FL120	10	3000	700	21%	Better
	Recessed-Kit	LED/RT/5/6/900/830/FL80 2/CS 1/SKU	13	3000	900	17%	Better
	Recessed-Kit	LED/RT/5/6/G/900/827/FL80/RP	13	2700	900	18%	Better
	Recessed-Kit	LED/RT/5/6/G/900/830	13	3000	900	18%	Better
	Recessed-Kit	LED/RT/5/6/HO/700/827	8	2700	700	1%	Better
	Recessed-Kit	LED/RT/5/6/HO/700/830	8	3000	700	1%	Better
	Recessed-Kit	LED/RT/5/6/HO/700/835	8	3500	700	1%	Better
	Recessed-Kit	LED/RT4/G/600/827	9	2700	600	20%	Better
	Recessed-Kit	LED/RT4/G/600/830	7	3000	600	20%	Better
	Recessed-Kit	LED/RT5/6/700/840/FL80	10	4000	700	19%	Better
	Recessed-Kit	LED/RT5/6/900/827/FL80	13	2700	900	17%	Better
	Recessed-Kit	LED/RT5/6/G/900/830/FL80/RP	13	3000	900	18%	Better
	Recessed-Kit	LED/RT5/6/HO/700/840	8	4000	700	1%	Better
	Recessed-Kit	LEDRT/5/6/700/850/FL80 2/CS 1/SKU	10	5000	700	19%	Better
	Recessed-Kit	LEDRT56700827FL80 2/CS 1/SKU	10	2700	700	19%	Better
	Recessed-Kit	LEDRT56700830FL80 2/CS 1/SKU	10	3000	700	19%	Better
	Recessed-Kit	LEDRT56900830RP	13	3000	900	17%	Better