

4

3


2

1


B

Line Phase Terminal


Line Neutral Terminal



Green Ground Screw



.32in [8.1mm]



B

A

**NOTES:**

- 20A-125V RECEPTACLE (NEMA 5-20R)
- CLASS 2, 5V 5.4A (1 USB TYPE A 2.0 AND 1 USB TYPE C 2.0)
- DIMENSIONS GIVEN IN INCHES (Millimeters).

DEVICE VOLUME	MEASUREMENT (IN <sup>3</sup> )
IN BOX (FROM STRAP, BACK)	6.31
TOTAL	7.39

STATUS: In Work

REV.	DATE	ECO NUMBER	CHGD	APVD
1	-	-	-	-
-	-	-	-	-
-	-	-	-	-
-	-	-	-	-

**LEVITON.**

The information in this document is the exclusive **PROPRIETARY** property of **LEVITON MFG. CO., INC.** It is disclosed with the understanding that acceptance or review by the recipient constitutes an undertaking by the recipient: (1) to hold this information in strict confidence. (2) not to disclose, duplicate, copy, or use the information, in whole or in part, for any purpose other than that for which disclosed.

Copyright 2013. Unpublished. All Rights Reserved.

UNLESS OTHERWISE SPECIFIED: DO NOT SCALE DRAWING. ALL DIMENSIONS ARE IN INCHES. ALL ANGLES ARE IN DEGREES.

TOLERANCES	
INCH	METRIC
.XX ± .01	.X ± .2 mm
.XXX ± .005	.XX ± .1 mm

ANGLES: ± 1/2°

THIRD ANGLE PROJECTION

**ALL PRINTED COPIES ARE UNCONTROLLED**

TITLE: -

**CATSTD-T5833-XXX**

DWN BY	RJ	10/10/2016	ENGRG	-	-
CHK BY	-	-	MFG	-	-

DWG NO. **CATSTD-T5833-XXX-D01**

SIZE	PROJECT NO. PROJ-03192	REV
<b>B</b>	SCALE:3:2	1
	SHEET 1 OF 1	

4

3

2

1

A

A