


Commercial & Industrial Straight Blade Receptacles

Specification and
Hospital Grades



Straight Blade Receptacles Overview

CODE COMPLIANT SOLUTIONS

TAMPER-RESISTANT RECEPTACLES

Safety shutters prevent unintended contact with live parts as specified by the National Electrical Code®.



ISOLATED GROUND RECEPTACLES

Provides a more reliable, noise-free equipment ground path to sensitive electrical equipment.



POWER INDICATION RECEPTACLES

Provides visual indication of power present at the receptacle; ideal for emergency circuit applications.



WEATHER-RESISTANT RECEPTACLES

Designed for wet or damp locations, these receptacles provide added protection against corrosion, UV degradation, and cold impact damage.




SURGE PROTECTIVE RECEPTACLES

Provides point-of-use surge protection for sensitive electronic devices, such as monitors, projectors, computers, etc.



MARKED "CONTROLLED" RECEPTACLES

The National Electrical Code requires all 15 A and 20 A, 125 V receptacles that are automatically controlled to be marked with a specific symbol  and the word "CONTROLLED" on the receptacle.



HOSPITAL GRADE RECEPTACLES

In addition to UL Listing requirements for general use receptacles, hospital grade receptacles incorporate additional construction features and are subjected to more stringent performance requirements.



SMARTLOCKPRO® GFCI RECEPTACLES

By cutting off power if a ground-fault is detected, these receptacles are engineered to help protect people from the hazards of electric shock and electrocution.



SMARTLOCKPRO® AFCI RECEPTACLES

By detecting hazardous arc-faults and responding by interrupting power, these receptacles help reduce the likelihood of electrical fires.



Leviton uses several Nationally Recognized Testing Labs (NRTLs) for certification of receptacles. UL and CSA are two of these NRTLs. When you see the UL and CSA symbols, you can have the confidence that the devices adhere to strict scientific safety, quality or security standards.



In addition to complying with UL general use requirements, when you see the FULS marking you are assured that the receptacle has been investigated for compliance with US Federal Specification W-C-596 for the purpose of more durability and service life.

Commercial & Industrial Straight Blade Receptacles

Specification and Hospital Grades



TABLE OF CONTENTS

- Overview2
- Standard Receptacles6
- Time Savings 16
 - Lev-lok® Modular Wiring Devices: Receptacles 16
 - Receptacles with Pre-Wired Leads 28
- Protection 30
 - SmartlockPro® AFCI Receptacles 30
 - SmartlockPro® GFCI Receptacles 30
 - SmartlockPro® Dual Function AFCI/GFCI Receptacles. 34
 - Surge Protective Receptacles 35
- Plug Load Control 37
 - Marked "Controlled" Receptacles 37
- Specialty 40
 - 4-in-1™ Receptacles 40
 - USB Receptacles..... 41
 - Clock Hanger & Display Receptacles 42
 - Short Strap Receptacles..... 43
 - Europlug/Universal Receptacles..... 43

Choose from among the broadest offering of safe and reliable receptacle outlets in the industry, with devices to suit your every need or function.

SYMBOLS TO SIMPLIFY BROWSING

Tamper-Resistant

Isolated Ground

Power Indication

Weather-Resistant

Corrosion-Resistant

Audible Alarm

Single Receptacle

Plug Load Control

Fast-Charging USB

A receptacle for every application

HOSPITAL GRADE

UL construction and performance requirements for Hospital Grade receptacles are more stringent than those for specification grade devices. Leviton Hospital Grade receptacles meet or exceed these requirements. These receptacles are Fed Spec W-C-596 rated.*



Extra Heavy-Duty

Heavy-Duty

INDUSTRIAL SPECIFICATION GRADE

For demanding applications requiring robust construction and exceptional electrical performance, Leviton industrial specification grade receptacles are the ideal solution. These receptacles are Fed Spec W-C-596 rated.*



Extra Heavy-Duty

Heavy-Duty

* See website for product specifications.

leviton.com/receptaclegrades

COMMERCIAL SPECIFICATION GRADE

Leviton commercial specification grade receptacles strike the perfect balance between performance and value. These heavy-duty receptacles are the most widely specified for commercial building projects.



HOSPITAL GRADE Extra Heavy-Duty

- Single-piece wraparound nickel-plated brass strap
- Integral ground contacts
- Extra heavy-duty high-performance brass electrical contacts



HOSPITAL GRADE & INDUSTRIAL SPECIFICATION GRADE Heavy-Duty

- Single-piece heavy-duty wraparound galvanized steel strap
- Brass ground contacts
- Heavy-duty copper alloy electrical contacts



COMMERCIAL SPECIFICATION GRADE

- Single-piece wraparound galvanized steel strap
- Brass ground contacts
- Heavy-duty copper alloy electrical contacts



Standard Receptacles



HOSPITAL GRADE

Extra Heavy-Duty



2-Pole, 3-Wire • 125 Volt

Color

15 Amp

20 Amp

STANDARD	<ul style="list-style-type: none"> Duplex Receptacle Smooth Face Back and Side Wire 	White	8200-W	8300-W
		Ivory	8200-I	8300-I
		Lt Almond	8200-T	8300-T
		Brown	8200	8300
		Gray	8200-GY	8300-GY
		Black	—	8300-E
		Red	8200-R	8300-R
		Blue	8200-BU	8300-BU
	<ul style="list-style-type: none"> Duplex Receptacle Smooth Face Tamper-Resistant Back and Side Wire 	White	8200-SGW	8300-SGW
		Ivory	8200-SGI	8300-SGI
		Lt Almond	—	8300-SGT
		Brown	8200-SG	8300-SG
		Gray	8200-SGG	8300-SGG
		Red	8200-SGR	8300-SGR
	<ul style="list-style-type: none"> Duplex Receptacle Smooth Face Power Indication LED Back and Side Wire 	White	8200-PLW	8300-PLW
		Ivory	8200-PLI	8300-PLI
		Brown	—	8300-PL
		Gray	—	8300-PLG
		Red	8200-PLR	8300-PLR
	<ul style="list-style-type: none"> Duplex Receptacle Smooth Face MRI Back and Side Wire 	White	MRI82-W	MRI83-W
		Ivory	MRI82-I	MRI83-I
Lt Almond		MRI82-T	MRI83-T	
Gray		MRI82-GY	MRI83-GY	
Red		MRI82-R	MRI83-R	
DECORA PLUS™	<ul style="list-style-type: none"> Duplex Receptacle Smooth Face Back and Side Wire 	White	16262-HGW*	16362-HGW*
		Ivory	16262-HGI*	16362-HGI*
		Lt Almond	—	16362-HGT*
		Gray	16262-HGG*	16362-HGG*
		Red	16262-HGR*	16362-HGR*
	<ul style="list-style-type: none"> Duplex Receptacle Smooth Face Power Indication LED Back and Side Wire 	White	16262-PLW*	16362-PLW*
		Ivory	16262-PLI*	16362-PLI*
		Red	16262-PLR*	16362-PLR*
	<ul style="list-style-type: none"> Duplex Receptacle Smooth Face Tamper-Resistant Back and Side Wire 	White	16262-SGW*	16362-SGW*
		Ivory	16262-SGI*	16362-SGI*
		Lt Almond	16262-SGT*	16362-SGT*
		Brown	16262-SG*	—
		Gray	—	16362-SGG*
		Red	16262-SGR*	16362-SGR*



8300-PLW








8200-SGG



16262-SGR

* Not Fed Spec rated

HOSPITAL GRADE Extra Heavy-Duty		NEMA 6-15R 	NEMA 6-20R 	250 V
2-Pole, 3-Wire • 250 Volt		15 Amp	20 Amp	
STANDARD	• Duplex Receptacle	White	—	8400-W
	• Smooth Face	Ivory	8600-I	8400-I
	• Back and Side Wire	Brown	8600	8400
		Gray	—	8400-GY
		Red	—	8400-R
HOSPITAL GRADE Heavy-Duty		NEMA 5-15R 	NEMA 5-20R 	
2-Pole, 3-Wire • 125 Volt		15 Amp	20 Amp	
STANDARD	• Single Receptacle	White	8210-W	8310-W
	• Smooth Face	Ivory	8210-I	8310-I
	• Back and Side Wire	Brown	8210	8310
		Gray	—	8310-GY
		Red	8210-R	8310-R
	• Duplex Receptacle	White	8200-HW	8300-HW
	• Smooth Face	Ivory	8200-HI	8300-HI
	• Back and Side Wire	Lt Almond	8200-HT	8300-HT
		Brown	8200-H	8300-H
		Gray	8200-HGY	8300-HGY
		Red	8200-HR	8300-HR
	Yellow	8200-HY	—	
	Blue	8200-HBU	8300-HBU	
• Duplex Receptacle	White	C8200-W	C8300-W	
• Indented Face	Ivory	C8200-I	C8300-I	
• Back and Side Wire	Lt Almond	C8200-T	C8300-T	
	Brown	C8200	C8300	
	Gray	C8200-GY	C8300-GY	
	Black	C8200-E	C8300-E	
	Red	C8200-R	C8300-R	
	Blue	C8200-BU	C8300-BU	
• Duplex Receptacle	White	T8200-W	T8300-W	
• Smooth Face	Ivory	T8200-I	T8300-I	
• Tamper-Resistant	Lt Almond	T8200-T	T8300-T	
• Back and Side Wire	Brown	T8200	T8300	
	Gray	T8200-GY	T8300-GY	
	Black	T8200-E	T8300-E	
	Red	T8200-R	T8300-R	
	Blue	T8200-BU	T8300-BU	
• Single Receptacle	Orange	8210-IG	8310-OIG	
• Smooth Face				
• Isolated Ground				
• Back and Side Wire				



8400-I



C8200-W



T8200-I

Standard Receptacles



HOSPITAL GRADE

Heavy-Duty



2-Pole, 3-Wire • 125 Volt

Color

15 Amp

20 Amp

STANDARD

- Duplex Receptacle
- Smooth Face
- Isolated Ground
- Back and Side Wire



White	8200-IGW	8300-IGW
Ivory	8200-IGI	8300-IGI
Brown	8200-IGB	8300-IGB
Gray	8200-IGG	8300-IGG
Red	8200-IGR	8300-IGR
Orange	8200-IG	8300-OIG

- Duplex Receptacle
- Smooth Face
- Isolated Ground
- Back and Side Wire
- Pre-wired Ground Lead



Orange	8200-LIG	8300-LIG
--------	----------	----------

- Duplex Receptacle
- Smooth Face
- Illuminated Blade Slot
- Back and Side Wire



White	8200-HLW	8300-HLW
Ivory	8200-HLI	8300-HLI
Gray	—	8300-HLG
Red	8200-HLR	8300-HLR

- Duplex Receptacle
- Smooth Face
- Isolated Ground
- Tamper-Resistant
- Back and Side Wire



White	T8200-IGW	T8300-IGW
Ivory	T8200-IGI	T8300-IGI
Gray	T8200-IGG	T8300-IGG
Red	T8200-IGR	T8300-IGR
Orange	T8200-IG	T8300-IG
Blue	T8200-IGB	T8300-IGB

DECORA PLUS™

- Duplex Receptacle
- Smooth Face
- Isolated Ground
- Back and Side Wire



White	D8200-IGW	D8300-IGW
Ivory	D8200-IGI	D8300-IGI
Lt Almond	D8200-IGT	D8300-IGT
Brown	D8200-IGB	D8300-IGB
Gray	D8200-IGG	D8300-IGG
Black	D8200-IGE	D8300-IGE
Red	D8200-IGR	D8300-IGR
Orange	D8200-IG	D8300-IG

- Duplex Receptacle
- Smooth Face
- Isolated Ground
- Tamper-Resistant
- Back and Side Wire



White	DT820-IGW	DT830-IGW
Ivory	DT820-IGI	DT830-IGI
Brown	DT820-IGB	DT830-IGB
Gray	DT820-IGG	DT830-IGG
Red	DT820-IGR	DT830-IGR
Orange	DT820-IG	DT830-IG



T8300-IGW



D8300-IGR



5362-W

INDUSTRIAL SPECIFICATION GRADE

Extra Heavy-Duty



2-Pole, 3-Wire • 125 Volt

Color

15 Amp

20 Amp

STANDARD

- Duplex Receptacle
- Smooth Face
- Back and Side Wire

White	5262-W	5362-W
Ivory	5262-I	5362-I
Brown	5262	5362
Gray	5262-GY	5362-GY
Black	5262-E	5362-E
Red	5262-R	5362-R
Blue	—	5362-BU

INDUSTRIAL SPECIFICATION GRADE
Extra Heavy-Duty



2-Pole, 3-Wire • 125 Volt		Color	15 Amp	20 Amp
STANDARD	<ul style="list-style-type: none"> • Duplex Receptacle • Smooth Face • Tamper-Resistant • Back and Side Wire 	White	5262-SGW	5362-SGW
		Ivory	5262-SGI	5362-SGI
		Lt Almond	5262-SGT	5362-SGT
		Brown	5262-SG	5362-SG
		Gray	5262-SGG	5362-SGG
		Black	5262-SGE	5362-SGE
		Red	5262-SGR	5362-SGR
		Blue	5262-SGB	5362-SGB
		Yellow	52CM-62	53CM-62
		<ul style="list-style-type: none"> • Duplex Receptacle • Corrosion-Resistant • Smooth Face • Back and Side Wire 		



5362-SGW

INDUSTRIAL SPECIFICATION GRADE
Heavy-Duty



2-Pole, 3-Wire • 125 Volt		Color	15 Amp	20 Amp
STANDARD	<ul style="list-style-type: none"> • Single Receptacle • Smooth Face • Side Wire Only 	Ivory	5251-I	5351-I
		Brown	5251	5351
		White	5261-W	5361-W
		Ivory	5261-I	5361-I
		Lt Almond	—	5361-T
		Brown	5261	5361
		Gray	5261-GY	5361-GY
		Black	5261-E	5361-E
		Red	5261-R	5361-R
		<ul style="list-style-type: none"> • Duplex Receptacle • Smooth Face • Side Wire Only 	White	5242-W
Ivory	5242-I		5342-I	
Brown	5242		5342	
Gray	5242-GY		5342-GY	
Black	—		5342-E	
Red	5242-R		5342-R	
White	5252-W		5352-W	
Ivory	5252-I		5352-I	
Lt Almond	5252-T		5352-T	
Brown	5252		5352	
<ul style="list-style-type: none"> • Duplex Receptacle • Smooth Face • Back and Side Wire 	Gray	5252-GY	5352-GY	
	Black	5252-E	5352-E	
	Red	5252-R	5352-R	
	Blue	5252-BU	5352-BU	
	White	5262-SW	5362-SW	
	Ivory	5262-SI	5362-SI	
	Lt Almond	5262-ST	5362-ST	
	Brown	5262-S	5362-S	
	Gray	5262-GYS	5362-GYS	
	Black	5262-SE	5362-SE	
Red	5262-SR	5362-SR		
Orange	—	5362-SO		
Blue	5262-SBU	5362-SBU		



5352-GY



5361-W

Standard Receptacles



INDUSTRIAL SPECIFICATION GRADE Heavy-Duty



2-Pole, 3-Wire • 125 Volt

Color

15 Amp

20 Amp

- Duplex Receptacle
- Indented Face
- Back and Side Wire

White	C5262-W	C5362-W
Ivory	C5262-I	C5362-I
Lt Almond	C5262-T	C5362-T
Brown	C5262	C5362
Gray	C5262-GY	C5362-GY
Black	C5262-E	C5362-E
Red	C5262-R	C5362-R
Blue	C5262-BU	C5362-BU

- Duplex Receptacle
- Indented Face
- Back and Side Wire
- Single Piece Ground Shunt

White	L5262-W	L5362-W
Ivory	L5262-I	L5362-I
Lt Almond	L5262-T	L5362-T
Brown	L5262	L5362
Gray	L5262-GY	L5362-GY
Black	L5262-E	L5362-E
Red	L5262-R	L5362-R
Blue	L5262-BU	L5362-BU

- Duplex Receptacle
- Smooth Face
- Tamper-Resistant
- Back and Side Wire



White	T5262-W	T5362-W
Ivory	T5262-I	T5362-I
Lt Almond	T5262-T	T5362-T
Brown	T5262	T5362
Gray	T5262-GY	T5362-GY
Black	T5262-E	T5362-E
Red	T5262-R	T5362-R
Blue	T5262-BU	T5362-BU

STANDARD

- Single Receptacle
- Smooth Face
- Corrosion-Resistant
- Back and Side Wire



Yellow	5261-CR	5361-CR
--------	---------	---------

- Single Receptacle
- Smooth Face
- Isolated Ground
- Back and Side Wire



Orange	5261-IG	5361-IG
--------	---------	---------

- Duplex Receptacle
- Smooth Face
- Isolated Ground
- Back and Side Wire



White	5262-IGW	5362-IGW
Ivory	5262-IGI	5362-IGI
Lt Almond	—	5362-IGT
Brown	5262-IGB	5362-IGB
Gray	5262-IGG	5362-IGG
Black	5262-IGE	5362-IGE
Red	5262-IGR	5362-IGR
Orange	5262-IG	5362-IG
Blue	—	5362-BIG

- Single Receptacle
- Smooth Face
- Weather-Resistant
- Back and Side Wire



White	W5261-W	W5361-W
Ivory	W5261-I	W5361-I
Lt Almond	W5261-T	W5361-T
Brown	W5261	W5361
Gray	W5261-GY	W5361-GY
Black	W5261-E	W5361-E
Red	W5261-R	W5361-R
Yellow	W5261-Y	W5361-Y



C5362-W



L5362-I



5361-CR

INDUSTRIAL SPECIFICATION GRADE
Heavy-Duty



2-Pole, 3-Wire • 125 Volt		Color	15 Amp	20 Amp	
STANDARD	<ul style="list-style-type: none"> • Duplex Receptacle • Indented Face • Weather-Resistant • Back and Side Wire 	White	WBR15-W	WBR20-W	
		Ivory	—	WBR20-I	
		Gray	—	WBR20-GY	
		Black	—	WBR20-E	
		Red	—	WBR20-R	
		Yellow	WBR15-Y	WBR20-Y	
		Blue	—	WBR20-BU	
		<ul style="list-style-type: none"> • Duplex Receptacle • Smooth Face • Isolated Ground • Tamper-Resistant • Back and Side Wire 	White	T5262-IGW	T5362-IGW
			Ivory	T5262-IGI	T5362-IGI
	Gray		T5262-IGG	T5362-IGG	
	Red		T5262-IGR	T5362-IGR	
	Orange		T5262-IG	T5362-IG	
	Blue		T5262-IGB	T5362-IGB	
	<ul style="list-style-type: none"> • Duplex Receptacle • Smooth Face • Weather-Resistant • Tamper-Resistant • Back and Side Wire 	White	TWR15-W	TWR20-W	
		Ivory	—	TWR20-I	
Gray		TWR15-GY	TWR20-GY		
Yellow		—	TWR20-Y		
<ul style="list-style-type: none"> • Duplex Receptacle • Smooth Face • Back and Side Wire 		White	16262-W*	16362-W*	
		Ivory	16262-I*	16362-I*	
		Brown	16262*	16362*	
		Gray	16262-GY*	16362-GY*	
		Black	16262-E*	16362-E*	
<ul style="list-style-type: none"> • Duplex Receptacle • Smooth Face • Side Wire Only 	White	16242-W	16342-W		
	Ivory	16242-I	16342-I		
	Lt Almond	—	16342-T		
	Brown	16242	16342		
	Gray	—	16342-GY		
	Black	16242-E	16342-E		
	<ul style="list-style-type: none"> • Duplex Receptacle • Smooth Face • Back and Side Wire 	White	16252-W	16352-W	
		Ivory	16252-I	16352-I	
		Lt Almond	16252-T	16352-T	
		Brown	16252	16352	
Gray		16252-GY	16352-GY		
Black		16252-E	16352-E		
Red		16252-R	16352-R		
<ul style="list-style-type: none"> • Single Receptacle • Smooth Face • Tamper-Resistant • Back and Side Wire 	White	—	16351-SGW		

* Not Fed Spec rated



Standard Receptacles

INDUSTRIAL SPECIFICATION GRADE Heavy-Duty



2-Pole, 3-Wire • 125 Volt		Color	15 Amp	20 Amp	
<ul style="list-style-type: none"> Duplex Receptacle Smooth Face Tamper-Resistant Back and Side Wire 		White	TDR15-W	TDR20-W	
		Ivory	TDR15-I	TDR20-I	
		Lt Almond	TDR15-T	TDR20-T	
		Brown	TDR15	TDR20	
		Gray	TDR15-GY	TDR20-GY	
		Black	TDR15-E	TDR20-E	
		Red	TDR15-R	—	
		Blue	TDR15-BU	—	
	<ul style="list-style-type: none"> Duplex Receptacle Smooth Face Isolated Ground Back and Side Wire 		White	16262-WIG	16362-WIG
			Ivory	16262-IIG	16362-IIG
		Lt Almond	16262-TIG	16362-TIG	
		Gray	16262-GIG	16362-GIG	
		Black	16262-EIG	16362-EIG	
		Red	16262-RIG	16362-RIG	
		Orange	16262-OIG	16362-OIG	
		Blue	16262-BIG	16362-BIG	
<ul style="list-style-type: none"> Duplex Receptacle Smooth Face Weather-Resistant Back and Side Wire 			White	WDR15-W	WDR20-W
			Ivory	WDR15-I	WDR20-I
		Brown	WDR15	WDR20	
		Gray	WDR15-GY	WDR20-GY	
		Black	WDR15-E	WDR20-E	
<ul style="list-style-type: none"> Duplex Receptacle Smooth Face Tamper-Resistant Weather-Resistant Back and Side Wire 		White	WTD15-W	WTD20-W	
		Gray	WTD15-GY	WTD20-GY	
		Black	WTD15-E	WTD20-E	
		Blue	WTD15-BU	WTD20-BU	
<ul style="list-style-type: none"> Duplex Receptacle Smooth Face Isolated Ground Tamper-Resistant Back and Side Wire 		White	T1626-IGW	T1636-IGW	
		Ivory	T1626-IGI	T1636-IGI	
		Gray	T1626-IGG	T1636-IGG	
		Red	T1626-IGR	T1636-IGR	
		Orange	T1626-IG	T1636-IG	
		Blue	T1626-IGB	T1636-IGB	

DECORA PLUS™



INDUSTRIAL SPECIFICATION GRADE Heavy-Duty



2-Pole, 3-Wire • 125 and 250 Volt		Color	15 Amp	COMBO
STD.	<ul style="list-style-type: none"> Duplex Receptacle Smooth Face Side Wire Only 	Ivory	5292-I	
		Brown	5292	



INDUSTRIAL SPECIFICATION GRADE Heavy-Duty



2-Pole, 3-Wire • 250 Volt		Color	15 Amp	20 Amp	250 V
STD.	<ul style="list-style-type: none"> Single Receptacle Smooth Face Side Wire Only 	White	5651-W	—	
		Ivory	5651-I	—	
		Brown	5651	—	

INDUSTRIAL SPECIFICATION GRADE Heavy-Duty		NEMA 6-15R 	NEMA 6-20R 	250 V
2-Pole, 3-Wire • 250 Volt		15 Amp	20 Amp	
<ul style="list-style-type: none"> • Single Receptacle • Smooth Face • Back and Side Wire 		White	5661-W	5461-W
		Ivory	5661-I	5461-I
		Lt Almond	—	5461-T
		Brown	5661	5461
		Gray	—	5461-GY
		Black	5661-E	—
		Red	—	5461-R
		White	—	5462-W
		Ivory	5662-I	5462-I
		Brown	5662	5462
Gray	—	5462-GY		
<ul style="list-style-type: none"> • Single Receptacle • Smooth Face • Tamper-Resistant • Back and Side Wire 	 	White	T5661-W	T5461-W
		Ivory	T5661-I	T5461-I
		Lt Almond	T5661-T	T5461-T
		Brown	T5661	T5461
		Gray	T5661-GY	T5461-GY
		Black	T5661-E	T5461-E
<ul style="list-style-type: none"> • Single Receptacle • Smooth Face • Isolated Ground • Back and Side Wire • Pre-wired Ground Lead 	 	Orange	5661-IG	5461-IG
		Orange	5662-IG	5462-IG
<ul style="list-style-type: none"> • Duplex Receptacle • Smooth Face • Isolated Ground • Back and Side Wire 		Orange	5662-IG	5462-IG
		Orange	5662-IG	5462-IG
<ul style="list-style-type: none"> • Single Receptacle • Smooth Face • Corrosion-Resistant • Back and Side Wire 	 	Yellow	5661-CR	5461-CR
		Yellow	5661-CR	5461-CR
<ul style="list-style-type: none"> • Single Receptacle • Smooth Face • Weather-Resistant • Back and Side Wire 	 	White	W5661-W	W5461-W
		Ivory	W5661-I	W5461-I
		Lt Almond	W5661-T	W5461-T
		Brown	W5661	W5461
		Gray	W5661-GY	W5461-GY
		Black	W5661-E	W5461-E
		Yellow	W5661-Y	W5461-Y
		White	W5661-TOW	W5461-TOW
<ul style="list-style-type: none"> • Single Receptacle • Smooth Face • Weather- and Tamper-Resistant • Back and Side Wire 	  	Ivory	W5661-TOI	W5461-TOI
		Lt Almond	W5661-TOT	W5461-TOT
		Brown	W5661-T00	W5461-T00
		Gray	W5661-TGY	W5461-TGY
		Black	W5661-T0E	W5461-T0E
		Yellow	W5661-T0Y	W5461-T0Y
		Yellow	W5661-T0Y	W5461-T0Y



5461-W



5662-IG



CR20-W

Standard Receptacles

COMMERCIAL SPECIFICATION GRADE



2-Pole, 3-Wire • 125 Volt

Color

15 Amp

20 Amp

STANDARD	<ul style="list-style-type: none"> Single Receptacle Indented Face Side Wire Only 	White	5015-W	5801-W
		Ivory	5015-I	5801-I
		Lt Almond	5015-T	5801-T
		Brown	5015	5801
	<ul style="list-style-type: none"> Single Receptacle Indented Face Back and Side Wire 	White	—	5891-W
		Ivory	5088-I	—
		Brown	5088	5891
	<ul style="list-style-type: none"> Duplex Receptacle Smooth Face Side Wire Only 	White	CR015-W	CR020-W
		Ivory	CR015-I	CR020-I
		Brown	CR015	CR020
Gray		CR015-GY	CR020-GY	
Black		CR015-E	CR020-E	
<ul style="list-style-type: none"> Duplex Receptacle Indented Face Side Wire Only 	White	CR15-W	CR20-W	
	Ivory	CR15-I	CR20-I	
	Lt Almond	CR15-T	CR20-T	
	Brown	CR15	CR20	
	Gray	CR15-GY	CR20-GY	
	Black	CR15-E	CR20-E	
	Orange	—	CR20-O	
<ul style="list-style-type: none"> Duplex Receptacle Indented Face Back and Side Wire 	White	BR15-W	BR20-W	
	Ivory	BR15-I	BR20-I	
	Lt Almond	BR15-T	BR20-T	
	Brown	BR15	BR20	
	Gray	BR15-GY	BR20-GY	
	Black	BR15-E	BR20-E	
<ul style="list-style-type: none"> Single Receptacle Smooth Face Tamper-Resistant Back and Side Wire Grounding 	White	T5015-W	T5020-W	
	Ivory	T5015-I	T5020-I	
	Lt Almond	T5015-T	T5020-T	
	Brown	T5015	T5020	
	Gray	T5015-GY	T5020-GY	
	Black	T5015-E	T5020-E	
<ul style="list-style-type: none"> Duplex Receptacle Smooth Face Tamper-Resistant Back and Side Wire 	White	TBR15-W	TBR20-W	
	Ivory	TBR15-I	TBR20-I	
	Lt Almond	TBR15-T	TBR20-T	
	Brown	TBR15	TBR20	
	Gray	TBR15-GY	TBR20-GY	
	Black	TBR15-E	TBR20-E	
<ul style="list-style-type: none"> Duplex Receptacle Smooth Face Tamper-Resistant Side Wire Only 	White	TCR15-W	TCR20-W	
	Ivory	TCR15-I	TCR20-I	
	Lt Almond	TCR15-T	TCR20-T	
	Brown	TCR15	TCR20	
	Gray	TCR15-GY	TCR20-GY	
<ul style="list-style-type: none"> Single Receptacle Smooth Face Back and Side Wire 	White	16251-W	16351-W	
	Ivory	16251-I	16351-I	
	Brown	16251	16351	



BR20-W



16351-I



TBR20-W

COMMERCIAL SPECIFICATION GRADE



2-Pole, 3-Wire • 125 Volt

	Color	15 Amp	20 Amp
DECORA PLUS™	• Single Receptacle	White 16241-W	16341-W
	• Smooth Face	Ivory 16241-I	16341-I
	• Side Wire Only	Lt Almond —	16341-T
		Brown —	16341
		Gray —	16341-GY
		Black —	16341-E
		White —	16351-SGW



COMMERCIAL SPECIFICATION GRADE



2-Pole, 3-Wire • 125/250 Volt

	Color	20 Amp
STD.	• Single Receptacle	Ivory 5032-I
	• Smooth Face	Brown 5032



125/250 V



16292-W

COMMERCIAL SPECIFICATION GRADE



2-Pole, 3-Wire • 125 and 250 Volt

	Color	15 Amp
STD.	• Duplex Receptacle	White 5031-W
	• Indented Face	Ivory 5031-I
	• Side Wire Only	Brown 5031
DECORA PLUS™	• Duplex Receptacle	White 16292-W
	• Smooth Face	Ivory 16292-I

COMBO



5842-I

COMMERCIAL SPECIFICATION GRADE



2-Pole, 3-Wire • 125 and 250 Volt

	Color	20 Amp
STANDARD	• Duplex Receptacle	Ivory 5842-I
	• Indented Face	Brown 5842
	• Duplex Receptacle	Ivory 5844-I
	• Indented Face	Brown 5844

COMBO

COMMERCIAL SPECIFICATION GRADE



3-Pole, 4-Wire • 125/250 Volt

	Color	20 Amp
STD.	• Single Receptacle	Black 8410



125/250 V



5821-W

COMMERCIAL SPECIFICATION GRADE



2-Pole, 3-Wire • 250 Volt

	Color	15 Amp	20 Amp
STANDARD	• Duplex Receptacle	White —	5822-W
	• Indented Face	Ivory 5028-I	5822-I
	• Side Wire Only	Brown 5028	5822
	• Single Receptacle	White 5029-W	5821-W
	• Indented Face	Ivory 5029-I	5821-I
	• Side Wire Only	Lt Almond —	5821-T
		Brown 5029	5821

250 V



Standard Receptacles



COMMERCIAL SPECIFICATION GRADE		NEMA 6-15R	NEMA 6-20R	250 V
2-Pole, 3-Wire • 250 Volt		15 Amp	20 Amp	
STD.	• Single Receptacle	Ivory	5089-I	5823-I
	• Indented Face	Brown	—	5823
	• Back and Side Wire			
DECORA PLUS™	• Single Receptacle	White	16651-W	16451-W
	• Smooth Face	Ivory	16651-I	16451-I
	• Back and Side Wire			
	• Duplex Receptacle	White	—	16462-W
	• Smooth Face	Ivory	16662-I	16462-I
	• Back and Side Wire	Black	—	16462-E
	• Single Receptacle	White	16641-W	16441-W
	• Smooth Face	Ivory	16641-I	16441-I
	• Side Wire Only	Lt Almond	—	16441-T
COMMERCIAL SPECIFICATION GRADE		NEMA 7-15R	277 V	
2-Pole, 3-Wire • 277 Volt		15 Amp		
STD.	• Duplex Receptacle	Brown	5585	
	• Smooth Face			
	• Back and Side Wire			



5585

Time Savings

lev-lok® Modular Receptacles

The perfect productivity solution for electrical construction & maintenance applications.



KEY FEATURES AND BENEFITS

<p>Future Proof</p> <p>It's 5x faster to replace devices in a facility to meet future needs, whether you're updating technology or meeting new requirements.</p>	<p>Compress Timelines</p> <p>Accelerate installation and swap outs to complete projects faster than using traditional wiring.</p>	<p>Accurate & Secure Connection</p> <p>Lev-Lok® lowers the risk of incorrect installation while providing a safe and secure connection.</p>

CALCULATE YOUR SAVINGS ONLINE: www.leviton.com/levlokcalculator

lev-lok® Modular Wiring Devices: Receptacles

HOSPITAL GRADE Extra Heavy-Duty




2-Pole, 3-Wire • 125 Volt		Color	15 Amp	20 Amp
<ul style="list-style-type: none"> Duplex Receptacle Smooth Face 		White	M8200-W	M8300-W
		Ivory	M8200-I	M8300-I
		Lt Almond	M8200-T	M8300-T
		Brown	M8200	M8300
		Gray	M8200-GY	M8300-GY
		Black	M8200-E	M8300-E
		Red	M8200-R	M8300-R
		Blue	M8200-B	M8300-B
<ul style="list-style-type: none"> Duplex Receptacle Smooth Face Tamper-Resistant 		White	M8200-SGW	M8300-SGW
		Ivory	M8200-SGI	M8300-SGI
		Lt Almond	M8200-SGT	M8300-SGT
		Brown	M8200-SG	M8300-SG
		Gray	M8200-SGG	M8300-SGG
		Black	M8200-SGE	M8300-SGE
		Red	M8200-SGR	M8300-SGR
		Blue	M8200-SGB	M8300-SGB
STANDARD <ul style="list-style-type: none"> Duplex Receptacle Smooth Face MRI 		White	MRI15-W	MRI20-W
		Ivory	MRI15-I	MRI20-I
		Lt Almond	MRI15-T	MRI20-T
		Gray	MRI15-GY	MRI20-GY
		Red	MRI15-R	MRI20-R
<ul style="list-style-type: none"> Duplex Receptacle Smooth Face Power Indication LED 		White	M8200-PLW	M8300-PLW
		Ivory	M8200-PLI	M8300-PLI
		Lt Almond	M8200-PLT	M8300-PLT
		Gray	M8200-PLG	M8300-PLG
		Red	M8200-PLR	M8300-PLR
<ul style="list-style-type: none"> Duplex Receptacle Smooth Face Illuminated Blade Slot 		White	M8200-ILW	M8300-ILW
		Ivory	M8200-ILI	M8300-ILI
		Lt Almond	M8200-ILT	M8300-ILT
		Gray	M8200-ILG	M8300-ILG
		Red	M8200-ILR	M8300-ILR
<ul style="list-style-type: none"> Duplex Receptacle Smooth Face Tamper-Resistant Illuminated Blade Slot 		White	MT820-ILW	MT830-ILW
		Ivory	MT820-ILI	MT830-ILI
		Lt Almond	MT820-ILT	MT830-ILT
		Gray	MT820-ILG	MT830-ILG
		Red	MT820-ILR	MT830-ILR

SIMPLE AND SECURE



Install Wiring Module

All modules have a Circuit ID Label for ease of identification



Connect Wiring Device

Simply push and twist to lock connection



Finish Installation

Install device into box and finish with wallplate

MSTWL series wiring modules (sold separately) must be used with Lev-Lok receptacles. See page 27 for options and ordering information.



FOR MORE INFORMATION ON THE FULL LINE: www.leviton.com/levlok

lev-lok® Modular Wiring Devices: Receptacles

HOSPITAL GRADE

Extra Heavy-Duty



2-Pole, 3-Wire • 125 Volt

Color

15 Amp

20 Amp

DECORA PLUS™	Features	Icon	NEMA 5-15R		NEMA 5-20R		
			Color	15 Amp	Color	20 Amp	
• Duplex Receptacle • Smooth Face			White	M1626-HGW	M1636-HGW		
			Ivory	M1626-HGI	M1636-HGI		
			Lt Almond	M1626-HGT	M1636-HGT		
			Gray	M1626-HGG	M1636-HGG		
			Black	M1626-HGE	M1636-HGE		
			Red	M1626-HGR	M1636-HGR		
			Blue	M1626-HGB	M1636-HGB		
			• Duplex Receptacle • Smooth Face • Tamper-Resistant	TR	White	MT162-HGW	MT163-HGW
					Ivory	MT162-HGI	MT163-HGI
					Lt Almond	—	MT163-HGT
Gray	MT162-HGG	MT163-HGG					
• Duplex Receptacle • Smooth Face • Power Indication LED	LED	White	M1626-PLW	M1636-PLW			
		Ivory	M1626-PLI	M1636-PLI			
		Lt Almond	M1626-PLT	M1636-PLT			
		Gray	M1626-PLG	M1636-PLG			
		Red	M1626-PLR	M1636-PLR			
• Duplex Receptacle • Smooth Face • Illuminated Blade Slot	LED	White	M1626-ILW	M1636-ILW			
		Ivory	M1626-ILI	M1636-ILI			
		Lt Almond	M1626-ILT	M1636-ILT			
		Gray	M1626-ILG	M1636-ILG			
		Red	M1626-ILR	M1636-ILR			
• Duplex Receptacle • Smooth Face • Tamper-Resistant • Illuminated Blade Slot	TR, LED	White	MT162-ILW	MT163-ILW			
		Ivory	MT162-ILI	MT163-ILI			
		Lt Almond	MT162-ILT	MT163-ILT			
		Gray	MT162-ILG	MT163-ILG			
		Red	MT162-ILR	MT163-ILR			



M8300-ILI



M1626-HGR

HOSPITAL GRADE

Heavy-Duty



2-Pole, 3-Wire • 125 Volt

Color

15 Amp

20 Amp

STANDARD	Features	NEMA 5-15R		NEMA 5-20R	
		Color	15 Amp	Color	20 Amp
• Duplex Receptacle • Smooth Face		White	M8200-HW	M8300-HW	
		Ivory	M8200-HI	M8300-HI	
		Lt Almond	M8200-HT	M8300-HT	
		Brown	M8200-H	M8300-H	
		Gray	M8200-HGY	M8300-HGY	
		Black	M8200-HE	M8300-HE	
		Red	M8200-HR	M8300-HR	
		Blue	M8200-HB	M8300-HB	

Receptacles must be used with MSTWL series wiring modules (sold separately). See pg 27 for module details.



MSTWL-R

lev-lok® Modular Wiring Devices: Receptacles

HOSPITAL GRADE Heavy-Duty



2-Pole, 3-Wire • 125 Volt		Color	15 Amp	20 Amp		
STANDARD	<ul style="list-style-type: none"> Duplex Receptacle Smooth Face Tamper-Resistant 	White	MT820-W	MT830-W		
		Ivory	MT820-I	MT830-I		
		Lt Almond	MT820-T	MT830-T		
		Brown	MT820	MT830		
		Gray	MT820-GY	MT830-GY		
		Black	MT820-E	MT830-E		
	<ul style="list-style-type: none"> Duplex Receptacle Smooth Face Isolated Ground 	 Red Blue	MT820-R MT820-B	MT830-R MT830-B		
		<ul style="list-style-type: none"> Duplex Receptacle Smooth Face Isolated Ground 		White	M8200-IGW	M8300-IGW
				Ivory	M8200-IGI	M8300-IGI
				Lt Almond	M8200-IGT	M8300-IGT
				Gray	M8200-IGG	M8300-IGG
				Black	M8200-IGE	M8300-IGE
  Red Orange	M8200-IGR M8200-IG			M8300-IGR M8300-IG		
DECORA PLUS™	<ul style="list-style-type: none"> Duplex Receptacle Smooth Face Isolated Ground 		White	MD820-IGW	MD830-IGW	
			Ivory	MD820-IGI	MD830-IGI	
			Lt Almond	MD820-IGT	MD830-IGT	
			Gray	MD820-IGG	MD830-IGG	
			Black	MD820-IGE	MD830-IGE	
			  Red Orange	MD820-IGR MD820-IG	MD830-IGR MD830-IG	
	<ul style="list-style-type: none"> Duplex Receptacle Smooth Face Isolated Ground Tamper-Resistant 		White	MDT82-IGW	MDT83-IGW	
			Ivory	MDT82-IGI	MDT83-IGI	
			Lt Almond	MDT82-IGT	MDT83-IGT	
			Gray	MDT82-IGG	MDT83-IGG	
			Black	MDT82-IGE	MDT83-IGE	
			  Red Orange	MDT82-IGR MDT82-IG	MDT83-IGR MDT83-IG	



lev-lok® Modular Wiring Devices: Receptacles

INDUSTRIAL SPECIFICATION GRADE

Extra Heavy-Duty



2-Pole, 3-Wire • 125 Volt

	Color	15 Amp	20 Amp	
STANDARD • Duplex Receptacle • Smooth Face	White	M5262-W	M5362-W	
	Ivory	M5262-I	M5362-I	
	Lt Almond	M5262-T	M5362-T	
	Brown	M5262	M5362	
	Gray	M5262-GY	M5362-GY	
	Black	M5262-E	M5362-E	
	Red	M5262-R	M5362-R	
	Blue	M5262-B	M5362-B	
	STANDARD • Duplex Receptacle • Smooth Face • Tamper-Resistant	White	M5262-SGW	M5362-SGW
		Ivory	M5262-SGI	M5362-SGI
Lt Almond		M5262-SGT	M5362-SGT	
Brown		M5262-SG	M5362-SG	
Gray		M5262-SGG	M5362-SGG	
Black		M5262-SGE	M5362-SGE	
Red		M5262-SGR	M5362-SGR	
Blue		M5262-SGB	M5362-SGB	



M5362-SGW

INDUSTRIAL SPECIFICATION GRADE

Heavy-Duty



2-Pole, 3-Wire • 125 Volt

	Color	15 Amp	20 Amp
STANDARD • Duplex Receptacle • Smooth Face	White	M5262-SW	M5362-SW
	Ivory	M5262-SI	M5362-SI
	Lt Almond	M5262-ST	M5362-ST
	Brown	M5262-S	M5362-S
	Gray	M5262-GYS	M5362-GYS
	Black	M5262-SE	M5362-SE
	Red	M5262-SR	M5362-SR
	Blue	M5262-SB	M5362-SB
STANDARD • Duplex Receptacle • Smooth Face • Tamper-Resistant	White	MT562-SW	MT563-SW
	Ivory	MT562-SI	MT563-SI
	Lt Almond	MT562-ST	MT563-ST
	Brown	MT562-S	MT563-S
	Gray	MT562-SGY	MT563-SY
	Black	MT562-SE	MT563-SE
STANDARD • Duplex Receptacle • Smooth Face • Tamper-Resistant	Red	MT562-SR	MT563-SR
	Blue	MT562-SB	MT563-SB



Detail of the solid brass pins on the back of a Lev-Lok Receptacle (straps may vary by device).

Receptacles must be used with MSTWL series wiring modules (sold separately). See pg 27 for module details.



MSTWL-A

lev-lok® Modular Wiring Devices: Receptacles

INDUSTRIAL SPECIFICATION GRADE
Heavy-Duty



2-Pole, 3-Wire • 125 Volt		Color	15 Amp	20 Amp		
<ul style="list-style-type: none"> • Duplex Receptacle • Smooth Face • Two Outlets Marked "Controlled" 		White	M5262-2SW	M5362-2SW		
		Ivory	M5262-2SI	M5362-2SI		
		Lt Almond	M5262-2ST	M5362-2ST		
		Brown	M5262-2S	M5362-2S		
		Gray	M5262-2SG	M5362-2SG		
		Black	M5262-2SE	M5362-2SE		
		Red	M5262-2SR	M5362-2SR		
		Green	M5262-2SN	M5362-2SN		
		Blue	M5262-2SU	M5362-2SU		
		<ul style="list-style-type: none"> • Duplex Receptacle • Smooth Face • Split-Circuit • Separate lead provided 		White	M5262-SCW	M5362-SCW
				Ivory	M5262-SCI	M5362-SCI
				Lt Almond	M5262-SCT	M5362-SCT
				Brown	M5262-SC	M5362-SC
Gray	M5262-SCG			M5362-SCG		
Black	M5262-SCE			M5362-SCE		
Red	M5262-SCR			M5362-SCR		
Blue	M5262-SCB			M5362-SCB		
<ul style="list-style-type: none"> • Duplex Receptacle • Smooth Face • Isolated Ground 				White	M5262-IGW	M5362-IGW
				Ivory	M5262-IGI	M5362-IGI
		Lt Almond	M5262-IGT	M5362-IGT		
		Gray	M5262-IGG	M5362-IGG		
		Black	M5262-IGE	M5362-IGE		
		Red	M5262-IGR	M5362-IGR		
		Orange	M5262-IG	M5362-IG		
		<ul style="list-style-type: none"> • Duplex Receptacle • Smooth Face • Tamper-Resistant • Two Outlets Marked "Controlled" 		White	MT562-2SW	MT563-2SW
Ivory	MT562-2SI			MT563-2SI		
Lt Almond	MT562-2ST			MT563-2ST		
Brown	MT562-2S			MT563-2S		
Gray	MT562-2SG			MT563-2SG		
Black	MT562-2SE			MT563-2SE		
Red	MT562-2SR			MT563-2SR		
Green	MT562-2SN			MT563-2SN		
Blue	MT562-2SU			MT563-2SU		
<ul style="list-style-type: none"> • Duplex Receptacle • Smooth Face • Tamper-Resistant • Split-Circuit • Separate lead provided 				White	MT562-SCW	MT563-SCW
				Ivory	MT562-SCI	MT563-SCI
				Lt Almond	MT562-SCT	MT563-SCT
				Brown	MT562-SC	MT563-SC
		Gray	MT562-SCG	MT563-SCG		
		Black	MT562-SCE	MT563-SCE		
		Blue	MT562-SCB	MT563-SCB		



MT563-SW



M5362-SCI

Receptacle modules are available in both stranded and solid wire. Options for 4-port push wire connectors are also available. See pg 27 for module details.



lev-lok® Modular Wiring Devices: Receptacles

INDUSTRIAL SPECIFICATION GRADE Heavy-Duty



2-Pole, 3-Wire • 125 Volt

Color

15 Amp

20 Amp

- Duplex Receptacle
- Smooth Face
- Split-Circuit, One Outlet Marked "Controlled"
- Separate lead provided for controlled receptacle



White	M5262-1CW	M5362-1CW
Ivory	M5262-1CI	M5362-1CI
Lt Almond	M5262-1CT	M5362-1CT
Brown	M5262-1C	M5362-1C
Gray	M5262-1CG	M5362-1CG
Black	M5262-1CE	M5362-1CE
Red	M5262-1CR	M5362-1CR
Blue	M5262-1CB	M5362-1CB

STANDARD

- Duplex Receptacle
- Smooth Face
- Tamper-Resistant
- Split-Circuit, One Outlet Marked "Controlled"
- Separate lead provided for controlled receptacle



White	MT562-1CW	MT563-1CW
Ivory	MT562-1CI	MT563-1CI
Lt Almond	MT562-1CT	MT563-1CT
Brown	MT562-1C	MT563-1C
Gray	MT562-1CG	MT563-1CG
Black	MT562-1CE	MT563-1CE
Red	MT562-1CR	MT563-1CR
Blue	MT562-1CB	MT563-1CB

- Duplex Receptacle
- Smooth Face
- Tamper-Resistant
- Isolated Ground



White	MT562-IGW	MT563-IGW
Ivory	MT562-IGI	MT563-IGI
Lt Almond	MT562-IGT	MT563-IGT
Gray	MT562-IGG	MT563-IGG
Black	MT562-IGE	MT563-IGE
Red	MT562-IGR	MT563-IGR
Orange	MT562-IG	MT563-IG

DECORA PLUS™

- Duplex Receptacle
- Smooth Face

White	M1626-W	M1636-W
Ivory	M1626-I	M1636-I
Lt Almond	M1626-T	M1636-T
Brown	M1626	M1636
Gray	M1626-GY	M1636-GY
Black	M1626-E	M1636-E
Red	M1626-R	M1636-R
Blue	M1626-B	M1636-B

- Duplex Receptacle
- Smooth Face
- Tamper-Resistant



White	MT162-W	MT163-W
Ivory	MT162-I	MT163-I
Lt Almond	MT162-T	MT163-T
Brown	MT162	MT163
Gray	MT162-GY	MT163-GY
Black	MT162-E	MT163-E
Red	MT162-R	MT163-R
Blue	MT162-B	MT163-B



M5362-2SW



MT562-SCG

Receptacles must be used with MSTWL series wiring modules (sold separately). See pg 27 for module details.




MSTWL-SIG

lev-lok® Modular Wiring Devices: Receptacles

INDUSTRIAL SPECIFICATION GRADE
Heavy-Duty



2-Pole, 3-Wire • 125 Volt		Color	15 Amp	20 Amp		
<ul style="list-style-type: none"> Duplex Receptacle Smooth Face Two Outlets Marked "Controlled" 		White	M1626-2SW	M1636-2SW		
		Ivory	M1626-2SI	M1636-2SI		
		Lt Almond	M1626-2ST	M1636-2ST		
		Brown	M1626-2S	M1636-2S		
		Gray	M1626-2SG	M1636-2SG		
		Black	M1626-2SE	M1636-2SE		
		Red	M1626-2SR	M1636-2SR		
		Green	M1626-2SN	M1636-2SN		
		Blue	M1626-2SU	M1636-2SU		
		<ul style="list-style-type: none"> Duplex Receptacle Smooth Face Split-Circuit Separate lead provided 		White	M1626-SCW	M1636-SCW
Ivory	M1626-SCI			M1636-SCI		
Lt Almond	M1626-SCT			M1636-SCT		
Brown	M1626-SC			M1636-SC		
Gray	M1626-SCG			M1636-SCG		
Black	M1626-SCE			M1636-SCE		
Red	M1626-SCR			M1636-SCR		
Blue	M1626-SCB			M1636-SCB		
<ul style="list-style-type: none"> Duplex Receptacle Smooth Face Isolated Ground 				White	M1626-IGW	M1636-IGW
				Ivory	M1626-IGI	M1636-IGI
		Lt Almond	M1626-IGT	M1636-IGT		
		Gray	M1626-IGG	M1636-IGG		
		Black	M1626-IGE	M1636-IGE		
		Red	M1626-IGR	M1636-IGR		
		Orange	M1626-IG	M1636-IG		
		<ul style="list-style-type: none"> Duplex Receptacle Smooth Face Split-Circuit, One Outlet Marked "Controlled" 		White	M1626-1CW	M1636-1CW
				Ivory	M1626-1CI	M1636-1CI
				Lt Almond	M1626-1CT	M1636-1CT
Brown	M1626-1C			M1636-1C		
Gray	M1626-1CG			M1636-1CG		
Black	M1626-1CE			M1636-1CE		
Red	M1626-1CR			M1636-1CR		
Blue	M1626-1CB			M1636-1CB		
<ul style="list-style-type: none"> Duplex Receptacle Smooth Face Tamper-Resistant Two Outlets Marked "Controlled" 				White	MT162-2W	MT163-2W
				Ivory	MT162-2I	MT163-2I
		Lt Almond	MT162-2T	MT163-2T		
		Brown	MT162-2	MT163-2		
		Gray	MT162-2GY	MT163-2GY		
		Black	MT162-2E	MT163-2E		
		Red	MT162-2R	MT163-2R		
		Green	MT162-2GN	MT163-2GN		
		Blue	MT162-2BU	MT163-2BU		



lev-lok® Modular Wiring Devices: Receptacles

INDUSTRIAL SPECIFICATION GRADE Heavy-Duty



2-Pole, 3-Wire • 125 Volt

Color

15 Amp

20 Amp

DECORA PLUS™	<ul style="list-style-type: none"> Duplex Receptacle Smooth Face Tamper-Resistant Split-Circuit Separate lead provided 		White	MT162-SCW	MT163-SCW
			Ivory	MT162-SCI	MT163-SCI
			Lt Almond	MT162-SCT	MT163-SCT
			Brown	MT162-SC	MT163-SC
			Gray	MT162-SCG	MT163-SCG
			Black	MT162-SCE	MT163-SCE
	<ul style="list-style-type: none"> Duplex Receptacle Smooth Face Tamper-Resistant Isolated Ground 		Red	MT162-SCR	MT163-SCR
			Blue	MT162-SCB	MT163-SCB
			White	MT162-IGW	MT163-IGW
			Ivory	MT162-IGI	MT163-IGI
			Lt Almond	MT162-IGT	MT163-IGT
			Gray	MT162-IGG	MT163-IGG
<ul style="list-style-type: none"> Duplex Receptacle Smooth Face Tamper-Resistant Split-Circuit, One Outlet Marked "Controlled" Separate lead provided for controlled receptacle 		Black	MT162-IGE	MT163-IGE	
		Red	MT162-IGR	MT163-IGR	
		Orange	MT162-IG	MT163-IG	
		White	MT162-1CW	MT163-1CW	
		Ivory	MT162-1CI	MT163-1CI	
		Lt Almond	MT162-1CT	MT163-1CT	
		Brown	MT162-1C	MT163-1C	
		Gray	MT162-1CG	MT163-1CG	
Black	MT162-1CE	MT163-1CE			
Red	MT162-1CR	MT163-1CR			
Blue	MT162-1CB	MT163-1CB			



lev-lok® Modular Wiring Devices: GFCI Receptacles

HOSPITAL GRADE Extra Heavy-Duty



2-Pole, 3-Wire • 125 Volt

Color

15 Amp

20 Amp

DECORA PLUS™	<ul style="list-style-type: none"> SmartlockPro® Self-Test GFCI Duplex Receptacle Power Indication LED Back and Side Wire 20 Amp Feed-Through Terminals 		White	MGFN1-HGW	MGFN2-HGW
			Ivory	MGFN1-HGI	MGFN2-HGI
			Lt Almond	MGFN1-HGT	MGFN2-HGT
			Brown	MGFN1-HG	MGFN2-HG
			Gray	MGFN1-HGG	MGFN2-HGG
			Black	MGFN1-HGE	MGFN2-HGE
	<ul style="list-style-type: none"> SmartlockPro® Self-Test GFCI Duplex Receptacle Power Indication LED Tamper-Resistant Back and Side Wire 20 Amp Feed-Through Terminals 		Red	MGFN1-HGR	MGFN2-HGR
			White	MGFT1-HGW	MGFT2-HGW
			Ivory	MGFT1-HGI	MGFT2-HGI
			Lt Almond	MGFT1-HGT	MGFT2-HGT
			Brown	MGFT1-HG	MGFT2-HG
			Gray	MGFT1-HGG	MGFT2-HGG
Black	MGFT1-HGE	MGFT2-HGE			
Red	MGFT1-HGR	MGFT2-HGR			



lev-lok® Modular Wiring Devices: GFCI Receptacles

INDUSTRIAL SPECIFICATION GRADE
Extra Heavy-Duty



2-Pole, 3-Wire • 125 Volt		Color	15 Amp	20 Amp
DECORA PLUS™	<ul style="list-style-type: none"> SmartlockPro® Self-Test GFCI Duplex Receptacle Power Indication LED 20 Amp Feed-Through Terminals 	White	MGFN1-W	MGFN2-W
		Ivory	MGFN1-I	MGFN2-I
		Lt Almond	MGFN1-T	MGFN2-T
		Brown	MGFN1	MGFN2
		Gray	MGFN1-GY	MGFN2-GY
		Black	MGFN1-E	MGFN2-E
	<ul style="list-style-type: none"> SmartlockPro® Self-Test GFCI Duplex Receptacle Power Indication LED Tamper-Resistant 20 Amp Feed-Through Terminals 	Red	MGFN1-R	MGFN2-R
		White	MGFT1-W	MGFT2-W
		Ivory	MGFT1-I	MGFT2-I
		Lt Almond	MGFT1-T	MGFT2-T
		Brown	MGFT1	MGFT2
		Gray	MGFT1-GY	MGFT2-GY
		Black	MGFT1-E	MGFT2-E
		Red	MGFT1-R	MGFT2-R



MGFN2-GY



M58AA-HGR



M56AC-HGW

lev-lok® Modular Wiring Devices: USB Receptacles

HOSPITAL GRADE
Extra Heavy-Duty



2-Pole, 3-Wire • 125 Volt		Color	15 Amp	20 Amp
DECORA PLUS™	<ul style="list-style-type: none"> Duplex Receptacle Two Type A USB Ports Smooth Face Tamper-Resistant 	White	M56AA-HGW	M58AA-HGW
		Ivory	M56AA-HGI	M58AA-HGI
		Lt Almond	M56AA-HGT	M58AA-HGT
		Brown	M56AA-HG	M58AA-HG
		Gray	M56AA-HGG	M58AA-HGG
		Black	M56AA-HGE	M58AA-HGE
	<ul style="list-style-type: none"> Duplex Receptacle One Type A & One Type C USB Port Smooth Face Tamper-Resistant 	Red	M56AA-HGR	M58AA-HGR
		White	M56AC-HGW	M58AC-HGW
		Ivory	M56AC-HGI	M58AC-HGI
		Lt Almond	M56AC-HGT	M58AC-HGT
		Brown	M56AC-HG	M58AC-HG
		Gray	M56AC-HGG	M58AC-HGG
		Black	M56AC-HGE	M58AC-HGE
		Red	M56AC-HGR	M58AC-HGR



lev-lok® Modular Wiring Devices: USB Receptacles

COMMERCIAL SPECIFICATION GRADE		NEMA 5-15R	NEMA 5-20R	
2-Pole, 3-Wire • 125 Volt		15 Amp	20 Amp	
DECORA PLUS™	<ul style="list-style-type: none"> Duplex Receptacle Two Type A USB Ports Smooth Face Tamper-Resistant 	White	M56AA-W	M58AA-W
		Ivory	M56AA-I	M58AA-I
		Lt Almond	M56AA-T	M58AA-T
		Brown	M56AA	M58AA
		Gray	M56AA-GY	M58AA-GY
		Black	M56AA-E	M58AA-E
		Red	M56AA-R	M58AA-R
		Orange	M56AA-O	M58AA-O
		Green	M56AA-N	M58AA-N
		Blue	M56AA-B	M58AA-B
	<ul style="list-style-type: none"> Duplex Receptacle One Type A & One Type C USB Port Smooth Face Tamper-Resistant 	White	M56AC-W	M58AC-W
		Ivory	M56AC-I	M58AC-I
		Lt Almond	M56AC-T	M58AC-T
		Brown	M56AC	M58AC
		Gray	M56AC-GY	M58AC-GY
		Black	M56AC-E	M58AC-E
		Red	M56AC-R	M58AC-R
		Orange	M56AC-O	M58AC-O
		Green	M56AC-N	M58AC-N
		Blue	M56AC-B	M58AC-B



lev-lok® Modular Wiring Devices: Surge Receptacles

HOSPITAL GRADE Heavy-Duty		NEMA 5-15R	NEMA 5-20R	
2-Pole, 3-Wire • 125 Volt		15 Amp	20 Amp	
DECORA PLUS™	<ul style="list-style-type: none"> Duplex Receptacle Surge Protective Tamper-Resistant Audible Alarm 	White	MT828-W	MT838-W
		Ivory	MT828-I	MT838-I
		Lt Almond	MT828-T	—
		Gray	—	MT838-GY
		Red	—	MT838-R
		Blue	MT828-B	MT838-B

COMMERCIAL SPECIFICATION GRADE		NEMA 5-15R	NEMA 5-20R	
2-Pole, 3-Wire • 125 Volt		15 Amp	20 Amp	
DECORA PLUS™	<ul style="list-style-type: none"> Duplex Receptacle Surge Protective Tamper-Resistant 	White	MT528-W	MT538-W
		Ivory	MT528-I	MT538-I
		Lt Almond	MT528-T	—
		Brown	MT528	MT538
		Gray	MT528-GY	MT538-GY
		Black	MT528-E	MT538-E
		Blue	MT528-B	MT538-B





lev-lok® Circuit Analyzer

Connect the receptacle wiring module to the circuit analyzer to confirm that wiring is correct, or identify a wiring problem.

Catalog Number: LVLOK-TST

lev-lok® Modular Wiring Devices: Surge Receptacles

COMMERCIAL SPECIFICATION GRADE		NEMA 5-15R 	NEMA 5-20R 	
2-Pole, 3-Wire • 125 Volt	Color	15 Amp	20 Amp	
DECORA PLUS™ <ul style="list-style-type: none"> • Duplex Receptacle • Surge Protective • Tamper-Resistant 	White	MT528-W	MT538-W	
	Ivory	MT528-I	MT538-I	
	Lt Almond	MT528-T	—	
	Brown	MT528	MT538	
	Gray	MT528-GY	MT538-GY	
	Black	MT528-E	MT538-E	
	Blue	MT528-B	MT538-B	
	<ul style="list-style-type: none"> • Duplex Receptacle • Surge Protective • Tamper-Resistant • Audible Alarm 	White	MT728-W	MT738-W
		Ivory	MT728-I	MT738-I
		Lt Almond	MT728-T	—
Black		MT728-E	MT738-E	
Blue	MT728-B	MT738-B		



lev-lok® Modular Wiring Receptacle Modules

20 Amp, 125 Volt Max.	Module Color	Wire Type	Wire Colors	Catalog Number
Stranded Wire Leads	White	THHN	Black, White, Green	MSTWL-A
Stranded Wire Leads with 4-Port Push Wire Connectors	White	THHN	Black, White, Green	MSTWL-WST
Dual Module for 2-Gang Applications with Leads Pre-Installed in Push Wire Connectors	White	THHN	Black, White, Green	MSTWL-WTK
Stranded Wire Leads for Emergency Circuits	Red	THHN	Black, White, Green	MSTWL-R
Stranded Wire Leads for Isolated Ground Circuits	Orange	THHN	Black, White, Green	MSTWL-IG
Stranded Wire Leads with 4-Port Push Wire Connectors for Isolated Ground Circuits	Orange	THHN	Black, White, Green	MSTWL-WIG
Solid Wire Leads	White	THHN	Black, White, Green	MSTWL-SDA
Solid Wire Leads for Isolated Ground Circuits	Orange	THHN	Black, White, Green	MSTWL-SIG
Solid Wire Leads with 4-Port Push Wire Connectors	White	THHN	Black, White, Green	MSTWL-WSD
Stranded Wire Leads for Low Leakage Circuits	White	XHHW-2	Orange, Brown, Green/Yellow	MSTWL-XA*
Stranded Wire Leads for Low Leakage Circuits	White	XHHW-2	Brown/Yellow, Orange/Blue, Green/Yellow	MSTWL-XI*
Stranded Wire Leads for Low Leakage Circuits	White	XHHW-2	Black, White, Green/Yellow	MSTWL-XN*

*Add suffix of 0 for 6", 1 for 12", 2 for 24" or 3 for 36" long leads; please allow 4 to 6 weeks for delivery



Wire Leads



Push Wire Connectors



Module for Emergency Circuits



Standard Module



Module for Isolated Ground Circuits




MSTWL-WTK for 2-Gang Applications

Receptacles with Pre-Wired Leads



KEY FEATURES & BENEFITS


- Eliminates the need to make pigtails
- Available in the most common configurations
- No terminal screws means faster wiring and no need to wrap device with electrical tape

HOSPITAL GRADE Heavy-Duty		NEMA 5-15R	NEMA 5-20R	
2-Pole, 3-Wire • 125 Volt		15 Amp	20 Amp	
STANDARD	• Duplex Receptacle	White	8200-LW	8300-LW
	• Smooth Face	Ivory	8200-LI	8300-LI
	• Pre-Wired Leads	Brown	8200-L	8300-L
		Gray	8200-LGY	8300-LGY
		Black	—	8300-LE
		Red	8200-LR	8300-LR
	• Duplex Receptacle	White	8200-CW	8300-CW
	• Smooth Face	Ivory	8200-CI	8300-CI
	• Pre-Wired Leads (hot and neutral only)	Gray	8200-CGY	8300-CGY
INDUSTRIAL SPECIFICATION GRADE Heavy-Duty		NEMA 5-15R	NEMA 5-20R	
2-Pole, 3-Wire • 125 Volt		15 Amp	20 Amp	
STANDARD	• Duplex Receptacle	White	5262-LW	5362-LW
	• Smooth Face	Ivory	5262-LI	5362-LI
	• Pre-Wired Leads	Lt Almond	—	5362-LT
		Brown	5262-L0	5362-L0
		Gray	5262-LGY	5362-LGY
		Black	5262-LE	5362-LE
		Red	5262-LR	5362-LR
	• Duplex Receptacle	White	5262-CW	—
	• Smooth Face	Ivory	5262-CI	—
	• Pre-Wired Leads (hot and neutral only)	Gray	5262-CGY	—
COMMERCIAL SPECIFICATION GRADE		NEMA 5-15R	NEMA 5-20R	
2-Pole, 3-Wire • 125 Volt		15 Amp	20 Amp	
STANDARD	• Duplex Receptacle	White	5040-W	5340-W
	• Smooth Face	Ivory	5040-I	5340-I
	• Pre-Wired Leads	Brown	—	5340
		Gray	—	5340-GY
	• Duplex Receptacle	White	5040-CW	5340-CW
	• Smooth Face	Ivory	5040-CI	5340-CI
	• Pre-Wired Leads (hot and neutral only)	Gray	5040-CGY	5340-CGY






Receptacles with Pre-Wired Leads

COMMERCIAL SPECIFICATION GRADE		NEMA 5-15R 	NEMA 5-20R 
2-Pole, 3-Wire • 125 Volt		15 Amp	20 Amp
DECORA PLUS™	• Duplex Receptacle	White 16252-LW	16352-LW
	• Smooth Face	Ivory 16252-LI	16352-LI
	• Pre-Wired Leads	Brown 16252-L0	—
		Gray 16252-LGY	16352-LGY
		Black 16252-LE	16352-LE
	• Duplex Receptacle	White —	16352-CW
	• Smooth Face	Ivory —	16352-CI
	• Pre-Wired Leads (hot and neutral only)	Gray —	16352-CGY



GFCI Receptacles with Pre-Wired Leads

INDUSTRIAL SPECIFICATION GRADE Extra Heavy-Duty		NEMA 5-15R 	NEMA 5-20R 
2-Pole, 3-Wire • 125 Volt		15 Amp	20 Amp
DECORA PLUS™	• SmartlockPro® Self-Test GFCI	White GFTR1-5LW	GFTR2-5LW
	• Duplex Receptacle	Ivory GFTR1-5LI	GFTR2-5LI
	• Power Indication LED	Lt Almond GFTR1-5LT	GFTR2-5LT
	• Tamper-Resistant	Brown GFTR1-5L	GFTR2-5L
	• 5 Pre-Wired Leads	Gray GFTR1-5LG	GFTR2-5LG
	• 20 Amp Feed-Through Terminals	Black GFTR1-5LE	GFTR2-5LE
		Red GFTR1-5LR	GFTR2-5LR
	• SmartlockPro® Self-Test GFCI	White GFTR1-3LW	GFTR2-3LW
	• Duplex Receptacle	Ivory GFTR1-3LI	GFTR2-3LI
	• Power Indication LED	Black GFTR1-3LE	—



smartlockpro® AFCI Receptacles

Outlet Branch Circuit (OBC) AFCI Devices offer advanced technology to help protect against electrical fires. These devices are designed to interrupt power in the event potentially hazardous arcing is detected, which could originate from a number of sources including damaged wires and cords. Meeting the latest UL requirements for OBC AFCI outlets, they provide protection against series and parallel arcs. SmartlockPro® OBC AFCI devices feature Leviton's patented reset lockout and tamper-resistant technology. AFCI's are now required by the National Electrical Code® (NEC) in many areas.

HOSPITAL GRADE Heavy-Duty		NEMA 5-15R	NEMA 5-20R
2-Pole, 3-Wire • 125 Volt		15 Amp	20 Amp
DECORA PLUS™ 	• Duplex Receptacle	White AFTR1-HGW	AFTR2-HGW
	• Power Indication LED	Ivory AFTR1-HGI	AFTR2-HGI
	• Tamper-Resistant	Lt Almond AFTR1-HGT	AFTR2-HGT
	• Back and Side Wire	Brown AFTR1-HG	AFTR2-HG
	• 20 Amp Feed-Through Terminals	Gray AFTR1-HGG	AFTR2-HGG
	• Wallplate Included	Black AFTR1-HGE	AFTR2-HGE
		Red AFTR1-HGR	AFTR2-HGR
COMMERCIAL SPECIFICATION GRADE		NEMA 5-15R	NEMA 5-20R
2-Pole, 3-Wire • 125 Volt		15 Amp	20 Amp
DECORA® 	• Duplex Receptacle	White AFTR1-W	AFTR2-W
	• Power Indication LED	Ivory AFTR1-I	AFTR2-I
	• Tamper-Resistant	Lt Almond AFTR1-T	AFTR2-T
	• Back and Side Wire	Brown AFTR1	AFTR2
	• 20 Amp Feed-Through Terminals	Gray AFTR1-GY	AFTR2-GY
	• Wallplate Included	Black AFTR1-E	AFTR2-E
• Blank Face Receptacle	White	—	AFRBF-W
	Ivory	—	AFRBF-I
	Lt Almond	—	AFRBF-T



smartlockpro® GFCI Receptacles

The SmartlockPro® Self-Test GFCIs contain the latest innovation in ground fault protection by automatically conducting a periodic internal test to confirm that the GFCI is able to respond to a ground fault. Easy to install, they take up to 25% less space in the wallbox vs. typical GFCIs and can fit into any box, even shallow ones. These slim GFCIs provide all the lockout benefits of our standard SmartlockPro® offering, and are available in tamper-resistant and non tamper-resistant versions. Constructed of resilient thermoplastic and able to withstand high torque levels, self-test GFCIs come in styles for every need, including a combination light/receptacle and a blankface device.



smartlockpro® GFCI Receptacles

HOSPITAL GRADE

Extra Heavy-Duty



2-Pole, 3-Wire • 125 Volt

Color

15 Amp

20 Amp

- Duplex Receptacle
- Power Indication LED
- Back and Side Wire
- 20 Amp Feed-Through Terminals
- Wallplate Included



White	GFNT1-HGW	GFNT2-HGW
Ivory	GFNT1-HGI	GFNT2-HGI
Lt Almond	GFNT1-HGT	GFNT2-HGT
Brown	GFNT1-HG	GFNT2-HG
Gray	GFNT1-HGG	GFNT2-HGG
Black	GFNT1-HGE	GFNT2-HGE
Red	GFNT1-HGR	GFNT2-HGR

- Duplex Receptacle
- Power Indication LED
- Back and Side Wire
- 20 Amp Feed-Through Terminals
- Wallplate Included
- **NAFTA Compliant**



White	GFNT1-HFW	GFNT2-HFW
Ivory	GFNT1-HFI	GFNT2-HFI
Lt Almond	GFNT1-HFT	GFNT2-HFT
Brown	GFNT1-HF	GFNT2-HF
Gray	GFNT1-HFG	GFNT2-HFG
Black	GFNT1-HFE	GFNT2-HFE
Red	GFNT1-HFR	GFNT2-HFR

- Duplex Receptacle
- Power Indication LED
- Tamper-Resistant
- Back and Side Wire
- 20 Amp Feed-Through Terminals
- Wallplate Included



White	GFTR1-HGW	GFTR2-HGW
Ivory	GFTR1-HGI	GFTR2-HGI
Lt Almond	GFTR1-HGT	GFTR2-HGT
Brown	GFTR1-HG	GFTR2-HG
Gray	GFTR1-HGG	GFTR2-HGG
Black	GFTR1-HGE	GFTR2-HGE
Red	GFTR1-HGR	GFTR2-HGR

- Duplex Receptacle
- Power Indication LED
- Tamper-Resistant
- Back and Side Wire
- 20 Amp Feed-Through Terminals
- Wallplate Included
- **NAFTA Compliant**



White	GFTR1-HFW	GFTR2-HFW
Ivory	GFTR1-HFI	GFTR2-HFI
Lt Almond	GFTR1-HFT	GFTR2-HFT
Brown	GFTR1-HF	GFTR2-HF
Gray	GFTR1-HFG	GFTR2-HFG
Black	GFTR1-HFE	GFTR2-HFE
Red	GFTR1-HFR	GFTR2-HFR

- Duplex Receptacle
- Power Indication LED
- Weather and Tamper-Resistant
- Back and Side Wire
- 20 Amp Feed-Through Terminals
- Wallplate Included



White	GFWT1-HGW	GFWT2-HGW
Ivory	GFWT1-HGI	GFWT2-HGI
Lt Almond	GFWT1-HGT	GFWT2-HGT
Brown	GFWT1-HG	GFWT2-HG
Gray	GFWT1-HGG	GFWT2-HGG
Black	GFWT1-HGE	GFWT2-HGE
Red	GFWT1-HGR	GFWT2-HGR

- Duplex Receptacle
- Tamper-Resistant
- **WHITE** Guidelight
- Power Indication LED
- Back and Side Wire
- 20 Amp Feed-Through Terminals
- Wallplate Included



White	GFNL1-HGW	GFNL2-HGW
Ivory	GFNL1-HGI	GFNL2-HGI
Lt Almond	GFNL1-HGT	GFNL2-HGT
Brown	GFNL1-HG	GFNL2-HG
Gray	GFNL1-HGG	GFNL2-HGG
Black	GFNL1-HGE	GFNL2-HGE
Red	GFNL1-HGR	GFNL2-HGR

DECORA PLUS™


GFCI Status Indicator Light

Leviton GFCI devices feature an LED Status Indicator Light which provides a visual indication to the user of the status of GFCI protection. This is a convenient way to check the level of protection at-a-glance.




Green LED - Normal Operation.

- GFCI has passed self-test and is providing power



Red LED - Alert!

- Blinking - Initial self-test upon first power up
- Solid or blinking - Press TEST and RESET buttons to reset GFCI
- If GFCI will not reset OR solid or blinking red continues, replace device



No LED - No Power.

- GFCI in tripped state
- Press RESET button
- If GFCI will not reset, no power on the circuit

smartlockpro® GFCI Receptacles

HOSPITAL GRADE

Heavy-Duty

2-Pole, 3-Wire • 125 Volt

Color



15 Amp



20 Amp

DECORA PLUS™

- Duplex Receptacle
- Tamper-Resistant
- AMBER Guidelight
- Power Indication LED
- Back and Side Wire
- 20 Amp Feed-Through Terminals



Amber guidelight ideal for healthcare applications where disrupting circadian rhythms is a concern



GFNL2-HWA

INDUSTRIAL SPECIFICATION GRADE

Extra Heavy-Duty

2-Pole, 3-Wire • 125 Volt

Color



15 Amp



20 Amp

DECORA PLUS™

- Duplex Receptacle
- DIN Rail Mount
- Power Indication LED
- Terminal Blocks
- 20 Amp Feed-Through Terminals
- Grounding



- Duplex Receptacle
- Power Indication LED
- Back and Side Wire
- 20 Amp Feed-Through Terminals



- Duplex Receptacle
- Power Indication LED
- Tamper-Resistant
- Back and Side Wire
- 20 Amp Feed-Through Terminals



- Duplex Receptacle
- Power Indication LED
- Tamper-Resistant
- Isolated Ground
- Back and Side Wire
- 20 Amp Feed-Through Terminals



- Duplex Receptacle
- Weather and Tamper-Resistant
- Power Indication LED
- Back and Side Wire
- 20 Amp Feed-Through Terminals
- Wallplate Included



Black

GFNT1-DIN

GFNT2-DIN

White

G5262-W

G5362-W

Ivory

G5262-I

G5362-I

Lt Almond

G5262-T

G5362-T

Brown

G5262

G5362

Gray

G5262-GY

G5362-GY

Black

G5262-E

G5362-E

Red

G5262-R

G5362-R

White

G5262-TW

G5362-TW

Ivory

G5262-TI

G5362-TI

Lt Almond

G5262-TT

G5362-TT

Brown

G5262-T0

G5362-T0

Gray

G5262-TGY

G5362-TGY

Black

G5262-TE

G5362-TE

Red

G5262-TR

G5362-TR

White

GFTR1-IGW

GFTR2-IGW

Ivory

GFTR1-IGI

GFTR2-IGI

Lt Almond

GFTR1-IGT

GFTR2-IGT

Brown

GFTR1-IG

GFTR2-IG

Gray

GFTR1-IGG

GFTR2-IGG

Black

GFTR1-IGE

GFTR2-IGE

Red

GFTR1-IGR

GFTR2-IGR

Orange

GFTR1-IG

GFTR2-IG

White

G5262-WTW

G5362-WTW

Ivory

G5262-WTI

G5362-WTI

Lt Almond

G5262-WTT

G5362-WTT

Brown

G5262-WT

G5362-WT

Gray

G5262-WTG

G5362-WTG

Black

G5262-WTE

G5362-WTE

Red

G5262-WTR

G5362-WTR



GFTR2-IGO



G5362-WTW

smartlockpro[®] GFCI Receptacles

INDUSTRIAL SPECIFICATION GRADE Extra Heavy-Duty



2-Pole, 3-Wire • 125 Volt

Color

15 Amp

20 Amp

DECORA PLUS[™]

- Single Receptacle
- Tamper-Resistant
- Pilot Light (Illuminated - ON)
- Back and Side Wire
- 20 Amp Feed-Through Terminals
- Wallplate Included



White	GFPL1-PLW	GFPL2-PLW
Ivory	GFPL1-PLI	GFPL2-PLI
Lt Almond	GFPL1-PLT	GFPL2-PLT
Brown	GFPL1-PL	GFPL2-PL
Gray	GFPL1-PLG	GFPL2-PLG
Black	GFPL1-PLE	GFPL2-PLE
Red	GFPL1-PLR	GFPL2-PLR

COMMERCIAL SPECIFICATION GRADE



2-Pole, 3-Wire • 125 Volt

Color

15 Amp

20 Amp

DECORA[®]

- Duplex Receptacle
- Power Indication LED
- Back and Side Wire
- 20 Amp Feed-Through Terminals
- Wallplate Included



White	GFNT1-W	GFNT2-W
Ivory	GFNT1-I	GFNT2-I
Lt Almond	GFNT1-T	GFNT2-T
Brown	GFNT1	GFNT2
Gray	GFNT1-GY	GFNT2-GY
Black	GFNT1-E	GFNT2-E
Red	—	GFNT2-R

- Duplex Receptacle
- Power Indication LED
- Tamper-Resistant
- Back and Side Wire
- 20 Amp Feed-Through Terminals
- Wallplate Included



White	GFTR1-W	GFTR2-W
Ivory	GFTR1-I	GFTR2-I
Lt Almond	GFTR1-T	GFTR2-T
Brown	GFTR1	GFTR2
Gray	GFTR1-GY	GFTR2-GY
Black	GFTR1-E	GFTR2-E
Red	—	GFTR2-R

- Duplex Receptacle
- Power Indication LED
- Weather-Resistant
- Back and Side Wire
- 20 Amp Feed-Through Terminals



White	GFWR1-W*	GFWR2-W*
Black	GFWR1-E*	GFWR2-E*

- Duplex Receptacle
- Power Indication LED
- Weather and Tamper-Resistant
- Back and Side Wire
- 20 Amp Feed-Through Terminals



White	GFWT1-W*	GFWT2-W*
Ivory	GFWT1-I*	GFWT2-I*
Lt Almond	GFWT1-T*	GFWT2-T*
Gray	GFWT1-GY*	GFWT2-GY*
Black	GFWT1-E*	GFWT2-E*

- Duplex Receptacle Guidelight
- Power Indication LED
- Tamper-Resistant
- Back and Side Wire
- 20 Amp Feed-Through Terminals



White	GFNL1-W	GFNL2-W
Ivory	GFNL1-I	GFNL2-I
Lt Almond	GFNL1-T	GFNL2-T
Black	GFNL1-E	—



GFNT2-R



GFWT1-W



GFNL2-T

* No self-grounding clip on device

Protection

smartlockpro® GFCI Receptacles

COMMERCIAL SPECIFICATION GRADE

2-Pole, 3-Wire • 125 Volt

Color



15 Amp



20 Amp

- Duplex Receptacle
- Power Indication LED
- Tamper-Resistant
- Audible Trip Alert
- Back and Side Wire
- 20 Amp Feed-Through

Color	15 Amp	20 Amp
White	GFTA1-W	GFTA2-W
Ivory	GFTA1-I	GFTA2-I
Lt Almond	GFTA1-T	GFTA2-T

DECORA®

- Wallplate Included



- Combination Switch with Single Receptacle
- Power Indication LED
- Tamper-Resistant
- Back and Side Wire
- 20 Amp Feed-Through
- Terminals
- Wallplate Included



Color	15 Amp	20 Amp
White	GFSW1-W	—
Ivory	GFSW1-I	—
Lt Almond	GFSW1-T	—

Dual Function AFCI/GFCI Status Indicator Light



Solid Green LED.

- Load Power ON.
- RESET button is in.
Device is in normal working state.
- Load Power OFF.
- RESET button is out.
Line & load wires are reversed.



Solid or Constant Flashing Red LED.

- Load Power ON.
- RESET button is in.
Press TEST button & RESET button.
If RED indication continues or will not RESET, replace device.
- Load Power OFF.
- RESET button is out.
Device has tripped & self-test function detects a potential problem.
If RED indication continues or will not RESET, replace device.

LED OFF & Flashes Red Twice Every 5 Seconds.

- Load Power OFF.
- RESET button is out.
AFCI trip; press RESET, if device continues to trip, contact an electrician.



LED is OFF.

- Load Power OFF.
RESET button is out.
GFCI trip; press RESET, if device will not reset, there is no power on the circuit.

smartlockpro® Dual Function AFCI/GFCI Receptacles

The SmartlockPro AFCI/GFCI Receptacle offers an effective alternative to a Dual Function breaker and features the convenience of localized test and reset. It provides clear visual indication of status making it intuitive for users to assess various conditions such as power availability and GFCI self-test status. The device also distinguishes between a trip caused by a ground fault and a trip caused by an arc fault.

HOSPITAL GRADE

Heavy-Duty

2-Pole, 3-Wire • 125 Volt

Color



15 Amp



20 Amp

- Duplex Receptacle
- Power Indication LED
- Tamper-Resistant
- Back and Side Wire
- 20 Amp Feed-Through
- Terminals
- Wallplate NOT Included



Color	15 Amp	20 Amp
White	AGTR1-HGW	AGTR2-HGW
Ivory	AGTR1-HGI	AGTR2-HGI
Lt Almond	AGTR1-HGT	AGTR2-HGT
Brown	AGTR1-HG	AGTR2-HG
Gray	AGTR1-HGG	AGTR2-HGG
Black	AGTR1-HGE	AGTR2-HGE
Red	AGTR1-HGR	AGTR2-HGR

COMMERCIAL SPECIFICATION GRADE

2-Pole, 3-Wire • 125 Volt

Color



15 Amp



20 Amp

- Duplex Receptacle
- Power Indication LED
- Tamper-Resistant
- Back and Side Wire
- 20 Amp Feed-Through
- Terminals
- Wallplate Included



Color	15 Amp	20 Amp
White	AGTR1-W	AGTR2-W
Ivory	AGTR1-I	AGTR2-I
Lt Almond	AGTR1-T	AGTR2-T
Brown	AGTR1	AGTR2
Gray	AGTR1-GY	AGTR2-GY
Black	AGTR1-E	AGTR2-E

Surge Protective Receptacles

The value of these receptacles and ease of installation allow for placement anywhere you have a standard electrical outlet. With a small investment, you have the assurance that your equipment is well protected, from a heart monitor in the emergency room, to a computer in the office, or a big screen TV in the living room.

HOSPITAL GRADE Heavy-Duty		NEMA 5-15R 	NEMA 5-20R 
2-Pole, 3-Wire • 125 Volt		15 Amp	20 Amp
<ul style="list-style-type: none"> • Duplex Receptacle • Indicator Light • Back and Side Wire • Wallplate Included 	White	8280-W	8380-W
	Ivory	8280-I	8380-I
	Lt Almond	8280-T	—
	Brown	8280	8380
	Gray	—	8380-GY
	Red	8280-R	8380-R
	Blue	8280-B	8380-B
	Ivory	—	8381-I
<ul style="list-style-type: none"> • Single Receptacle • Indicator Light • Audible Alarm • Back and Side Wire • Wallplate Included  	White	T8280-W	T8380-W
	Ivory	T8280-I	T8380-I
	Lt Almond	T8280-T	—
	Gray	—	T8380-GY
	Red	T8280-R	T8380-R
	Blue	T8280-B	T8380-B
	Ivory	—	8381-IGI
	<ul style="list-style-type: none"> • Duplex Receptacle • Indicator Light • Audible Alarm • Isolated Ground • Back and Side Wire • Wallplate Included   	White	8280-IGW
Ivory		8280-IGI	8380-IGI
Gray		—	8380-IGG
Orange		8280-IGO	8380-IGO
Blue		8280-IGB	8380-IGB



Surge Protective Receptacles

COMMERCIAL SPECIFICATION GRADE



2-Pole, 3-Wire • 125 Volt

Color

15 Amp

20 Amp

DECORA PLUS™	<ul style="list-style-type: none"> Duplex Receptacle Indicator Light Back and Side Wire Wallplate Included 	White	5280-W	5380-W
		Ivory	5280-I	5380-I
		Lt Almond	5280-T	—
		Brown	5280	5380
		Gray	5280-GY	5380-GY
		Red	5280-R	5380-R
		Blue	5280-B	5380-B
	<ul style="list-style-type: none"> Duplex Receptacle Indicator Light Isolated Ground Back and Side Wire Wallplate Included 	White	5280-IGW	5380-IGW
		Ivory	5280-IGI	5380-IGI
		Brown	5280-IG	5380-IG
		Gray	—	5380-IGG
		Orange	5280-IGO	5380-IGO
	<ul style="list-style-type: none"> Duplex Receptacle Indicator Light Audible Alarm Back and Side Wire Wallplate Included 	Blue	5280-IGB	5380-IGB
		White	7280-W	7380-W
		Ivory	7280-I	7380-I
	<ul style="list-style-type: none"> Duplex Receptacle Indicator Light Tamper-Resistant Back and Side Wire Wallplate Included 	Lt Almond	7280-T	—
		Gray	—	7380-GY
		Blue	7280-B	7380-B
		White	T5280-W	T5380-W
		Ivory	T5280-I	T5380-I
<ul style="list-style-type: none"> Duplex Receptacle Indicator Light Audible Alarm Tamper-Resistant Back and Side Wire Wallplate Included 	Lt Almond	T5280-T	T5380-T	
	Brown	T5280	T5380	
	Gray	T5280-GY	T5380-GY	
	Black	T5280-E	T5380-E	
<ul style="list-style-type: none"> Duplex Receptacle Indicator Light Audible Alarm Tamper-Resistant Back and Side Wire Wallplate Included 	Blue	T5280-B	T5380-B	
	White	T7280-W	T7380-W	
	Ivory	T7280-I	T7380-I	
<ul style="list-style-type: none"> Duplex Receptacle Indicator Light Audible Alarm Tamper-Resistant Back and Side Wire Wallplate Included 	Lt Almond	T7280-T	T7380-T	
	Black	T7280-E	—	
Blue	T7280-B	T7380-B		



7380-W



5380-IGI



T5380-W

Marked “Controlled” Receptacles

For use with plug load control systems

The National Electrical Code requires all 15 A & 20 A, 125 V receptacles that are automatically controlled to be marked with a specific symbol  and the word “CONTROLLED” on the receptacle.

- Decora Plus™ and Standard Duplex options
- Conventionally wired and Lev-Lok® modular wiring system platforms available
- Control either one outlet or both outlets
 - For conventionally wired devices with one marked “controlled” receptacle, “hot” tab is split
 - For Lev-Lok devices with one marked “controlled” receptacle, an additional “hot” contact is split internally, and a separate lead is provided for the controlled receptacle

Comply with NEC Article 406.3(E), CA Title 24 & ASHRAE Energy Efficiency Standard 90.1

For examples of recommended energy code compliant solutions for typical commercial applications visit ashrae.leviton.com and title24.leviton.com

INDUSTRIAL SPECIFICATION GRADE Extra Heavy-Duty




2-Pole, 3-Wire • 125 Volt		Color	15 Amp	20 Amp
STANDARD	<ul style="list-style-type: none"> • Duplex Receptacle • Smooth Face • Split-Circuit, One Outlet Marked “Controlled” • Tamper-Resistant • Back and Side Wire 	White	5262-1PW	5362-1PW
		Ivory	5262-1PI	5362-1PI
		Lt Almond	5262-1PT	5362-1PT
		Brown	5262-1P	5362-1P
		Gray	5262-1PG	5362-1PG
		Black	5262-1PE	5362-1PE
		Red	5262-1PR	5362-1PR
		Blue	5262-1PB	5362-1PB
		<ul style="list-style-type: none"> • Duplex Receptacle • Smooth Face • Two Outlets Marked “Controlled” • Tamper-Resistant • Back and Side Wire 	White	5262-2PW
	Ivory		5262-2PI	5362-2PI
	Lt Almond		5262-2PT	5362-2PT
	Brown		5262-2P	5362-2P
	Gray		5262-2PG	5362-2PG
	Black		5262-2PE	5362-2PE
	Red		5262-2PR	5362-2PR
	Green		—	5362-2PN
	Blue		5262-2PB	5362-2PB



5362-1PW

INDUSTRIAL SPECIFICATION GRADE Heavy-Duty



2-Pole, 3-Wire • 125 Volt		Color	15 Amp	20 Amp
STANDARD	<ul style="list-style-type: none"> • Duplex Receptacle • Smooth Face • Two Outlets Marked “Controlled” • Back and Side Wire 	White	5262-S2W	5362-S2W
		Ivory	5262-S2I	5362-S2I
		Lt Almond	5262-S2T	5362-S2T
		Brown	5262-S2	5362-S2
		Gray	5262-S2G	5362-S2G
		Black	5262-S2E	5362-S2E
		Red	5262-S2R	5362-S2R
		Green	—	5362-S2N
		Blue	5262-S2B	5362-S2B



5362-S2G

Marked "Controlled" Receptacles

INDUSTRIAL SPECIFICATION GRADE

Heavy-Duty



2-Pole, 3-Wire • 125 Volt

Color

15 Amp

20 Amp

STANDARD

- Duplex Receptacle
- Smooth Face
- Split-Circuit, One Outlet Marked "Controlled"
- Back and Side Wire



White	5262-S1W	5362-S1W
Ivory	5262-S1I	5362-S1I
Lt Almond	5262-S1T	5362-S1T
Brown	5262-S1	5362-S1
Gray	5262-S1G	5362-S1G
Black	5262-S1E	5362-S1E
Red	5262-S1R	5362-S1R
Green	—	5362-S1N
Blue	5262-S1B	5362-S1B



TDR20-S2W

- Duplex Receptacle
- Smooth Face
- Two Outlets Marked "Controlled"
- Back and Side Wire



White	16252-2PW	16352-2PW
Ivory	16252-2PI	16352-2PI
Lt Almond	16252-2PT	16352-2PT
Brown	16252-2P	16352-2P
Gray	16252-2PG	16352-2PG
Black	16252-2PE	16352-2PE
Red	16252-2PR	16352-2PR
Blue	16252-2PB	16352-2PB



16352-1PI

DECORA PLUS™

- Duplex Receptacle
- Smooth Face
- Two Outlets Marked "Controlled"
- Tamper-Resistant
- Back and Side Wire



White	TDR15-S2W	TDR20-S2W
Ivory	TDR15-S2I	TDR20-S2I
Lt Almond	TDR15-S2T	TDR20-S2T
Brown	TDR15-S2	TDR20-S2
Gray	TDR15-S2G	TDR20-S2G
Black	TDR15-S2E	TDR20-S2E

- Duplex Receptacle
- Smooth Face
- Split-Circuit, One Outlet Marked "Controlled"
- Back and Side Wire



White	16252-1PW	16352-1PW
Ivory	16252-1PI	16352-1PI
Lt Almond	16252-1PT	16352-1PT
Brown	16252-1P	16352-1P
Gray	16252-1PG	16352-1PG
Black	16252-1PE	16352-1PE
Red	16252-1PR	16352-1PR
Blue	16252-1PB	16352-1PB



G5362-2TN

- Duplex Receptacle
- Smooth Face
- Split-Circuit, One Outlet Marked "Controlled"
- Tamper-Resistant
- Back and Side Wire



White	TDR15-S1W	TDR20-S1W
Ivory	TDR15-S1I	TDR20-S1I
Lt Almond	TDR15-S1T	TDR20-S1T
Brown	TDR15-S1	TDR20-S1
Gray	TDR15-S1G	TDR20-S1G
Black	TDR15-S1E	TDR20-S1E





SMARTLOCKPRO® GFCI

- Duplex Receptacle
- Power Indication LED
- Tamper-Resistant
- Two Outlets Marked "Controlled"
- Back and Side Wire
- 20 Amp Feed-Through Terminals



White	—	G5362-2TW
Ivory	—	G5362-2TI
Lt Almond	—	G5362-2TT
Brown	—	G5362-2T0
Gray	—	G5362-2TG
Black	—	G5362-2TE
Red	—	G5362-2TR
Green	—	G5362-2TN

Marked "Controlled" Receptacles

COMMERCIAL SPECIFICATION GRADE		NEMA 5-15R 	NEMA 5-20R 	
2-Pole, 3-Wire • 125 Volt		15 Amp	20 Amp	
STANDARD	<ul style="list-style-type: none"> Duplex Receptacle Smooth Face Two Outlets Marked "Controlled" Side Wire Only 	White CR015-2PW Ivory CR015-2PI Lt Almond CR015-2PT	CR020-2PW CR020-2PI CR020-2PT	
	<ul style="list-style-type: none"> Duplex Receptacle Smooth Face Two Outlets Marked "Controlled" Tamper-Resistant Back and Side Wire  	White TBR15-S2W Ivory TBR15-S2I Lt Almond TBR15-S2T Brown TBR15-S2 Gray TBR15-S2G Black TBR15-S2E	TBR20-S2W TBR20-S2I TBR20-S2T TBR20-S2 TBR20-S2G TBR20-S2E	
	<ul style="list-style-type: none"> Duplex Receptacle Smooth Face Split-Circuit, One Outlet Marked "Controlled" Side Wire Only 	White CR015-1PW Ivory CR015-1PI Lt Almond CR015-1PT	CR020-1PW CR020-1PI CR020-1PT	
	<ul style="list-style-type: none"> Duplex Receptacle Smooth Face Split-Circuit, One Outlet Marked "Controlled" Tamper-Resistant Back and Side Wire  	White TBR15-S1W Ivory TBR15-S1I Lt Almond TBR15-S1T Brown TBR15-S1 Gray TBR15-S1G Black TBR15-S1E	TBR20-S1W TBR20-S1I TBR20-S1T TBR20-S1 TBR20-S1G TBR20-S1E	
	DECORA PLUS™	<ul style="list-style-type: none"> Duplex Receptacle Smooth Face Two Outlets Marked "Controlled" One Type A and one Type C USB Port Tamper-Resistant Back and Side Wire   	White T5633-2BW Ivory T5633-2I Brown T5633-2B Gray T5633-2G Black T5633-2E Green T5633-2GN Blue T5633-2BU	T5833-2BW T5833-2I T5833-2B T5833-2G T5833-2E T5833-2GN T5833-2BU



CR020-2PW



TBR20-S1G



T5833-2W


For Lev-lok Marked "Controlled" devices, please refer to Lev-lok section on page 16.

4-in-1™ Receptacles

Hospital Grade 4-in-1™ Receptacles provide a simple transition in retrofit applications to comply with new receptacle requirements in health care facilities. These devices allow you to increase the number of receptacles in your facility without having to pull new wires.



21254-HI (Front)



21254-HI (Back)



21254-W (Front)

HOSPITAL GRADE

Heavy-Duty



2-Pole, 3-Wire • 125 Volt

- Quadruplex Receptacle
- Side Wire Only

Color

15 Amp

20 Amp

White	1254-HW	21254-HW
Ivory	1254-HI	21254-HI
Brown	1254-H	21254-H
Gray	—	21254-HGY
Red	1254-HR	21254-HR

- Quadruplex Receptacle
- Isolated Ground
- Side Wire Only



White	—	21254-IGW
Ivory	—	21254-IGI
Orange	1254-IG	21254-IG

- Quadruplex Receptacle
- Surge Protective
- Indicator Light
- Side Wire Only

White	8480-W	8490-W
Ivory	8480-I	8490-I
Red	8480-R	8490-R

- Quadruplex Receptacle
- Surge Protective
- Isolated Ground
- Indicator Light
- Side Wire Only



White	8480-IGW	—
Ivory	8480-IGI	8490-IGI
Orange	—	8490-IG
Blue	8480-IGB	8490-IGB

INDUSTRIAL SPECIFICATION GRADE

Heavy-Duty



2-Pole, 3-Wire • 125 Volt

- Quadruplex Receptacle
- Side Wire Only

Color

15 Amp

20 Amp

White	1254-W	21254-W
Ivory	1254-I	21254-I
Brown	1254	21254
Gray	1254-GY	21254-GY
Black	1254-E	21254-E
Red	1254-R	21254-R
Yellow	—	21254-Y

- Quadruplex Receptacle
- Surge Protective
- Indicator Light
- Side Wire Only


















White	5480-W	5490-W
Ivory	5480-I	5490-I
Gray	5480-GY	5490-GY
Red	5480-R	—
Blue	5480-BU	5490-BU

- Quadruplex Receptacle
- Surge Protective
- Isolated Ground
- Indicator Light
- Side Wire Only



Ivory	—	5490-IGI
Orange	5480-IG	5490-IG
Blue	—	5490-IGB

USB Receptacles

HOSPITAL GRADE Heavy-Duty		NEMA 5-15R 	NEMA 5-20R 	
2-Pole, 3-Wire • 125 Volt		15 Amp	20 Amp	
DECORA PLUS™	<ul style="list-style-type: none"> Duplex Receptacle Two Type A USB Ports (3.6 Amp) Smooth Face Tamper-Resistant Back and Side Wire  	White	T5632-HGW	T5832-HGW
		Ivory	T5632-HGI	T5832-HGI
		Lt Almond	T5632-HGT	T5832-HGT
		Brown	T5632-HG	T5832-HG
		Gray	T5632-HGG	T5832-HGG
		Black	T5632-HGE	T5832-HGE
		Red	T5632-HGR	T5832-HGR
	<ul style="list-style-type: none"> Duplex Receptacle One Type A & One Type C USB Port (5.1 Amp) Smooth Face Tamper-Resistant Back and Side Wire  	White	T5633-HGW	T5833-HGW
		Ivory	T5633-HGI	T5833-HGI
		Lt Almond	T5633-HGT	T5833-HGT
	Brown	T5633-HG	T5833-HG	
	Gray	T5633-HGG	T5833-HGG	
	Black	T5633-HGE	T5833-HGE	
	Red	T5633-HGR	T5833-HGR	
COMMERCIAL SPECIFICATION GRADE		NEMA 5-15R 	NEMA 5-20R 	
2-Pole, 3-Wire • 125 Volt		15 Amp	20 Amp	
DECORA®	<ul style="list-style-type: none"> Duplex Receptacle Power Indication LED Two Type A USB Ports (3.6 Amp) SmartlockPro® GFCI Tamper-Resistant Wire Leads   	White	GUSB1-W	GUSB2-W
	<ul style="list-style-type: none"> Duplex Receptacle Two Type C USB Ports (6 Amp, 30W) Smooth Face Tamper-Resistant Back and Side Wire  	White	T5635-W	T5835-W
		Ivory	T5635-I	T5835-I
		Lt Almond	T5635-T	T5835-T
		Brown	—	T5835-B
		Gray	T5635-G	T5835-G
		Black	T5635-E	T5835-E
	<ul style="list-style-type: none"> Duplex Receptacle Two Type C USB Ports (6 Amp, 60W) Smooth Face Tamper-Resistant Wire Leads  	White	T5636-W	T5836-W
	<ul style="list-style-type: none"> Duplex Receptacle One Type A & One Type C USB Port (5.1 Amp) Smooth Face Tamper-Resistant Back and Side Wire  	White	T5633-W	T5833-W
		Ivory	T5633-I	T5833-I
	Lt Almond	T5633-T	T5833-T	
	Brown	T5633	T5833	
	Gray	T5633-GY	T5833-GY	
	Black	T5633-E	T5833-E	



USB Receptacles

COMMERCIAL SPECIFICATION GRADE		NEMA 5-15R	NEMA 5-20R
2-Pole, 3-Wire • 125 Volt	Color	15 Amp	20 Amp
<ul style="list-style-type: none"> • Duplex Receptacle • Two Type A USB Ports (3.6 Amp) • Smooth Face • Tamper-Resistant • Back and Side Wire 	White	T5632-W	
	Ivory	T5632-I	T5832-I
	Lt Almond	T5632-T	T5832-T
	Brown	T5632	T5832
	Gray	T5632-GY	T5832-GY
	Black	T5632-E	T5832-E
	Red	T5632-R	T5832-R



Combination Straight & Locking Blade Receptacles

INDUSTRIAL SPECIFICATION GRADE Heavy-Duty		NEMA 5-15R	NEMA L5-15R	
2-Pole, 3-Wire • 125 Volt	Feed	Color	15 Amp	
COMBO	• Duplex Receptacle	Common Feed	Black	4792
	• Smooth Face	2 Hot, 1 Neutral Return	Black	4794-1R
	• Back and Side Wire	2 Hot, 2 Neutral Returns	Black	4795-2R







Clock Hanger & Display Receptacles

COMMERCIAL SPECIFICATION GRADE		NEMA 5-15R	NEMA 5-20R	
2-Pole, 3-Wire • 125 Volt	Color	15 Amp	20 Amp	
CLOCK-HANGER	<ul style="list-style-type: none"> • Recessed Single Receptacle with Hook on Wallplate • Smooth Face • Tamper-Resistant • Back and Side Wire 	White	T5015-CHW	T5020-CHW
		Ivory	T5015-CHI	T5020-CHI
	<ul style="list-style-type: none"> • Recessed Single Receptacle with Wallplate Featuring Removable Receptacle Cover • Smooth Face • Tamper-Resistant • Back and Side Wire 	Stainless Steel	T5261-CH	T5361-CH
		Brass	T5250-B	T5350-B






Short Strap Receptacles

COMMERCIAL SPECIFICATION GRADE			NEMA 5-15R 	NEMA 5-20R 
2-Pole, 3-Wire • 125 Volt		Color	15 Amp	20 Amp
SHORT STRAP	<ul style="list-style-type: none"> • Single Receptacle • Smooth Face • Side Wire Only 	Black	—	5558-SS
	<ul style="list-style-type: none"> • Single Receptacle • Tapped Mounting Holes • Smooth Face • Side Wire Only 	Black	5258-SS	—
4" CVR.	<ul style="list-style-type: none"> • Mounted to Round 4" Cover • Smooth Face • Side Wire Only 	Black	5059 (Single)	—
		Black	5042 (Duplex)	—







5558-SS

COMMERCIAL SPECIFICATION GRADE			NEMA 6-15R 	NEMA 6-20R 
2-Pole, 3-Wire • 250 Volt		Color	15 Amp	20 Amp
SH. STRAP	<ul style="list-style-type: none"> • Single Receptacle • Smooth Face • Side Wire Only 	Black	5658-SS	5458-SS



5825-W

Universal (Europlug)

COMMERCIAL SPECIFICATION GRADE			NEMA 5-15R 	CEE 7/16 	NEMA 5-15R 	CEE 7/16 
2-Pole, 3-Wire • 125/250 Volt		Color	15 Amp	16 Amp		
DECORA PLUS™	• Straight Blade and Europlug Duplex Receptacle	White	5825-W	5835-W		
	• Smooth Face	Ivory	5825-I	5835-I		
	• Back and Side Wire	Lt Almond	5825-T	5835-T		
		Black	5825-E	5835-E		

SOLUTIONS FOR...



Health Care



Food & Beverage



Education



Temporary Power



Oil & Gas



Manufacturing



Entertainment



Commercial Properties



Office Buildings

...AND MUCH MORE!

Visit our Website at:
leviton.com/receptaclegrades
email: commercial@leviton.com

Q-1101G

082223

Leviton Manufacturing Co., Inc.

201 N Service Rd, Melville, NY 11747
Telephone: 1-800-323-8920 • FAX: 1-800-832-9538
Tech Line: 1-800-824-3005 (M-F 8AM-10PM; Sat 9AM-7PM; Sun 9AM-5PM)

© 2023 Leviton Manufacturing Co., Inc. All rights reserved.
NEC® is a registered trademark of the National Fire Protection Association, Quincy, MA 02169

