



Lev-lok[®] Modular Wiring Devices

Competitive Cross Reference



HOSPITAL GRADE RECEPTACLES						
Description/Features		Amp	Leviton	Hubbell	Legrand/P&S	Cooper (Arrow Hart)
STANDARD	Extra Heavy-Duty	15	M8200	SNAP8200A	PT8200	AH8200M
		20	M8300	SNAP8300A	PT8300	AH8300M
	Extra Heavy-Duty, Tamper-Resistant	15	M8200-SG	SNAP8200TR	PTTR8200	TR8200M
		20	M8300-SG	SNAP8300TR	PTTR8300	TR8300M
	Extra Heavy-Duty, MRI	15	MRI15	N/A	N/A	N/A
		20	MRI20	N/A	N/A	N/A
	Heavy-Duty	15	M8200-H	N/A	PT8200H	8200M
		20	M8300-H	N/A	PT8300H	8300M
	Heavy-Duty, Tamper-Resistant	15	MT820	N/A	PTTR8200	N/A
		20	MT830	N/A	PTTR8300	N/A
	Extra Heavy-Duty, Illuminated	15	M8200-IL	N/A	PT8200IL	8200LT_M
		20	M8300-IL	N/A	PT8300IL	8300LT_M
	Extra Heavy-Duty, Illuminated, Tamper-Resistant	15	MT820-IL	N/A	N/A	N/A
		20	MT830-IL	N/A	N/A	N/A
	Extra Heavy-Duty, Power Indication	15	M8200-PL	SNAP8200L	PT8200PI	N/A
		20	M8300-PL	SNAP8300L	PT8300PI	N/A
	Heavy-Duty, Isolated Ground	15	M8200-IG	N/A	PTIG8200	IG8200_M
		20	M8300-IG	N/A	PTIG8300	IG8300_M
	Heavy-Duty, Isolated Ground, Tamper-Resistant	15	MT820-IG	SNAP8200IGTR	N/A	N/A
		20	MT830-IG	SNAP8300IGTR	N/A	N/A
DECORA PLUS	Extra Heavy-Duty	15	M1626-HG	SNAP2172A	PT26262HG	8262M
		20	M1636-HG	SNAP2182A	PT26362HG	8362M
	Extra Heavy-Duty, Tamper-Resistant	15	MT162-HG	SNAP2172TR	PTTR26262HG	N/A
		20	MT163-HG	SNAP2182TR	PTTR26362HG	N/A
	Extra Heavy-Duty, Illuminated	15	M1626-IL	N/A	N/A	8262LT_M
		20	M1636-IL	N/A	N/A	8362LT_M
	Extra Heavy-Duty, Illuminated, Tamper-Resistant	15	MT162-IL	N/A	N/A	N/A
		20	MT163-IL	N/A	N/A	N/A
	Extra Heavy-Duty, Power Indication	15	M1626-PL	SNAP2172L	N/A	N/A
		20	M1636-PL	SNAP2182L	N/A	N/A
	Heavy-Duty, Isolated Ground	15	MD820-IG	N/A	N/A	IG8262_M
		20	MD830-IG	N/A	N/A	IG8362_M
Heavy-Duty, Isolated Ground, Tamper-Resistant	15	MDT82-IG	SNAP2172IGTR	N/A	N/A	
	20	MDT83-IG	SNAP2182IGTR	N/A	N/A	

Lev-lok® Competitive Cross Reference

INDUSTRIAL SPECIFICATION GRADE RECEPTACLES

Description/Features		Amp	Leviton	Hubbell	Legrand/P&S	Cooper (Arrow Hart)	
STANDARD	Spec Grade, Extra Heavy-Duty	15	M5262	SNAP5262A	PT5262A	AH5262M	
		20	M5362	SNAP5362A	PT5362A	AH5362M	
	Spec Grade, Extra Heavy-Duty, Tamper-Resistant	15	M5262-SG	SNAP5262TR	PTTR5262	N/A	
		20	M5362-SG	SNAP5362TR	PTTR5362	N/A	
	Spec Grade, Heavy-Duty	15	M5262-S	N/A	PT5262	5262M	
		20	M5362-S	N/A	PT5362	5362M	
	Spec Grade, Heavy-Duty, Tamper-Resistant	15	MT562-S	N/A	N/A	TR5262M	
		20	MT563-S	N/A	N/A	TR5362M	
	Spec Grade, Heavy-Duty, Split Circuit	15	M5262-SC	N/A	PT5262SC	N/A	
		20	M5362-SC	N/A	PT5362SC	N/A	
	Spec Grade, Heavy-Duty, Split Circuit, Tamper-Resistant	15	MT562-SC	N/A	PTTR5262SC	N/A	
		20	MT563-SC	N/A	PTTR5362SC	N/A	
	Spec Grade, Heavy-Duty, Isolated Ground	15	M5262-IG	N/A	PTIG5262	IG5262_M	
		20	M5362-IG	N/A	PTIG5362	IG5362_M	
	Spec Grade, Heavy-Duty, Isolated Ground, Tamper-Resistant	15	MT562-IG	SNAP5262IGTR	N/A	N/A	
		20	MT563-IG	SNAP5362IGTR	N/A	N/A	
	Spec Grade, Heavy-Duty, 1 Recept. Perm. Marked Controlled	15	M5262-1C	N/A	PT5262SCCH	N/A	
		20	M5362-1C	N/A	PT5362SCCH	N/A	
	Spec Grade, Heavy-Duty, 1 Recept. Perm. Marked Controlled, TR	15	MT562-1C	N/A	PTTR5262SCCH	N/A	
		20	MT563-1C	N/A	PTTR5362SCCH	N/A	
	Spec Grade, Heavy-Duty, 2 Recept. Perm. Marked Controlled	15	M5262-2S	N/A	PT5262CD	N/A	
		20	M5362-2S	N/A	PT5362CD	N/A	
	Spec Grade, Heavy-Duty, 2 Recept. Perm. Marked Controlled, TR	15	MT562-2S	N/A	PTTR5262CD	N/A	
		20	MT563-2S	N/A	PTTR5362CD	N/A	
	DECORA PLUS	Spec Grade, Heavy-Duty	15	M1626	SNAP2152A	PT26252	6262M
			20	M1636	SNAP2162A	PT26352	6362M
		Spec Grade, Heavy-Duty, Tamper-Resistant	15	MT162	SNAP2152TR	PTTR26262	N/A
			20	MT163	SNAP2162TR	PTTR26362	N/A
Spec Grade, Heavy-Duty, Split Circuit		15	M1626-SC	N/A	PT26262SC	N/A	
		20	M1636-SC	N/A	PT26362SC	N/A	
Spec Grade, Heavy-Duty, Split Circuit, Tamper-Resistant		15	MT162-SC	N/A	PTTR26262SC	N/A	
		20	MT163-SC	N/A	PTTR26362SC	N/A	
Spec Grade, Heavy-Duty, Isolated Ground		15	M1626-IG	N/A	PTIG26262	N/A	
		20	M1636-IG	N/A	PTIG26362	N/A	
Spec Grade, Heavy-Duty, Isolated Ground, Tamper-Resistant		15	MT162-IG	SNAP2152IGTR	N/A	N/A	
		20	MT163-IG	SNAP2162IGTR	N/A	N/A	
Spec Grade, Heavy-Duty, 1 Recept. Perm. Marked Controlled		15	M1626-1C	N/A	PT26252SCCT	N/A	
		20	M1636-1C	N/A	PT26352SCCT	N/A	
Spec Grade, Heavy-Duty, 1 Recept. Perm. Marked Controlled, TR		15	MT162-1C	N/A	PTTR26252SCCT	N/A	
		20	MT163-1C	N/A	PTTR26352SCCT	N/A	
Spec Grade, Heavy-Duty, 2 Recept. Perm. Marked Controlled		15	M1626-2S	N/A	PT26252CD	N/A	
		20	M1636-2S	N/A	PT26352CD	N/A	
Spec Grade, Heavy-Duty, 2 Recept. Perm. Marked Controlled, TR		15	MT162-2	N/A	PTTR26252CD	N/A	
		20	MT163-2	N/A	PTTR26352CD	N/A	

Lev-lok® Competitive Cross Reference

GFCI, USB AND SURGE RECEPTACLES						
Description/Features		Amp	Leviton	Hubbell	Legrand/P&S	Cooper (Arrow Hart)
GFCIs	Spec Grade, Extra Heavy-Duty	15	MGFN1	GFRST15SNAP	PT1597	SGFH15MOD
		20	MGFN2	GFRST20SNAP	PT2097	SGFH20MOD
	Spec Grade, Extra Heavy-Duty, Tamper-Resistant	15	MGFT1	GFTWRST15SNAP	PT1597TR	TRSGFH15MOD
		20	MGFT2	GFTWRST20SNAP	PT2097TR	TRSGFH20MOD
	Hospital Grade, Extra Heavy-Duty	15	MGFN1-HG	GFRST82SNAP	PT1597HG	SGFH15MOD
		20	MGFN2-HG	GFRST83SNAP	PT2097HG	SGFH20MOD
	Hospital Grade, Extra Heavy-Duty, Tamper-Resistant	15	MGFT1-HG	GFTWRST82SNAP	PT1597HGTR	TRSGFH15MOD
		20	MGFT2-HG	GFTWRST83SNAP	PT2097HGTR	TRSGFH20MOD
DUPLX WITH USB	Spec Grade, Heavy-Duty, Tamper-Resistant, USB Type A/A	15	M56AA	SNAP15USB	N/A	N/A
		20	M58AA	SNAP20USB	N/A	N/A
	Spec Grade, Heavy-Duty, Tamper-Resistant, USB Type A/C	15	M56AC	SNAP15UAC	PTTR15ACUSB	N/A
		20	M58AC	SNAP20UAC	PTTR20ACUSB	N/A
	Hospital Grade, Heavy-Duty, Tamper-Resistant, USB Type A/A	15	M56AA-HG	SNAP8200USB	N/A	N/A
		20	M58AA-HG	SNAP8300USB	N/A	N/A
	Hospital Grade, Heavy-Duty, Tamper-Resistant, USB Type A/C	15	M56AC-HG	N/A	PTTR15HACUSB	N/A
		20	M58AC-HG	N/A	PTTR20HACUSB	N/A
SURGE	Spec Grade, Heavy-Duty, Tamper-Resistant	15	MT528	SNAP5262S	PTTR5262SP	N/A
		20	MT538	SNAP5362S	PTTR5362SP	N/A
	Spec Grade, Heavy-Duty, Tamper-Resistant, Audible Alarm	15	MT728	N/A	N/A	N/A
		20	MT738	N/A	N/A	N/A
	Hospital Grade, Heavy-Duty, Tamper-Resistant, Audible Alarm	15	MT828	N/A	N/A	N/A
		20	MT838	N/A	N/A	N/A

RECEPTACLE TESTER & MODULES						
Description/Features		Color	Leviton	Hubbell	Legrand/P&S	Cooper (Arrow Hart)
MODULES	Receptacle Tester	—	LVLOK-TST	SNAPCTG	PTTESTER	ALTESTER
	Stranded Wire Leads	White	MSTWL-A	SNAP2RA	PTRA6STR	MCR125STR
	Solid Wire Leads	White	MSTWL-SDA	SNAP1RA	PTRA6SOL	MCR125SOL
	Stranded Wire Leads	Red	MSTWL-R	N/A	N/A	N/A
	Stranded Wire Leads w/4-Port Push-Wire Connectors	White	MSTWL-WST	N/A	PTRA6STRBP	N/A
	Solid Wire Leads w/4-Port Push-Wire Connectors	White	MSTWL-WSD	N/A	PTRA6SOLBP	N/A
	Stranded Wire Leads	Orange	MSTWL-IG	N/A	N/A	N/A
	Solid Wire Leads	Orange	MSTWL-SIG	N/A	N/A	N/A
	Stranded Wire Leads w/4-Port Push-Wire Connectors	Orange	MSTWL-WIG	N/A	N/A	N/A
	Stranded Wire Leads for Low Leakage Circuits	White	MSTWL-XA	N/A	N/A	N/A
	Stranded Wire Leads for Low Leakage Circuits	White	MSTWL-XI	N/A	N/A	N/A
	Stranded Wire Leads for Low Leakage Circuits	White	MSTWL-XN	N/A	N/A	N/A

Lev-lok® Competitive Cross Reference

SWITCHES & OCCUPANCY SENSORS

Description		Leviton	Hubbell	Legrand/P&S	Cooper (Arrow Hart)	
TOGGLES	Extra Heavy-Duty, Single Pole	15 A	M1201	SNAP1201BRNA	PT15AC1	AH1201BM
		20 A	M1221	SNAP1201BRNA	PT20AC1	AH1221BM
	Extra Heavy-Duty, Single Pole, Illuminated	15 A	M1201-LH	SNAP1201ILBKNA	PT15AC1SL	AH1201LT__M
		20 A	M1221-LH	SNAO1221ILBKNA	PT20AC1SL	AH1221LT__M
	Extra Heavy-Duty, Single Pole, Tamper-Resistant	15 A	M1201-L	N/A	N/A	N/A
		20 A	M1221-L	N/A	N/A	N/A
	Extra Heavy-Duty, Single Pole, Antimicrobial Treated	20 A	AM120	N/A	N/A	N/A
	Extra Heavy-Duty, 3-way	15 A	M1203	SNAP1206BRNA	PT15AC3	N/A
		20 A	M1223	SNAP1223BRNA	PT20AC3	N/A
	Extra Heavy-Duty, 3-way, Illuminated	15 A	M1203-LH	N/A	PT15AC3SL	N/A
		20 A	M1223-LH	N/A	PT20AC3SL	N/A
	Extra Heavy-Duty, 3-way, Tamper-Resistant	15 A	M1203-L	N/A	N/A	N/A
20 A		M1223-L	N/A	N/A	N/A	
Extra Heavy-Duty, 3-way, Antimicrobial Treated	20 A	AM320	N/A	N/A	N/A	
DECORA PLUS	Extra Heavy-Duty, Single Pole	15 A	M5691	SNAP2101BRNA	PT2601	7601BM
		20 A	M5621	SNAP2121BRNA	PT2621	7621BM
	Extra Heavy-Duty, Single Pole, Illuminated	20 A	M5631	SNAP2101ILBKNA	PT2625	7631__M
	Extra Heavy-Duty, 3-way	15 A	M5693	SNAP2103BRNA	PT2603	N/A
		20 A	M5623	SNAP2123BRNA	PT2623	N/A
Extra Heavy-Duty, 3-way, Illuminated	20 A	M5633	SNAP2103ILBKNA	PT2626	N/A	
OCC	Passive Infrared (PIR)		MDS10-ID	N/A	PTWSP250	N/A
	Passive Infrared (PIR) w/Self-Adaptive Technology		MDS15-ID	N/A	N/A	N/A
	Multi-Technology (PIR/Ultrasonic)		MSSMT-GD	N/A	N/A	N/A

MODULES FOR SWITCHES & OCC SENSORS

Description		Color	Leviton	Hubbell	Legrand/P&S	Cooper (Arrow Hart)
SINGLE POLE	Stranded Wire Leads	Yellow	MSPSW-ST	SNAPSP2NA	PTS6STR3	MCS120STR
	Stranded Wire Leads with Push Wire Connectors	Yellow	MSPSW-WST	SNAPSP2NAM2	PTS6STR3BP	N/A
	Solid Wire Leads	Yellow	MSPSW-SD	SNAPSP1NA	PTS6SOL3	MCS120SOL
	Stranded Wire Leads	Yellow	MSPSW-7ST	N/A	N/A	N/A
	Solid Wire Leads	Yellow	MSPSW-7SD	N/A	N/A	N/A
3-WAY	Stranded Wire Leads	Yellow	M3WSW-ST	SNAP3W2NA	PTS6STR4	N/A
	Stranded Wire Leads with Push Wire Connectors	Yellow	M3WSW-WST	SNAP3W2NAM2	N/A	N/A
	Stranded Wire Leads for 277 V Lighting Applications	Yellow	M3WSW-7ST	N/A	PTS6STR4277	N/A
	Solid Wire Leads	Yellow	M3WSW-SD	SNAP3W1NA	PTS6SOL4	N/A
OCC	Stranded Wire Leads	Yellow	MSPSW-XST	N/A	PTS6STR3	N/A
	Solid Wire Leads	Yellow	MSPSW-XSD	N/A	PTS6SOL3	N/A

Visit our Website at: leviton.com/levlok
 email: commercial@leviton.com

© 2019 Leviton Manufacturing Co., Inc. All rights reserved.
 Q-1185 071019

Leviton Manufacturing Co., Inc.
 201 N Service Rd, Melville, NY 11747
 Telephone: 1-800-323-8920 • FAX: 1-800-832-9538
 Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): 1-800-824-3005

