110-Style Voice-Grade Patch Panels

APPLICATION

Leviton 110-Style Voice-Grade Patch Panels are specifically designed for voice applications. Panels can be configured for one- or two-pair-per-port wiring schemes. Included is a rear label which delineates between the two wiring schemes and shows 25-pair, color-coded termination.

SPECIFICATION

Voice-Grade Patch Panels shall meet ANSI/TIA/-568-C standards compliance, ANSI/TIA-1096-A requirements, and be UL listed. The printed circuit board shall be rated UL94V-0. Panels shall be configured for 24 or 48 ports, mount on a standard 19-inch equipment rack, and accommodate top, bottom, and side cable entry. Patch panels shall be made of 16-gauge steel, with a black coat.

FEATURES

- 110-style connector for quick and easy punch-down. The connector has a separation mark between rack mounts
- Includes two threaded standoffs for attaching a Cable Management Bar
- Includes .6-inch wide 8P RJ45 jacks
- Color-coded 25-pair wiring information card

DESIGN CONSIDERATIONS

- Connector modules are built in groups of six
- Mounts on 19-inch wide equipment rack, or hinged wall-mount bracket

STANDARDS COMPLIANCE

ANSI/TIA-568-C
ANSI/TIA-1096-A (formerly FCC Part 68)
cULus Listed

PHYSICAL SPECIFICATIONS

Dimensions:	See page two
Materials:	16-gauge steel, black coat. Plastic components are rated UL 94V-0

COUNTRY OF ORIGIN

USA

WARRANTY INFORMATION

For a copy of Leviton product warranties, visit www.leviton.com/warranty.

Leviton Network Solutions
2222 - 222nd St. SE
Bothell, WA 98021-4416

tel 1-800-824-3005
tel +1-425-486-2222
appeng@leviton.com
www.leviton.com

Asia / Pacific
T +1.631.812.6228
E infoasean@leviton.com

Canada
T +1.514.954.1840
E pcservice@leviton.com

Caribbean
T +1.954.593.1896
E infocaribbean@leviton.com

China
T +852.2774.9876
E infochina@leviton.com

Colombia
T +57.1.743.6045
E infocolombia@leviton.com

Europe
T +33.6.8869.1380
E infoeurope@leviton.com

India / SAARC
T +971.4.886.4722
E infoindia@leviton.com

Mexico
T +52.55.5082.1040
E lsamarketing@leviton.com

Middle East & Africa
T +971.4.886.4722
E lmeinfo@leviton.com

South Korea
T +82.2.3273.9963
E infokorea@leviton.com

Copyright © 2015 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.

Revised January 2015

ELECTRONIC FILES

For CAD files, typical specs, or technical drawings (.DXF, .DWG), visit www.leviton.com.



PART NUMBERS

Description	Part No.
110-Style Voice-Grade Patch Panel, 24 ports	49013-P24
110-Style Voice-Grade Patch Panel, 48 ports	49013-P48

A15 5302

Leviton Network Solutions
2222 - 222nd St. SE
Bothell, WA 98021-4416

tel 1-800-824-3005
tel +1-425-486-2222
appeng@leviton.com
www.leviton.com

Asia / Pacific
T +1.631.812.6228
E infoasean@leviton.com

Canada
T +1.514.954.1840
E pcservice@leviton.com

Caribbean
T +1.954.593.1896
E infocaribbean@leviton.com

China
T +852.2774.9876
E infochina@leviton.com

Colombia
T +57.1.743.6045
E infocolombia@leviton.com

Europe
T +33.6.8869.1380
E infoeurope@leviton.com

India / SAARC
T +971.4.886.4722
E infoindia@leviton.com

Mexico
T +52.55.5082.1040
E lsamarketing@leviton.com

Middle East & Africa
T +971.4.886.4722
E lmeinfo@leviton.com

South Korea
T +82.2.3273.9963
E infokorea@leviton.com

Copyright © 2015 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.

Revised January 2015