

Wireless Companion Switch and Dimmer



SBK00-CSW



SBK00-CDW

Description

The Wireless Companion Switch and Dimmer pairs wirelessly with the Smart Ceiling Mount Room Controller (SRC) and Smart Ceiling Mount Sensor (CMS) to provide a simple to install solution for wireless manual lighting control. The Wireless Companion Switch and Dimmer can be mounted directly on wall surfaces or at an existing single or multi-gang wallbox, no wiring required. The Wireless Companion Switch and Dimmer are the perfect solution for locations where a wallbox may not be located or locations where there is no wiring present.

Applications


The Wireless Companion Switch and Dimmer work in conjunction with the SRC and CMS which offer occupancy/vacancy sensing, dimming (SRC only), and daylight harvesting capabilities.

- The SBK00-CSW is a rocker switch that provides ON/OFF control
- The SBK00-CDW is a rocker dimmer that provides ON/OFF control with a dimming bar for dimming control

Features


- Provides wireless switching or dimming control for Smart Ceiling Mount Room Controllers and Smart Ceiling Mount Sensors
- Place in any location near SRC or CMS
- 50 ft wireless RF range
- Mounts directly to wall surface or installs at existing wallbox (single and multi-gang) or where wiring may not be present
- Easy to pair to SRC and CMS using Leviton's Smart Sensor App
- Multiple control options including primary load, secondary load (if applicable), and 3-way (if applicable)
- Use with standard Decora wallplates (single and multi-gang)
- Replaceable CR2025 batteries, with estimated 5-year battery life
- Easy battery replacement - no need to remove the device from the wall or wallbox
- Designer styling complements any interior for sleek aesthetics

Installation



NOTE: These devices do not connect directly to the load or lights. Control of the load or lights is through the Leviton Smart Ceiling Mount Room Controller or Sensor, which are line voltage devices (sold separately).

Application



Specifications

Electrical

Batteries CR2025 x2, 3 V

Wireless

Network 2.4GHz

Range 50 ft

Environmental

Operating Temperature 32°F - 104°F (0°C - 40°C)

Storage Temperature 14°F - 185°F (-10°C - 85°C)

Relative Humidity 0-90% non-condensing

Physical

Color White

Other

IP Rating IP20

Listing UL 1472, CSA C22.2 No. 184.1-15, FCC Part 15, Class B

Warranty Limited 5-Year Warranty

Ordering Information

Wireless Companion Switch and Dimmer

Cat. No.	Description
SBK00-CSW	Wireless Companion Switch, Battery powered, White
SBK00-CDW	Wireless Companion Dimmer, Battery powered, White

Leviton Manufacturing Co., Inc. Lighting & Controls

10385 SW Avery Street, Tualatin, OR 97062 **tel** 800-736-6682 **tech line** (6:00AM-4:00PM PT Mon-Fri) 800-959-6004

Leviton Manufacturing Co., Inc. Global Headquarters

201 North Service Road, Melville, NY 11747-3138 **tel** 800-323-8920 **tech line** (8:00AM-10:00PM ET Mon-Fri, 9:00AM-7:00PM ET Sat, 9:00AM-5:00PM ET Sun) 800-824-3005

Visit our Website at: www.leviton.com/smartsensors

©2024 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.

LES-G-10739/A23-mm