

Specialty Switches - Momentary Contact and Maintained Contact

Toggle and Decora Plus™ rocker styles for use in either line-voltage or low-voltage applications



Leviton specification grade maintained contact and momentary contact switches are ideal for use in applications such as fan controls, energy control systems, motor relays, low-voltage lighting system relays, and the like.

- Single Pole Single Throw (SPST), Single Pole Double Throw (SPDT) Center-OFF, and Double Pole Double Throw (DPDT) Center-OFF configurations
- Available with either 120/277 VAC or 24 V ratings
- Offered in the most popular colors used in commercial and industrial environments
- Heavy-duty construction for long-service life – backed by a 10-year limited warranty!

Ordering Information

Description	SPST			SPDT - Center OFF				DPDT - Center OFF		
	Toggle	Decora Plus™		Toggle		Decora Plus™		Toggle		Decora Plus™
	Momentary Contact	Momentary Contact	Maintained Contact	Momentary Contact	Maintained Contact	Momentary Contact	Maintained Contact	Momentary Contact	Maintained Contact	Maintained Contact
15 A, 120/277 VAC										
Brown	—	—	—	1256	1281	5657-2	—	—	1282	—
Ivory	—	5655-2I	—	1256-I	1281-I	5657-2I	5685-2I	—	1282-I	5686-2I
White	—	5655-2W	—	1256-W	1281-W	5657-2W	5685-2W	—	1282-W	5686-2W
White (marked HI/LOW/OFF)	—	—	—	—	—	—	5685-W	—	—	—
Gray	—	—	—	1256-GY	—	5657-2GY	5685-2GY	—	—	—
Lt Almond	—	5655-2T	—	—	—	5657-2T	—	—	—	5686-2T
Black	—	5655-2E	—	—	1281-L*	5657-2E	5685-2E	—	—	—
20 A, 120/277 VAC										
Brown	—	—	—	1257	1285	—	—	—	1286	—
Ivory	—	—	—	1257-I	1285-I	—	—	—	1286-I	—
White	—	—	—	1257-W	1285-W	—	—	—	1286-W	—
Gray	—	—	—	1257-GY	1285-GY	—	—	—	—	—
Red	—	—	—	1257-R	1285-R	—	—	—	—	—
Lt Almond	—	—	—	1257-T	1285-T	—	—	—	—	—
Black	—	—	—	1257-L*	1285-L*	—	—	—	—	—
30 A, 120/277 VAC										
Brown	—	—	—	1260	1287	—	—	1262	1288	—
Ivory	—	—	—	—	1287-I	—	—	—	1288-I	—
White	—	—	—	—	—	—	—	—	1288-W	—
Black	—	—	—	—	1287-L*	—	—	—	1288-L*	—
3 A, 24 V										
Brown	—	—	—	—	—	56081-2	—	—	—	—
Ivory	1080-I	56080-2I	56021-2I^	1081-I	—	56081-2I	—	—	—	—
White	1080-W	56080-2W	56021-2W^	1081-W	—	56081-2W	—	—	—	—
Gray	1080-GY	—	—	1081-GY	—	—	—	—	—	—
Red	1080-R	—	—	1081-R	—	56081-2R	—	—	—	—
Lt Almond	—	56080-2T	—	—	—	—	—	—	—	—
Black	—	56080-2E	56021-2E^	—	—	—	—	—	—	—
Replacement Key for Tamper-Resistant Switches										55500-PRT

* = Tamper-Resistant Toggle ^ = Standard ON/OFF positions

Available in Popular Commercial Colors



Visit our Website at:

www.leviton.com/commercial

email: commercial@leviton.com

Q-1054B

061521

Leviton Manufacturing Co., Inc.

201 N Service Rd, Melville, NY 11747

Telephone: 1-800-323-8920 • FAX: 1-800-832-9538

Tech Line: 1-800-824-3005 (M-F 8AM-10PM; Sat 9AM-7PM; Sun 9AM-5PM)

© 2021 Leviton Manufacturing Co., Inc. All rights reserved.

