

# Power Distribution

Power that drives your network







Servers, storage, and networking equipment only perform as well as the power that drives them. Leviton Power Distribution Units (PDUs) provide robust, reliable power to rack and cabinet applications.

Choose from a wide variety of horizontal and vertical models, or rack-mounted units with surge protection.



## P1000 Series PDUs

Leviton P1000 Series PDUs are ideal for server rooms and other environments that require cost-effective “always on” power. The robust, compact design makes them a perfect fit for harsh environments where space is limited.



## 5500/5505 Series PDUs

Leviton 5500 and 5505 Series PDUs help power and protect vital electronic equipment. These PDUs provide Surge Protection for connected equipment and are Listed to UL 1449.






# P1000 Series PDUs




Leviton P1000 Series PDUs are designed for data centers, wiring closets, and other environments that require cost-effective, “always on” power. The robust, compact design ensures that these products can be used wherever reliability and density are important.

## Input Plug Types



- All models feature circuit breaker protection to prevent current overloads
- Available in 120V configurations with 15, 20, or 30 amps
- LED indicators for power and grounding/polarity
- Hardwired power input cord
- 18-gauge cold-rolled steel construction
- Available in vertical Zero-U or horizontal 19-inch rack-mount styles

## Output Receptacle Types



# P1000 Series PDUs



P1021-12S



Vertical P1000 units ship with flat brackets, L-brackets, backplates, mounting buttons, screws, and washers to support a variety of rack and cabinet mounting options.



P1041-10S

P1044-10L

## UNMETERED HORIZONTAL POWER DISTRIBUTION UNITS (PDUs), SINGLE INPUT

PART NO.	INPUT				OUTPUT			DIMENSIONS (inches) H x W x D
	VOLTAGE	AMPS	CORD LENGTH	PLUG TYPE	VOLTAGE	RECEPTACLE TYPE	RECEPTACLE QUANTITY	
P1020-12S	120V	15A	12'	5-15P	120V	5-15R	10	1.75 x 17.5 x 4.5
P1021-12S	120V	20A	12'	5-20P	120V	5-20R	10	1.75 x 17.5 x 4.5
P1022-12L	120V	20A	12'	L5-20P	120V	5-20R	10	1.75 x 17.5 x 4.5
P1023-12L	120V	30A	12'	L5-30P	120V	5-20R	16	3.5 x 17.5 x 4.5


## UNMETERED VERTICAL POWER DISTRIBUTION UNITS (PDUs), SINGLE INPUT

PART NO.	INPUT				OUTPUT			DIMENSIONS (inches) L x W x D
	VOLTAGE	AMPS	CORD LENGTH	PLUG TYPE	VOLTAGE	RECEPTACLE TYPE	RECEPTACLE QUANTITY	
P1040-10S	120V	15A	10'	5-15P	120V	5-15R	16	30 L x 1.8 W x 1.75
P1041-10S	120V	20A	10'	5-20P	120V	5-20R	16	30 L x 1.8 W x 1.75
P1042-10L	120V	20A	10'	L5-20P	120V	5-20R	16	30 L x 1.8 W x 1.75
P1043-10S	120V	20A	10'	5-20P	120V	5-20R	24	48 L x 1.8 W x 1.75
P1044-10L	120V	20A	10'	L5-20P	120V	5-20R	24	48 L x 1.8 W x 1.75
P1045-10L	120V	30A	10'	L5-30P	120V	5-20R	24	48 L x 1.8 W x 1.75


All P1000 Series PDUs have hard-wired input cords.

# 5500 / 5505 Series PDUs

## Input Plug Types



## Output Receptacle Types



Leviton 5500 and 5505 Series Surge Protected Power Distribution Units (PDUs) help power and protect vital electronic equipment. The 5500 and 5505 Series share several key features, including:

- Resettable circuit breaker to protect against overloading
- 12 receptacles: 10 in back, 2 in front
- 20-amp versions available with either straight blade or locking input plug
- Mounts horizontally on 19-inch racks or cabinets
- UL Listed: UL 1449 and 1363

### 5500 Series with Enhanced Surge Protection

- **Peak surge current:** 72 kA
- **VPR — L-N:** 400 Vpk, L-G/N-G: 500 Vpk
- **EMI/RFI noise filtering:** 100 kHz to 30 MHz, -10 dB to -35 dB
- **Type SPD:** 3CA
- **Physical dimensions:** 1.75" H x 19" W x 4.55" D

### 5505 Series with Surge Protection

- **Peak surge current:** 27 kA
- **VPR — L-N:** 600 Vpk, L-G/N-G: 700 Vpk
- **EMI/RFI noise filtering:** 100 kHz to 30 MHz, -5 dB to -40 dB
- **Type SPD:** 3CA
- **Physical dimensions:** 1.75" H x 19" W x 2.5" D

# 5500 / 5505 Series PDUs



5500-190



5500-20L

## 5500 SERIES POWER DISTRIBUTION UNITS (PDUS) WITH SURGE PROTECTION

PART NO.	FOOTPRINT	ON/OFF SWITCH		INPUT				OUTPUT		
		YES	NO	INPUT VOLTAGE	AMPS	CORD LENGTH	INPUT PLUG	OUTPUT VOLTAGE	RECEPTACLE TYPE	RECEPTACLE QUANTITY
5500-190	Horizontal / Rack Mnt.	•		120V	15A	12'	5-15P	120V	5-15R	12
5500-192	Horizontal / Rack Mnt.	•		120V	20A	12'	5-20P	120V	5-20R	12
5500-20L	Horizontal / Rack Mnt.	•		120V	20A	12'	L5-20P	120V	5-20R	12
5500-15N	Horizontal / Rack Mnt.		•	120V	15A	12'	5-15P	120V	5-15R	12

## 5505 SERIES POWER DISTRIBUTION UNITS (PDUS) WITH SURGE PROTECTION

5505-190	Horizontal / Rack Mnt.	•		120V	15A	12'	5-15P	120V	5-15R	12
----------	------------------------	---	--	------	-----	-----	-------	------	-------	----

All 5500/5505 Series PDUs have hard-wired Input Cords.

Today's networks must be fast and reliable, with the flexibility to handle ever-increasing data demands. Leviton can help expand your network possibilities and prepare you for the future. Our end-to-end cabling systems feature robust construction that reduces downtime, and performance that exceeds standards. We offer quick-ship make-to-order solutions from our US and UK factories. We even invent new products for customers when the product they need is not available. All of this adds up to the **highest return on infrastructure investment.**

#### USA — NETWORK SOLUTIONS HEADQUARTERS

2222 - 222nd Street S.E., Bothell, WA, 98021, USA  
+1 (800) 722 2082 | [infousa@leviton.com](mailto:infousa@leviton.com) | [leviton.com/ns](http://leviton.com/ns)

##### Customer Service

+1 (800) 722 2082  
[insidesales@leviton.com](mailto:insidesales@leviton.com)

##### International Customer Service

+1 (425) 486 2222  
[intl@leviton.com](mailto:intl@leviton.com)

##### Leviton Berk-Tek Cable Customer Service

+1 (800) 237 5835  
[berktek.info@leviton.com](mailto:berktek.info@leviton.com)

##### Technical Support

+1 (800) 722 2082  
+1 (425) 486 2222  
[appeng@leviton.com](mailto:appeng@leviton.com)

#### APAC

+85 (2) 3620 2602 | [infoapac@leviton.com](mailto:infoapac@leviton.com) | [leviton.com/ns](http://leviton.com/ns)

##### Customer Service

+1 (631) 812 6228  
[infoasean@leviton.com](mailto:infoasean@leviton.com)

##### China

+85 (2) 2774 9876  
[infochina@leviton.com](mailto:infochina@leviton.com)

##### South Korea

+82 (2) 3273 9963  
[infokorea@leviton.com](mailto:infokorea@leviton.com)

#### CANADA

+1 (800) 461 2002 | [infoканада@leviton.com](mailto:infoканада@leviton.com) | [leviton.com/ns](http://leviton.com/ns)

##### Customer Service

+1 (514) 954 1840  
[pcservice@leviton.com](mailto:pcservice@leviton.com)

Network Solutions products are **available worldwide in over 100 countries.** Visit us online at [leviton.com/ns](http://leviton.com/ns) to learn more.



#### EUROPE

Viewfield Industrial Estate, Glenrothes, KY6 2RS, UK  
+44 (0) 1592 772124 | [infoeurope@leviton.com](mailto:infoeurope@leviton.com) | [leviton.com/ns/emea](http://leviton.com/ns/emea)

##### Customer Service

+44 (0) 1592 772124  
[customerserviceeu@leviton.com](mailto:customerserviceeu@leviton.com)

##### Technical Support

+44 (0) 1592 778494  
[appeng.eu@leviton.com](mailto:appeng.eu@leviton.com)

##### Benelux

+44 (0) 1592 772124  
[infobenelux@leviton.com](mailto:infobenelux@leviton.com)

##### Nordics

+46 (70) 9675033  
[infonordics@leviton.com](mailto:infonordics@leviton.com)

##### Central & Eastern Europe (CEE)

+44 (0) 1592 772124  
[infocee@leviton.com](mailto:infocee@leviton.com)

##### Portugal

+351 (21) 421 4133  
[infoportugal@leviton.com](mailto:infoportugal@leviton.com)

##### DACH

+49 (0) 173 272 0128  
[infodach@leviton.com](mailto:infodach@leviton.com)

##### Spain

+34 (91) 490 59 19  
[infospain@leviton.com](mailto:infospain@leviton.com)

##### France

+33 (0) 1709 87826  
[infofrance@leviton.com](mailto:infofrance@leviton.com)

##### UK & Ireland

+44 (0) 1592 772124  
[infouk@leviton.com](mailto:infouk@leviton.com)

##### Italy

+39 (02) 3534896 (Milan)  
+39 (06) 68584613 (Rome)  
[infoitaly@leviton.com](mailto:infoitaly@leviton.com)

#### LATAM

[infoLATAM@leviton.com](mailto:infoLATAM@leviton.com) | [leviton.com/ns](http://leviton.com/ns)

##### Customer Service

+52 (55) 2333 5963  
[infoLATAM@leviton.com](mailto:infoLATAM@leviton.com)

##### Caribbean

+1 (954) 593 1896  
[infocaribbean@leviton.com](mailto:infocaribbean@leviton.com)

##### Mexico

+52 (55) 2128 6286  
[lsamarketing@leviton.com](mailto:lsamarketing@leviton.com)

##### Colombia

+57 (1) 743 6045  
[infocolombia@leviton.com](mailto:infocolombia@leviton.com)

#### MIDDLE EAST & AFRICA

Bay Square, Building 3, Office 205, Business Bay, Dubai, UAE  
+971 (4) 247 9800 | [infoMEA@leviton.com](mailto:infoMEA@leviton.com) | [leviton.com/ns](http://leviton.com/ns)

##### Customer Service

+971 (4) 247 9800  
[lmeinfo@leviton.com](mailto:lmeinfo@leviton.com)