


SOLUTION BRIEF

CAT 6A DURAPORT® FOR OUTDOOR CAMERA OR WIRELESS ACCESS POINT (WAP)

Have more versatility in where you place security cameras and protect your network connections with DuraPort Industrial connectivity. The system includes a robust water-tight seal provided by the jack housing, coupled with cable that withstands outdoor exposure to provide a reliable solution for your outdoor security and wireless access.



- IP67-rated environmental sealing (dust/water protection) — withstands exposure to wind and rain associated with outdoor exposure
- Patented over-molded wallplate gasket and embedded sealing feature on wallplate mounting holes ensure watertight fit and proper orientation in standard NEMA boxes
- Twist-lock mating of data connection allows for easy installations and provides a robust seal
- Compatible with Atlas-X1® and eXtreme® Cat 6A Shielded jacks
- Ensures alien crosstalk (AXT), EMI/RFI immunity, and PoE performance



DURAPORT® INDUSTRIAL JACK HOUSING



- Accepts all QuickPort® jacks for fast installation and wide selection of jack types and colors
- Encapsulated RJ-45 design protects integral components
- Patented design

PART NUMBERS

DuraPort Housing with Jack Cap	D6700-00E
DuraPort Replacement Jack Cap	D6701-00E

DURAPORT INDUSTRIAL CAT 6A S/FTP PATCH CORDS




- Industrial Plug to RJ-45 Plug
- Eight standard lengths (custom lengths available)
- Twist-lock design for fast installation

PART NUMBERS

DuraPort Industrial Plug to RJ-45 Plug Patch Cord, 3 feet	D6723-03E
DuraPort Industrial Plug to RJ-45 Plug Patch Cord, 5 feet	D6723-05E
DuraPort Industrial Plug to RJ-45 Plug Patch Cord, 7 feet	D6723-07E
DuraPort Industrial Plug to RJ-45 Plug Patch Cord, 10 feet	D6723-10E
DuraPort Industrial Plug to RJ-45 Plug Patch Cord, 15 feet	D6723-15E
DuraPort Industrial Plug to RJ-45 Plug Patch Cord, 20 feet	D6723-20E
DuraPort Industrial Plug to RJ-45 Plug Patch Cord, 35 feet	D6723-35E
DuraPort Industrial Plug to RJ-45 Plug Patch Cord, 50 feet	D6723-50E

Note: Industrial plug to industrial plug patch cords also available.

DURAPORT INDUSTRIAL WALLPLATES




- Provide a durable, easy-to-clean solution for demanding environments
- Over-molded gasket ensures watertight fit
- Kits include jack housing(s), jack cap(s), and stainless steel wallplate

PART NUMBERS

DuraPort Industrial Wallplate, stainless steel, 1 port, single gang*	D6710-1S1
DuraPort Industrial Wallplate, stainless steel, 2 port, single gang*	D6710-1S2
DuraPort Industrial Wallplate, stainless steel, 2 port, dual gang*	D6710-2S2
DuraPort Industrial Wallplate, stainless steel, 4 port, dual gang*	D6710-2S4
DuraPort Industrial Kit, 1 port, single gang	D670K-1S1
DuraPort Industrial Kit, 2 port, single gang	D670K-1S2
DuraPort Industrial Kit, 2 port, dual gang	D670K-2S2
DuraPort Industrial Kit, 4 port, dual gang	D670K-2S4

* = Purchase jack housing(s) D6700-00E separately.

ATLAS-X1® CAT 6A SHIELDED QUICKPORT JACKS



- Tested and approved for use in air-handling spaces (plenum rating) in accordance with UL Standard 2043
- Independently tested and guaranteed to exceed all component, permanent link, and channel margins
- Patented Retention Force Technology™ protects against tine damage and maintains contact force between plug and jack, preventing arcing from intermittent disconnects in PoE applications
- PoE optimized tine geometry prevents arcing damage where plug and jack make contact, extending the life of the jack and ensuring maximum performance (see specification sheets for full PoE capabilities)
- Solid metal body dissipates 53% more heat than plastic, minimizing damage from excess heat in PoE applications
- Available with internal shutter to protect from dust and debris
- Unique tool-free design requires no specialized termination or re-termination tool
- Short jack design supports a wider range of applications (e.g. shallow boxes, enclosures, bend radius, etc.)
- Interchangeable icons in 13 colors (VOICE, DATA, AV, and blank) make it easy to identify and track data, voice, or other functions (select jacks include color matching icons)
- Proudly manufactured in the U.S.

PART NUMBERS

Atlas-X1 Cat 6A Shielded QuickPort Jack	6ASJK-R*6
---	-----------

* = Color: White (W), Light Almond (T), Ivory (I), Yellow (Y), Orange (O), Crimson (C), Dark Red (R), Purple (P), Blue (L), Green (V), Gray (G), Black (E), Brown (B)

ATLAS-X1 CAT 6A PATCH CORDS



- SlimLine boot cords feature narrow profile to reduce congestion in high-density applications
- Snagless boot design prevents tab breakage
- AXT suppression and EMI/RFI protection

PART NUMBERS

Atlas-X1 Component-Rated SlimLine Boot Patch Cord	6AS10-xx*
---	-----------

xx = Length: 3' (03), 5' (05), 7' (07), 10' (10), 15' (15), 20' (20)

* = Color: Yellow (Y), Red (R), Black (E), White (W), Blue (L), Green (G), Grey (S)
For assistance customizing your cords, please visit leviton.com/configurator or call Tech Support at 800.824.3005



Leviton DuraPort Cat 6 UTP System available at Leviton.com/DuraPort.