

BC020003

LED Strip Drivers

24V 50W 1-10V dimmable IP67 driver

Features & Benefits

- 24V 50W 1-10V dimmable IP67 driver for use with single colour LED strip



CLASS I



WARRANTY DIMMABLE



RATING

General Information

Trade Name

Environment

Suitable For Zones

Product Group

Color Finish

Product Shape

Overall Dimensions

Product Weight(kg)

Additional Information

Recommended Product Location

IP Rating

Origin of manufacturer

Warranty

Dimming Protocol Compatibility

LED tape

Demanding

Outside zone 1

LED Strip - accessory

Silver

Rectangular

158x 67.5 x 33.5mm

0.65

For use with: LED Strip 24V 4.8W(max run 10.4m) LED Strip 24V 9.6W(max run 7.8m)LED Strip 24V 14.4W(max run 5.2m)

For indoor/outdoor use only

IP67

Made in China

2 years standard warranty extends to 3 years when registered within the first year of purchase (See Website for terms and conditions)

1-10V

Driver Manufacturer	Euchips
Lighting Product Type 1	Accessory
Lighting Product Type 2	Tapelight

Electrical

Voltage Rating	220-277
Primary Running Current(Amp)	0.3
Operating Frequency Hz	50/60Hz
Secondary running current(mA)	2100
Constant Current or Constant Voltage	CV
Class	I
Output Voltage Max/Range (VDC)	24
EMC Compliant (EN55015)	Yes
Power Factor Correction	0.97
Input Electrical Connections	Live, Neutral, Earth
Dimmable	Yes, 1-10V

Thermals

Thermal Cut Out	yes
Insulation Coverage	Do not cover
Operating Temperature Range °C	-40 to +60

Controls and Sensors

Overload Protection	Yes, auto recovery
Max LED Load	50W

Construction


Primary Material	Aluminium
------------------	-----------

Packaging

Product Packaged Weight(kg)	0.725
Quantity Per Outer Carton	20
Product Bar Code EAN-13 Number	5052544092794

Standards & Approvals

Manufactured In Accordance To	BS EN 61347
CE Marked	Yes
UKCA Marked	Yes
Date code/Purchase order No.	Yes
WEEE Symbol	Yes
Certificate Of Conformity	Available on request
Accredited Members	LIA, ISO9001-2015, ISO14001-2015



L:131mm W:68mm H:33.5mm

JCC Lighting LTD, Lux Park, Chichester Business Park, City Fields Way, Tangmere, Chichester, West Sussex, PO20 2FT.
Sales: 01243 838999 (8am to 5pm Monday to Friday) Fax: 01243 838998 | sales@jcc.co.uk | www.jcc.co.uk
Company Registration Number: 03044848 | VAT Number: 918544112

This document is uncontrolled if printed, all information is subject to change

Version 143 [06/02/2023]